

Specifications



Photo is representative



Eaton BK/S501-V-6.3-R

Eaton S501 Series Fast-acting fuse 6.30A, 250 Vac or less, 32 Vdc (self certified), BK-S501-V-6-3-R

General specifications

PRODUCT NAME	Eaton Bussmann series S501 fast-acting fuse
CATALOG NUMBER	BK/S501-V-6.3-R
UPC	051712648387
PRODUCT LENGTH/DEPTH	5.54 mm
PRODUCT HEIGHT	97.3 mm
PRODUCT WIDTH	5.54 mm
PRODUCT WEIGHT	1.46 g
WARRANTY	Not Applicable
COMPLIANCES	RoHS Compliant CE Marked CCC Marked
CERTIFICATIONS	VDE
GLOBAL CATALOG	BK/S501-V-6.3-R
PRODUCT TYPE	Fast-acting fuse

Product specifications

USED WITH	Axial leads
AMPERAGE RATING	6.30A
FREQUENCY RATING - MAX	50 Hz
FREQUENCY RATING - MIN	50 Hz
VOLTAGE DROP	150 mV typical
INTERRUPT RATING	1.5 kAIC at 250 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
MATERIAL	Nickel-plated endcap construction Ceramic tube
QUANTITY	100
VOLTAGE RATING	250 Vac or less, 32 Vdc (self certified)
TYPE	Electronic
APPLICATION	Electronic circuits

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BK/S501-V-6.3-R](#)

[Eaton S501 ceramic tube fuses data sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

