

FST-R-08X00-G0200M



FST Flexible Service Terminal, 8 Port, 8 Mini-size (DLX) hardened Adapters at drop side, cable stub at feeder side, black, 200m long

- Flexible Service Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-terminated and environmentally sealed for use in optical drop cable deployments
- Flexible structure plus very small branching unit, allowing installation in constrained spaces
- Output cables are staggered, optimizing distributed space consumption and minimizing cable kinking

Product Classification

Regional Availability	EMEA
Product Type	Access terminal, without splitter/tap
Product Brand	DLX®
Product Series	FST-R
Minimum Order Quantity	2

General Specifications


Cable Type	Dielectric - Loose Tube
Distribution Type	8 ports
Enclosure Color	Black
Mounting	Handhole Pedestal
Port Type	Hardened mini-size DLX
Port, quantity	8
Splitter, quantity	0
Stub Type	Stub tail

Dimensions

Cable Stub Length	200 m 656.168 ft
Outer Cable Dimensions	5.5 mm (0.22 in)

Dimension Drawing

FST-R-08X00-G0200M



Material Specifications

Enclosure Material Type Engineered plastic

Optical Specifications

Fiber Type G.657.A2

Wavelength Range 1310–1625 nm

Insertion Loss, Terminal Connector, maximum 0.45 dB

Return Loss, Connector, minimum 60 dB

Environmental Specifications

Operating Temperature -20 °C to +65 °C (-4 °F to +149 °F)

Environmental Space Above ground | Below ground | Buried

Qualification Standards IEC 61753-1 Ed2 category G, IP68, 2 m waterhead

UV Resistance UV stabilized

Packaging and Weights

Packaging quantity 2

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

FST-R-08X00-G0200M

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

