




HONEYWELL PART NUMBER
13SX1-T
PRODUCT CODE VDK2000

REV	DOCUMENT	CHANGED BY	CHECK
12	0060324	VKR 13JAN10	CMH



- NOTES
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
 - 2 - TERMINALS ARE SOLDER DIPPED WITH RoHS-COMPLIANT TIN/COPPER/SILVER SOLDER.
 - 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250° F
 - 4 - MOVABLE CONTACT MATERIAL - 24 K SOLID GOLD OVERLAY
 - 5 - STATIONARY CONTACT MATERIAL - GOLD ALLOY

RELEASE NO.	PR-8887
REPLACES	

CHARACTERISTICS	ELECTRICAL DATA			DESIGN UNITS: INCH	DRAWN	SPK	15FEB08	Honeywell		
	CONTACT ARRANGEMENT SPDT			TOLERANCES UNLESS NOTED:	CHECK	RJ	15FEB08			
	30 VOLTS DC RATING			NO PLACE X ±	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE		
	INDUCTIVE			ONE PLACE .X ±						
OPERATING FORCE - - - 3.5 OZ MAX	SEA LEVEL			TWO PLACE .XX ±				SIZE	TYPE	DRAWING NAME
RELEASE FORCE - - - .75 OZ MIN	50,000 FT			THREE PLACE .XXX ±	INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			B	I	13SX1-T
DIFFERENTIAL TRAVEL - - .001 MAX	0.5 AMP			FOUR PLACE .XXXX ±				SCALE	WEIGHT	SHEET
OVERTRAVEL - - - .004 MIN	1 AMP			ANGLES ±	THIRD ANGLE PROJECTION			-	.003 LB MAX	1 OF 1
	MAXIMUM INRUSH 2 AMP									
	KEMA, CE	1A 250 V ~ T125	25E3		RASTER					
	UL, CSA	1A 125 VAC								