





Color: ■ gray      Similar to illustration



Dimensions in mm  
L = (pole no. - 1) x pin spacing + 10 mm  
L1 = L + 1.7 mm Δ version without mounting flange

PCB terminal block, 745 Series, operating tool

This PCB terminal block (item number 745-653/006-000) is designed to connect conductors quickly and easily. It offers the flexibility needed for different mounting types. Conductors can only be connected to this PCB terminal block if their strip length is between 12 and 13 mm . This product incorporates one conductor terminal and utilizes CAGE CLAMP®. Our renowned universal connection known as CAGE CLAMP® is the industry standard when it comes to connection technology and electrical interconnections. The item's dimensions are (51.7 x 33.5 x 33.4) mm (width x height x depth). This PCB terminal block is suitable for conductor cross sections ranging from 0.2 mm<sup>2</sup> to 16 mm<sup>2</sup>.

The contact surface is coated with tin. An operating tool is used to operate this PCB terminal block. The PCB terminal block is designed for THT soldering. Insert the conductor into the board at a 45° angle..



| Notes     |                                                                                                                                                                                                                                                                                                                                                        |
|-----------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Variants: | Other pole numbers<br>Versions for Ex e II and Ex i<br>Other colors<br>Mixed-color PCB connector strips<br>Versions with mounting flanges<br>Direct marking<br>Solder pin length: 5 mm<br>Other versions (or variants) can be requested from WAGO Sales or configured at <a href="https://configurator.wago.com/">https://configurator.wago.com/</a> . |

| Electrical data                 |  |                |        |        |
|---------------------------------|--|----------------|--------|--------|
| Ratings per                     |  | IEC/EN 60664-1 |        |        |
| Overvoltage category            |  | III            | III    | II     |
| Pollution degree                |  | 3              | 2      | 2      |
| Nominal voltage                 |  | 1000 V         | 1000 V | 1000 V |
| Rated impulse withstand voltage |  | 12 kV          | 12 kV  | 12 kV  |
| Rated current                   |  | 76 A           | 76 A   | 76 A   |
| Approvals per                   |  | UL 1059        |        |        |
| Use group                       |  | B              | C      | D      |
| Rated voltage                   |  | 600 V          | 600 V  | -      |
| Rated current                   |  | 65 A           | 65 A   | -      |

| Approvals per |  | CSA   |       |   |
|---------------|--|-------|-------|---|
| Use group     |  | B     | C     | D |
| Rated voltage |  | 600 V | 600 V | - |
| Rated current |  | 65 A  | 65 A  | - |

| Connection Data            |   |
|----------------------------|---|
| Clamping units             | 3 |
| Total number of potentials | 3 |
| Number of connection types | 1 |
| Number of levels           | 1 |
| Number of jumper slots     | 1 |

| Connection 1                                      |                                     |
|---------------------------------------------------|-------------------------------------|
| Connection technology                             | CAGE CLAMP®                         |
| Actuation type                                    | Operating tool                      |
| Solid conductor                                   | 0.2 ... 16 mm² / 24 ... 6 AWG       |
| Fine-stranded conductor                           | 0.2 ... 16 mm² / 24 ... 6 AWG       |
| Fine-stranded conductor; with insulated ferrule   | 0.25 ... 10 mm²                     |
| Fine-stranded conductor; with uninsulated ferrule | 0.25 ... 10 mm²                     |
| Strip length                                      | 12 ... 13 mm / 0.47 ... 0.51 inches |
| Conductor connection direction to PCB             | 45 °                                |
| Pole number                                       | 3                                   |

| Physical data           |                          |
|-------------------------|--------------------------|
| Pin spacing             | 20 mm / 0.787 inches     |
| Width                   | 51.7 mm / 2.035 inches   |
| Height                  | 33.5 mm / 1.319 inches   |
| Height from the surface | 27 mm / 1.063 inches     |
| Depth                   | 33.4 mm / 1.315 inches   |
| Solder pin length       | 6.5 mm                   |
| Solder pin dimensions   | 1.2 x 1.6 mm             |
| Drilled hole diameter   | 2.2 <sup>(+0.1)</sup> mm |



| PCB contact                         |  |                                          |
|-------------------------------------|--|------------------------------------------|
| PCB contact                         |  | THT                                      |
| Solder pin arrangement              |  | over the entire terminal strip (in-line) |
| Number of solder pins per potential |  | 4                                        |

| Material data                      |  |                                                                          |
|------------------------------------|--|--------------------------------------------------------------------------|
| Note (material data)               |  | <a href="#">Information on material specifications can be found here</a> |
| Color                              |  | gray                                                                     |
| Material group                     |  | I                                                                        |
| Insulation material (main housing) |  | Polyamide (PA66)                                                         |
| Flammability class per UL94        |  | V0                                                                       |
| Clamping spring material           |  | Chrome-nickel spring steel (CrNi)                                        |
| Contact material                   |  | Electrolytic copper (E <sub>cu</sub> )                                   |
| Contact Plating                    |  | Tin                                                                      |
| Fire load                          |  | 0.571 MJ                                                                 |
| Weight                             |  | 35.3 g                                                                   |

| Environmental requirements |  |                 |
|----------------------------|--|-----------------|
| Limit temperature range    |  | -60 ... +105 °C |

| Commercial data       |  |                                |
|-----------------------|--|--------------------------------|
| Product Group         |  | 4 (Printed Circuit Connectors) |
| PU (SPU)              |  | 20 pcs                         |
| Packaging type        |  | Box                            |
| Country of origin     |  | PL                             |
| GTIN                  |  | 4044918303071                  |
| Customs tariff number |  | 85369010000                    |

| Product Classification |  |                      |
|------------------------|--|----------------------|
| UNSPSC                 |  | 39121409             |
| eCl@ss 10.0            |  | 27-44-04-01          |
| eCl@ss 9.0             |  | 27-44-04-01          |
| ETIM 9.0               |  | EC002643             |
| ETIM 10.0              |  | EC002643             |
| ECCN                   |  | NO US CLASSIFICATION |

| Environmental Product Compliance |  |                         |
|----------------------------------|--|-------------------------|
| RoHS Compliance Status           |  | Compliant, No Exemption |

Approvals / Certificates

| General approvals                                                                                                                                                                                                                                                                                                                              |  | General approvals              |         |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------------|---------|
|     |  | UR                             | UL 1059 |
|                                                                                                                                                                                                                                                                                                                                                |  | Underwriters Laboratories Inc. | E45172  |

| Approval                        | Standard      | Certificate Name |
|---------------------------------|---------------|------------------|
| CCA<br>DEKRA Certification B.V. | EN 60947      | 2160584.14       |
| CCA<br>DEKRA Certification B.V. | EN 60947      | NTR NL-7094      |
| CSA<br>DEKRA Certification B.V. | C22.2 No. 158 | 1604421          |



Declarations of conformity and manufacturer's declarations

| Approval                                                | Standard | Certificate Name |
|---------------------------------------------------------|----------|------------------|
| EU-Declaration of Confor-<br>mity<br>WAGO GmbH & Co. KG | -        | -                |
| UK-Declaration of Confor-<br>mity<br>WAGO GmbH & Co. KG | -        | -                |

Downloads

Environmental Product Compliance

| Compliance Search                                      |
|--------------------------------------------------------|
| Environmental Product<br>Compliance<br>745-653/006-000 |



Documentation

| Additional Information |
|------------------------|
| Technical Section      |
| 03.04.2019             |
| pdf<br>2027.26 KB      |



CAD/CAE-Data

| CAD data                        |
|---------------------------------|
| 2D/3D Models<br>745-653/006-000 |



| CAE data                             |
|--------------------------------------|
| EPLAN Data Portal<br>745-653/006-000 |
| ZUKEN Portal<br>745-653/006-000      |



PCB Design

|                                                                |
|----------------------------------------------------------------|
| Symbol and Footprint<br>via SamacSys<br>745-653/006-000        |
| Symbol and Footprint<br>via Ultra Librarian<br>745-653/006-000 |





| 1 Compatible Products                                                                                                                                                                  |                                                                                                                                                                                       |                                                                                                                                                                                        |                                                                                                                                                                                       |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1.1 Optional Accessories                                                                                                                                                               |                                                                                                                                                                                       |                                                                                                                                                                                        |                                                                                                                                                                                       |
| 1.1.1 Ferrule                                                                                                                                                                          |                                                                                                                                                                                       |                                                                                                                                                                                        |                                                                                                                                                                                       |
| 1.1.1.1 Ferrule                                                                                                                                                                        |                                                                                                                                                                                       |                                                                                                                                                                                        |                                                                                                                                                                                       |
|                                                                                                       |                                                                                                      |                                                                                                       |                                                                                                    |
| <p><b>Item No.: 216-262</b><br/>Ferrule; Sleeve for 0.75 mm² / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray</p> | <p><b>Item No.: 216-263</b><br/>Ferrule; Sleeve for 1 mm² / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red</p>    | <p><b>Item No.: 216-264</b><br/>Ferrule; Sleeve for 1.5 mm² / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black</p> | <p><b>Item No.: 216-209</b><br/>Ferrule; Sleeve for 10 mm² / AWG 8; insulated; electro-tin plated; red</p>                                                                            |
|                                                                                                       |                                                                                                      |                                                                                                       |                                                                                                    |
| <p><b>Item No.: 216-109</b><br/>Ferrule; Sleeve for 10 mm² / AWG 8; un-insulated; electro-tin plated</p>                                                                               | <p><b>Item No.: 216-266</b><br/>Ferrule; Sleeve for 2.5 mm² / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; blue</p> | <p><b>Item No.: 216-267</b><br/>Ferrule; Sleeve for 4 mm² / AWG 12; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray</p>    | <p><b>Item No.: 216-208</b><br/>Ferrule; Sleeve for 6 mm² / AWG 10; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; yellow</p> |
|                                                                                                       |                                                                                                                                                                                       |                                                                                                                                                                                        |                                                                                                                                                                                       |
| <p><b>Item No.: 216-108</b><br/>Ferrule; Sleeve for 6 mm² / AWG 10; un-insulated; electro-tin plated; silver-colored</p>                                                               |                                                                                                                                                                                       |                                                                                                                                                                                        |                                                                                                                                                                                       |
| 1.1.2 Jumper                                                                                                                                                                           |                                                                                                                                                                                       |                                                                                                                                                                                        |                                                                                                                                                                                       |
| 1.1.2.1 Jumper                                                                                                                                                                         |                                                                                                                                                                                       |                                                                                                                                                                                        |                                                                                                                                                                                       |
|                                                                                                     |                                                                                                    |                                                                                                    |                                                                                                                                                                                       |
| <p><b>Item No.: 745-681</b><br/>Jumper; 2-way; unplated; silver-colored</p>                                                                                                            | <p><b>Item No.: 745-682</b><br/>Jumper; 2-way; unplated; silver-colored</p>                                                                                                           | <p><b>Item No.: 745-683</b><br/>Jumper; 3-way; silver-colored</p>                                                                                                                      |                                                                                                                                                                                       |
| 1.1.3 Marking                                                                                                                                                                          |                                                                                                                                                                                       |                                                                                                                                                                                        |                                                                                                                                                                                       |
| 1.1.3.1 Marker                                                                                                                                                                         |                                                                                                                                                                                       |                                                                                                                                                                                        |                                                                                                                                                                                       |
|                                                                                                     |                                                                                                    |                                                                                                    |                                                                                                  |
| <p><b>Item No.: 2009-145/000-006</b><br/>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; blue</p>                                | <p><b>Item No.: 2009-145/000-007</b><br/>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; gray</p>                               | <p><b>Item No.: 2009-145/000-023</b><br/>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; green</p>                               | <p><b>Item No.: 2009-145/000-012</b><br/>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; orange</p>                             |
|                                                                                                     |                                                                                                    |                                                                                                    |                                                                                                  |
| <p><b>Item No.: 2009-145/000-005</b><br/>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; red</p>                                 | <p><b>Item No.: 2009-145/000-024</b><br/>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; violet</p>                             | <p><b>Item No.: 2009-145</b><br/>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white</p>                                       | <p><b>Item No.: 2009-145/000-002</b><br/>Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; yellow</p>                             |
|                                                                                                     |                                                                                                    |                                                                                                    |                                                                                                  |
| <p><b>Item No.: 248-501/000-006</b><br/>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; blue</p>                                                                 | <p><b>Item No.: 248-501/000-007</b><br/>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; gray</p>                                                                | <p><b>Item No.: 248-501/000-023</b><br/>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; green</p>                                                                | <p><b>Item No.: 248-501/000-017</b><br/>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; light green</p>                                                         |
|                                                                                                     |                                                                                                    |                                                                                                    |                                                                                                  |
| <p><b>Item No.: 248-501/000-012</b><br/>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; orange</p>                                                               | <p><b>Item No.: 248-501/000-005</b><br/>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; red</p>                                                                 | <p><b>Item No.: 248-501/000-024</b><br/>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; violet</p>                                                               | <p><b>Item No.: 248-501</b><br/>Mini-WSB marking card; as card; not stretchable; plain; snap-on type; white</p>                                                                       |



1.1.3.1 Marker



**Item No.: 248-501/000-002**  
Mini-WSB marking card; as card; not stretchable; plain; snap-on type; yellow



**Item No.: 793-5501/000-006**  
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; blue



**Item No.: 793-5501/000-007**  
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; gray



**Item No.: 793-5501/000-023**  
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; green



**Item No.: 793-5501/000-017**  
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; light green



**Item No.: 793-5501/000-012**  
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; orange



**Item No.: 793-5501/000-005**  
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; red



**Item No.: 793-5501/000-024**  
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; violet



**Item No.: 793-5501**  
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; white



**Item No.: 793-5501/000-002**  
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; yellow



**Item No.: 793-501**  
WMB marking card; as card; not stretchable; plain; snap-on type; white



**Item No.: 2009-115/000-006**  
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; blue



**Item No.: 2009-115/000-007**  
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; gray



**Item No.: 2009-115/000-023**  
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; green



**Item No.: 2009-115/000-017**  
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; light green



**Item No.: 2009-115/000-012**  
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; orange



**Item No.: 2009-115/000-024**  
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; violet



**Item No.: 2009-115**  
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white



**Item No.: 2009-115/000-002**  
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; yellow

1.1.4 Test and measurement

1.1.4.1 Testing accessories



**Item No.: 210-136**  
Test plug; 2 mm Ø; with 500 mm cable; red

1.1.5 Tool


1.1.5.1 Operating tool



**Item No.: 210-721**  
Operating tool; Blade: 5.5 x 0.8 mm; with a partially insulated shaft; multicoloured


Installation Notes

Conductor termination




Inserting/removing a conductor via 5.5 mm screwdriver – 745 Series, 16 mm².

Marking




Marking via Mini-WSB and WMB markers or factory direct marking – 745 Series.

Testing




Testing with test plug – 745 Series.


Commoning



Inserting a comb-style jumper bar.



To insert a comb-style jumper bar, push it down using a screwdriver until it hits the backstop – 745 Series.



To remove the jumper bar, lift it up using a screwdriver – 745 Series.