

Catalog No. TY272MX

Description: CBL TIE 120LB 9IN UV BLK NYLON

UPC No 786210850726

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 224mm (8.8 Inches), Width of 6.9mm (0.27 Inch), Thickness of 1.5mm (0.06 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds), Bulk Pack

Representative Image

Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Stainless Steel Barb
Tensile Strength	120 pounds , 530 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405 UL E49405

Dimensions

Width	0.275 in , 6.99 mm
Length	8.75 in , 222.3 mm
Thickness	0.07 in , 1.78 mm
Bundle Diameter	0.236 to 1.97 in , 6 to 50 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant

ETIM Classification

ETIM	EC000046 Cable tie
Band width	6.9 mm

by ABB

ETIM	EC000046 Cable tie
Band width	0.27 inch
Length belt/tape/tie	224 mm
Length belt/tape/tie	8.8 inch
Tie thickness	1.5 mm
Tie thickness	0.06 inch
Max. bundle diameter	51 mm
Max. bundle diameter	2.01 inch
Min. holding force	540 N
Operation temperature	-60-+85 °C
Operation temperature	-76-+185 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y