


COAXIAL CONNECTOR, TNC, 50 Ohm, Right angle cable plug (male)

16_TNC-50-2-10/133_N

Properties

- Threaded coupling mechanism improves control over the interface dimensions
- Used under a higher environmental load than BNC
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 11 GHz



Product configuration		
Interface type	Gender	Standard
TNC	plug	IEC 60169-17_MIL-STD-348A/313_CECC 22200

Interface and material data		
Piece parts	Material	Plating
Centre contact	Brass	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 2 GHz	29 dB	1.07
2 GHz ... 3 GHz	26 dB	1.1
3 GHz ... 4 GHz	20 dB	1.22

Mechanical data	
Weight	0.0297 kg
Mating cycles	500
Cable entry centre contact	soldered

COAXIAL CONNECTOR, TNC, 50 Ohm, Right angle cable plug (male)

16_TNC-50-2-10/133_N

Mechanical data	
Cable entry outer contact	clamped

Environmental data	
Operation temperature	-65 °C ... 165 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84013229	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
84013229	16_TNC-50-2-10/133_NE	Single

Suitable cables	
Cable group	X3 - 2 mm / 50 Ohm U2 - 2 mm / 50 Ohm
Suitable cables	RG_316_/U RG_188_A/U RG_174_/U

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543112	74_Z-0-0-2	Spanner

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2984 / Date of publication: 11.07.2025 / uncontrolled copy