

Color: orange

Similar to illustration

Technical data	
Marking method	Thermal transfer
Marking	L3
Marking (number)	100
Marking direction	Vertical marking
Marking color	black
Marking type	Symbol
Marking differentiation	Same symbols per strip
Delivery form	Marker card
Delivery form configuration	10 strips with 10 markers per card
Flammability class per UL94	V2
Physical data	
Marker/strip width	5 mm
Marker width	5 mm
Mechanical data	
Smear resistance	EN 60998-1:2004
Material data	
Color	orange
UV resistance	EN 60068-2-5:2010 Procedure B
Halogen-free	Yes
Weight	9 g
Fire load	0.27 MJ



Commercial data	
Product Group	2 (Terminal Block Accessories)
PU (SPU)	50 (5) pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332034609
Customs tariff number	49119900000

Product classification	
UNSPSC	55121718
eCl@ss 10.0	27-14-11-37
eCl@ss 9.0	27-14-11-37
ETIM 9.0	EC000761
ETIM 8.0	EC000761
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance


Compliance Search

Environmental Product Compliance
793-676/000-012


↓

Installation Notes


Application




Separating a strip from the WMB or WMB marker card.



Stretching a WMB marker strip.




Separating an individual marker from the WMB marker strip – for larger terminal blocks.




Snapping a marking strip into the marker slot.

Marking



Snapping a WMB marker strip into the marker slot of the double marker carrier.



Snapping a marking strip into the marker slot.