


PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
A	DCN 56713	03/25	SEE PDM







MATERIALS:

BODIES & CONTACTS:	BERYLLIUM COPPER PER ASTM B196, ALLOY No. UNS C17300, TD04.
INSULATORS:	PTFE PER ASTM D1710.
SPRING:	MUSIC WIRE PER ASTM A228

FINISHES:

BODIES & CONTACTS:	GOLD PER ASTM B488, TYPE II GRADE C, CLASS 1.27, OVER NICKEL PER AMS-QQ-N-290, .000050" MINIMUM.
SPRING:	ZINC

PERFORMANCE:

IMPEDANCE:	50 OHMS.
FREQ. RANGE:	DC TO 32 GHz.
AXIAL COMPRESSION:	.030 NOMINAL

MATERIAL: SEE NOTES

FINISH: SEE NOTES

SURFACE AREA: N/A

PROPRIETARY

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.

DIMENSIONS ARE IN INCHES TOLERANCES:

FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15'

DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005

INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994

THIRD ANGLE PROJECTION

UNLESS OTHERWISE SPECIFIED

1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS]
2) ALL DIMENSIONS ARE AFTER PLATING.
3) BREAK CORNERS & EDGES .005 R. MAX.
4) CHAM. 1ST & LAST THREADS.
5) SURFACE ROUGHNESS 63 MIL-STD-10.
6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R.
7) REMOVE ALL BURRS

DRAWN:	ENB 06/10/24
CHECKED:	SEE PDM
APPROVED:	SEE PDM

Amphenol SV MICROWAVE
www.svmicrowave.com

TITLE: SMPS F TO SMPS F STR. COMPRESSIBLE ADAPTER

SIZE B | DWG. NO. 1138-4073

SCALE: 16:1 | SHEET 1 OF 1

Downloaded from Arrow.com.