
Part Number : 532611171
Product Description : 1.25mm Pitch, PicoBlade PCB Header, Single Row, Right-Angle, Surface Mount, Tin (Sn) Plating, Friction Lock, 11 Circuits, Natural, Tape and Reel
Series Number : 53261
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

532611171_sd.pdf

532611171_stp.zip

Symbol and Footprint (Multi-Format)

532611171.dxf

Specifications

510210000-AS-000.pdf

SPK-53261-002-001.pdf

510211024-PS-000.pdf

510211124-PS-000.pdf

PS-51021-024-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	53261
Description	1.25mm Pitch, PicoBlade PCB Header, Single Row, Right-Angle, Surface Mount, Tin (Sn) Plating, Friction Lock, 11 Circuits, Natural, Tape and Reel
Application	Wire-to-Board
Component Type	PCB Header
Product Name	PicoBlade
UPC	822348164240

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

Downloaded from Arrow.com.

Physical

Breakaway	No
Circuits (Loaded)	11
Circuits (maximum)	11
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Gender	Male
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	No
Lock to Mating Part	Yes
Mated Height	3.40mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyamide (PA)
Net Weight	299.100/mg
Number of Rows	1
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to PCB	Yes
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

Mates With / Use With

Downloaded from Arrow.com.

Mates with Part(s)

Description	Part Number
PicoBlade Single Row Receptacle Housings	51021
PicoBlade Female-to-PicoBlade Female Off-the-Shelf (OTS) Cable Assemblies	15134

Downloaded from Arrow.com.