


ACCESSORIES

EFA04 91 ASS
Fiber Winding and Storage Reel







Features
- Fiber maintained on a 30mm radius
- Stores up to 5000mm of 900 micron fiber
- Also accepts ribbon fiber
- Easy pull-out of fiber
- Gentle winding motion by hand
- Board mountable using Stand-off EFA04 27 ASS (page 43)
- Stackable using Stacking Pillar EFA04 53 ASS (page 43)


A Europlus/Richco product


Material: Flame Retardant Polyamide 6 (UL 94V0) Color: Black
Standard Pack: 50 per bag


Dimensioned in millimeters


EFA04 67 ASS
Fiber Winding Reel

Features
- Intended to be used with Identification Tape (one piece per reel included)
- Wound fiber is taped to maintain bend radius and provide identification
- Two-part reel is then disassembled for easy fiber removal
- Stores up to 8000mm of 900 micron fiber at a 30mm radius
- Reusable











A-A








A Europlus/Richco product

Material: 40% Glass-filled Liquid Crystal Polymer Color: Black
Standard Pack: 50 per bag


Dimensioned in millimeters


Downloaded from Arrow.com.



EFA04 78 002

Multi-Position Array Tray






Features

- Design layout using various Corner Guides (page 44) and Fiber Reels (page 42)
- Stackable using Stacking Pillar EFA04 53 ASS (page 43)
- Board mountable using Stand-off EFA04 27 ASS (page 43)
- Can be broken apart into 3 segments


A Europlus/Richco product

Material: Flame Retardant Polyamide 6 (UL 94V0) Color: Black
Standard Pack: 50 per bag

Dimensioned in millimeters



EFA64 01 001



EFA64 08 002

EFA64 XX XXX

Polishing Puck



Features

- Maintains perpendicular placement of ferrule to polishing surface
- EFA64 01 001 accepts FC, SC, ST and E2 connectors
- EFA64 08 002 accepts MT-RJ connectors

A Europlus/Richco product



Material: 15% Glass-filled Polyamide 6 • Color: Black
Standard Pack: 50 per bag
Part No.
EFA64 01 001
EFA64 08 002

Dimensioned in millimeters


Downloaded from Arrow.com.

ACCESSORIES

RKW
Richco Kwik Wrap

NOTE:
See FTH-27 for a Flat Tie Holder designed for RKW Series




Features
- Custom sizes and styles available by special order
- Excellent in reusable applications
- Won't pinch fiber

Material: Low Density Polyethelene Hook • Nylon Knit Loop • Color: Black (-BK), White (-W), Blue (-BL), Red (-R), Yellow (-YL), Green (-GN), Orange (-OR). Specify suffix when ordering.			
Part No.	**Standard Pack: 100 per bag**		
	"A" ± 1/8 (3.2)	**"W" ± .125 (3.2)**	**"L" ± 1/2 (12.7)**
RKW-6-6	3/8 (9.5)	.75 (19.1)	6 (152.4)
RKW-8-6	1/2 (12.7)	1.0 (25.4)	
RKW-8-8			8 (203.2)
RKW-8-11			11 (279.4)
RKW-12-15	3/4 (19.1)		15 (381.0)
RKW-12-18		1.5 (38.1)	18 (457.2)
RKW-12-24			24 (609.6)


FTH-27
Flat Tie Holder


Features
- Accommodates RKW series ties up to 1/2" wide



- UL #E71558

RKWID-8-8
Richco Kwik Wrap, Identification






Features
- Identifies wires, bundles, leads or terminals


Material: Low Density Polyethelene Hook • Nylon Knit Loop • Color: Black (-BK), White (-W), Blue (-BL), Red (-R), Yellow (-YL), Green (-GN), Orange (-OR). Specify suffix when ordering.
Standard Pack: 100 pieces

Downloaded from Arrow.com.

RKWB


Richco Kwik Wrap on Base





Features

- Accommodates a wide variety of diameters
- Releasable





Material: Low Density Polyethelene Hook • Nylon Knit Loop • Color: Black


Standard Pack: 100 per bag


RKWFA-16-300


Richco Kwik Wrap - Adhesive Flat Wiring













Material: Low Density Polyethelene Hook • Nylon Knit Loop • Color: Black

Standard Pack: 100 pieces

OFDS-1

Optical Fiber Duplex Splitter





Features

- For use on 3mm dual patchcord fibers to stop continued pigtail splitting
- Two-piece design snaps together

Material: ABS • Color: Black


Standard Pack: 1000 of each per bag

Dimensioned in millimeters


Downloaded from Arrow.com.

ACCESSORIES

WSLT
Wire Saddle Locking Top




• UL #E71558




Features
- Safely isolates cable or wire from board components
- Lock is releasable for repair, replacement or addition of wire or cable

Color: Natural									
Part No.	Standard Pack: 1000 per bag								
Material: Nylon 6/6, RMS-01	Material: Flame Retardant Nylon, RMS-19	Dim. "A"	Dim. "B"	Dim. "C"	Dim. "D"	Dim. "E"	Dim. "F"	Dim. "G"	Hole Dia. ± .003 (±0.08)
WSLT-3.5-2-1-01	WSLT-3.5-2-1-19	.13 (3.4)	.53 (13.5)	.35 (8.8)	.77 (19.6)	.38 (9.5)	.118 (3.0)	.10 (2.5)	.138 (3.50)
WSLT-01-1-01	WSLT-01-1-19					.62 (15.8)	7/32 (5.6)	.11 (2.8)	.187 (4.75)
WSLT-01A-01	WSLT-01A-19	.19 (4.8)	.42 (10.7)	.41 (10.4)	.66 (16.8)				
WSLT-01-2-01	WSLT-01-2-19	.36 (9.1)		.59 (15.0)					
WSLT-02A-01	WSLT-02A-19	.39 (10.0)	.64 (16.3)	.61 (15.5)	.88 (22.4)				
WSLT-03-2-01	WSLT-03-2-19	.56 (14.1)		.87 (22.0)					
WSLT-03-3-01	WSLT-03-3-19	.85 (21.7)	.71 (18.0)	1.08 (27.5)	.95 (24.1)				

WSLT-9
Wire Saddle, Locking Top Quarter-Turn Base




Features
- Low bottom-of-the-board protrusion
- Easily releasable
- Reusable




Material: Nylon 6/6, RMS-01 • Color: Natural								
Part No.	Standard Pack: 1000							
	"A"	"B"	"C" Ref.	"D"	"E"	"F"	"G"	"H"
WSLT-9-01A-01	.201 (5.1)	.421 (10.7)	.26 (6.6)	.661 (16.8)	.563 (14.3)	.197 (5.0)	.134 (3.4)	.039 (1.0)
WSLT-9-01-2-01	.358 (9.1)		.441 (11.2)					
WSLT-9-02-1-01	.134 (3.4)	.531 (13.5)	.209 (5.3)	.772 (19.6)				
WSLT-9-02A-1-01	.394 (10.0)	.642 (16.3)	.461 (11.7)	.882 (22.4)				
WSLT-9-03-2-01	.555 (14.1)		.717 (18.2)					
WSLT-9-03-3-01	.854 (21.7)	.709 (18.0)	.933 (23.7)	.949 (24.1)				
Flame retardant nylon available by special order. To order, replace -01 with -19								

Downloaded from Arrow.com.

EFCW
Extruded Flat Cable Clamp






Material: Clip Base - Rigid PVC, RMS-04; Bottom Adhesive 1/16 (1.6) Thick, RMS-15 • Color: Natural						
Part No.	Standard Pack: 100 per bag					
	Max. No. of Conductors	"A" ± .015 (0.4)	"B" ± .020 (0.5)	"C" Ref.	"D" ± .014 (0.4)	"F" ± .020 (0.5)
EFCW-29A-RT	30	1.24 (31.5)	1.79 (45.5)	.40 (10.2)	.75 (19.1)	.22 (5.6)
EFCW-30A-RT		1.26 (32.0)	1.80 (45.7)	.51 (13.0)	.76 (19.3)	.28 (7.1)
EFCW-40A-RT	40	1.56 (39.6)	2.11 (53.6)			
EFCW-50A-RT	50	2.52 (64.0)	3.05 (77.5)			.26 (6.6)

SF
Silicone Foam

• UL #E57750




SILICONE FOAM ROLLS			
Part No.	"T" ± .015 (0.4)	"L" ± .13 (3.2)	"W" .030 (0.8)
SF2R	.13 (3.2)	180 (4572)	.75 (19.1)
SF3R	.19 (4.8)		

USAGE CHART		
Silicone Foam is cut to length to fit into the Extruded Flat Cable Clamps		
Part No.	Apply this Part No.	In this Quantity
EFCW-29	SF2-30	2
EFCW-30	SF2-30	1
	SF3-30	
EFCW-40	SF2-40	
	SF3-40	
EFCW-50	SF2-50	
	SF3-50	
Install SF2 on bottom & SF3 on top. Exception for EFCW-29 install SF2 on top & bottom.		

Material: Adhesive Backed V-0 Silicone Foam, RMS-135 • Color: Gray			
Part No.	Standard Pack: 100 per bag		
	"T" ± .015 (0.4)	"L" ± .030 (0.8)	"W" ± .030 (0.8)
SF2-30	.13 (3.3)	1.23 (31.2)	.75 (19.1)
SF2-40		1.53 (38.9)	
SF2-50		2.49 (63.2)	
SF3-30	.19 (4.8)	1.23 (31.2)	
SF3-40		1.53 (38.9)	
SF3-50		2.49 (63.2)	

EFCWSF
Extruded Flat Cable Clamp with Silicone Foam



Features

• Provides hold for varying thickness cables and is gentle on fiber cables





Material: Clip Base - Rigid PVC, RMS-04; Foam - V-0 Silicone, RMS-135;Bottom Adhesive 1/16 (1.6) Thick, RMS-15 • Color: Natural									
Part No. with Rubber Cushion	Standard Pack: 100 per bag								
	Max. No. of Conductors	"A" ± .015 (0.4)	"B" ± .020 (0.5)	"C" Ref.	"D" ± .015 (0.4	"E" Ref.	"F" ± .020 (0.5)	"G" Ref.	"H" Ref.
EFCWSF-29A-RT	30	1.24 (31.5)	1.79 (45.5)	.40 (10.2)	.75 (19.1)	1.23 (31.2)	.22 (5.6)	.13 (3.3)	.13 (3.2)
EFCWSF-30A-RT		1.26 (32.0)	1.80 (45.7)	.51 (13.0)	.76 (19.3)		.28 (7.1)		.19 (4.8)
EFCWSF-40A-RT	40	1.56 (39.6)	2.11 (53.6)			1.53 (38.9)			
EFCWSF-50A-RT	50	2.52 (64.0)	3.05 (77.5)			2.49 (63.2)	.26 (6.6)		

Downloaded from Arrow.com.

ACCESSORIES

WHC
Wire Harness







Features
- Cable and wire can be installed or removed for repair without removing clamp
- Mounts with screws, mounting buttons or rivets

Material: Nylon 6/6, RMS-01 • Color: Natural						
Part No.	**"A" (Holding Diameter)**	**"B"**	**"C"**	**"D"**	**"E" Ref.**	**Standard Pack**
WHC-125-01	1/8 (3.2)	.05 (1.3)	.33 (8.4)	.23 (5.8)	.75 (19.1)	1000 per Bag
WHC-250-01	1/4 (6.4)	.04 (1.0)	.40 (10.2)	.25 (6.4)	.83 (21.1)	
WHC-375-01	3/8 (9.5)	.05 (1.3)		.19 (4.8)	.83 (21.1)	
WHC-500-01	1/2 (12.7)	.07 (1.8)		.25 (6.4)	1 - 5/32 (29.4)	
WHC-625-01	5/8 (15.9)	.08 (2.0)	.50 (12.7)	.19 (4.8)	1 - 1/8 (28.6)	
WHC-750-01	3/4 (19.1)	.08 (2.0)			1 - 9/32 (32.5)	
WHC-1000-01	1 (25.4)	.09 (2.3)			1 - 17/32 (38.9)	500 per Bag
WHC-1500-01	1 - 1/2 (38.1)	.10 (2.5)			2 - 1/8 (53.9)	
Part available in V-0 material by special order. To order, replace -01 with -19						

EXWHC
Extruded Wire Harness Clip






Features
- Locking mechanism ensures cable hold down


Material: PVC • Color: Off White					
Part No.	**Standard Pack: 1000**				
	"A" Holding Dia.	**"B"**	**"C"**	**"D"**	**"E" Ref.**
EXWHC-250*	.25 (6.35)	.07 (1.8)	.394 (10.0)	.188 (4.8)	.854 (21.7)
EXWHC-500	.50 (12.7)				1.18 (30.0)
EXWHC-750	.75 (19.0)		.50 (12.7)		1.34 (34.0)

*EXWHC-250 is produced with no latch feature

Downloaded from Arrow.com.

AKKL
Adjustable Kwik Klip






Features
- Locks securely and can be easily reopened for routing changes
- Adjustable to various diameters

Material: Nylon 6/6, RMS-01 or Flame Retardant Nylon, RMS-19; Adhesive Back, RMS-15* • Color: Natural								
Part No.				Standard Pack: 100 pieces				
Nylon w/o Tape	Nylon w/Tape	V-0 Nylon w/o Tape	V-0 Nylon w/Tape	Bundle Dia. Range Ref.	"A" ± .015 (0.4)	"B" ± .015 (0.4)	"C" Ref.	"D"
AKKL-2140-01	AKKL-2140-A-RT*	AKKL-2140-19	AKKL-2140-A-RT-19*	.215-.258 (5.5-6.5)	.87 (22.0)	.669 (17.0)	.708 (18.0)	.39 (10.0)
AKKL-3140-01	AKKL-3140-A-RT	AKKL-3140-19	AKKL-3140-A-RT-19	.312-.406 (7.9-10.3)	1.0 (25.4)	.750 (19.1)	.866 (22.0)	.40 (10.2)
AKKL-4756-01	AKKL-4756-A-RT	AKKL-4756-19	AKKL-4756-A-RT-19	.469-.562 (11.9-14.3)	1.25 (31.8)		1.09 (27.7)	
AKKL-5775-01	AKKL-5775-A-RT	AKKL-5775-19	AKKL-5775-A-RT-19	.578-.750 (14.7-19.1)	1.50 (38.1)		1.25 (31.8)	.50 (12.7)
AKKL-8710-01	AKKL-8710-A-RT	AKKL-8710-19	AKKL-8710-A-RT-19	.875-1.00 (22.2-25.4)	2.0 (50.8)	1.0 (25.4)	1.75 (44.5)	

PAKKL
Plug In Adjustable Kwik Klip






Features
- Locks securely and can be easily reopened for routing changes
- Adjustable to various diameters


Material: Nylon 6/6, RMS-01 or Flame Retardant Nylon, RMS-19 • Color: Natural	
Part No.	Standard Pack: 100 per bag
	Material
PAKKL-5775-01	Nylon 6/6 (RMS-01)
PAKKL-5775-19	Nylon 6/6 (RMS-19)

Downloaded from Arrow.com.

ACCESSORIES

KKU
Kwik Klip Type "U"







Features

- 1/4" diameter holding clip is excellent for routing the 1/4" (6.35mm) diameter Bend Limiting Tubing found on page 26

Material: PVC, RMS-04 • Adhesive Back, 1/16" (1.59mm) thick, RMS-15 • Color: Gray					
Part No.	Holding Capacity "A"	"B" ±.015 (0.4)	"C" ±.02 (0.5)	"D" At Max Capacity Ref.	Standard Pack
KKU-2-RT	1/8 (3.2)	3/4 (19.1)	3/4 (19.1)	9/32 (7.1)	500
KKU-4-RT	1/4 (6.4)			15/32 (11.9)	
KKU-6-RT	3/8 (9.5)			19/32 (15.1)	
KKU-8-RT	1/2 (12.7)	1 (25.4)	1 (25.4)	11/16 (17.5)	100
KKU-9-RT	9/16 (14.3)			3/4 (19.1)	
KKU-12-RT	3/4 (19.1)			29/32 (23.0)	
Also available in clear PVC, RMS-32 by special order. Custom lengths available by special order.					


MKKJ
Micro Kwik Klip Type "J"






Material: Rigid PVC, RMS-32 • Adhesive Back, 1/32" (.8mm) thick, RMS-15 • Color: Clear				
Part No.	Standard Pack: 1000 per bag			
	Holding Capacity "A"	"B" ±.015 (0.4)	"C" ±.02 (0.5)	"D" At Max Capacity Ref.
MKKJ-2-RT	1/8 (3.2)	7/16 (11.1)	3/8 (9.5)	15/64 (6.0)
MKKJ-3-RT	3/16 (4.8)	5/8 (15.9)	7/16 (11.1)	21/64 (8.3)
MKKJ-4-RT	1/4 (6.4)	21/32 (16.7)	1/2 (12.7)	13/32 (10.3)
MKKJ-5-RT	5/16 (7.9)	13/16 (20.6)	9/16 (14.3)	31/64 (12.3)
MKKJ-6-RT	3/8 (9.5)	7/8 (22.2)	5/8 (15.9)	9/64 (14.3)
Custom lengths available by special order.				

NGS/PGS/SNGS/SPGS
Continous Grommet Strip






Features

- Insulates wires from chafing
- Can be used for round, square and rectangular shapes

Color: Natural or Black; Add B for black.							
Solid Lengths Part No.	Serrated Lengths Part No.	Standard Pack: 100 ft. (3048 cm) Rolls; custom lengths available by special order					
		"A" Ref	"B" Ref	"C" Ref	"Gap" Ref	Material	Panel Thickness Range
NGS-1	SNGS-1	.125 (3.2)	.031 (0.8)	.031 (0.8)	.018 (0.5)	Nylon (RMS-21)	UP TO .036 (0.9)
NGS-2	SNGS-2	.172 (4.4)		.109 (2.8)	.037 (0.9)		.037 (0.9) - .071 (1.8)
NGS-2.5	SNGS-2.5				.060 (1.5)		.072 (1.8) - .105 (2.7)
NGS-3	SNGS-3	.188 (4.8)	.047 (1.2)	.156 (4.0)	.106 (2.7)		.106 (2.7) - .164 (4.2)
NGS-4	SNGS-4			.188 (4.8)	.165 (4.2)		.165 (4.2) - .187 (4.7)
NGS-5	SNGS-5			.250 (6.4)	.187 (4.7)		.188 (4.8) - .250 (6.4)
PGS-1	SPGS-1	.125 (3.2)	.031 (0.8)	.031 (0.8)	.018 (0.5)	Polyethylene (RMS-06)	UP TO .036 (0.9)
PGS-2	SPGS-2	.172 (4.4)		.109 (2.8)	.037 (0.9)		.037 (0.9) - .071 (1.8)
PGS-2.5	SPGS-2.5				.060 (1.5)		.072 (1.8) - .105 (2.7)
PGS-3	SPGS-3	.188 (4.8)	.047 (1.2)	.156 (4.0)	.106 (2.7)		.106 (2.7) - .164 (4.2)
PGS-4	SPGS-4			.188 (4.8)	.165 (4.2)		.165 (4.2) - .187 (4.7)
PGS-5	SPGS-5			.250 (6.4)	.187 (4.7)		.188 (4.8) - .250 (6.4)

Downloaded from Arrow.com.

MCCG
Metal Continuous Cushioned Grommet



Material: 300 Series Stainless Steel with Fusion Bonded Nylon 11 Coating and a 46 Durometer, Shore D Cushion		
100 ft Reel Color: Black	**"W"**	**"T" Application Thickness**
MCCG-1N	.19 (4.8)	.025 (0.64) - .036 (0.91)
MCCG-2N		.037 (0.93) - .055 (1.40)
MCCG-3N		.056 (1.42) - .074 (1.90)
MCCG-4N	.22 (5.6)	.075 (1.91) - .093 (2.36)
MCCG-6N		.113 (2.87) - .134 (3.40)
***Extra flexible grommet is available by special order.**		



NOTE:
Hand held cutting tool needed, order part number MCGS-1

Features:

Heat Continuous:
185 degrees F (85 degrees C)


Salt Spray:
2000 hours per MIL-STD-202D Method: 101D


Dielectric:
1200 volts @ 60Hz per MIL-STD-202; Method 301.


Shock and Vibration:
MIL-STD-1344, Method 2005 Test Condition VI Letter J. Duration: 8 hours in the longitudinal and 8 hours in the perpendicular direction. Shock: Overall RMS: G41.7


Flammability: UL 94-V0


Applications



Cushion



Outside Right Angles



U-Shape (Mouse Hole)


Grounding Clip (EMI/RFI) Uncoated part only



Continous Straight Edge


Inside Right Angles



Irregular Holes


Flexible Grommet*

NGSG/SNGSG/PGSG/ SPGSG
Grommet Strip w/Adhesive



Color: Natural or Black; Add B for black.							
Part No.		**Standard Pack: 100 ft. (3048 cm) Rolls; custom lengths available by special order**					
Solid Lengths	**Serrated Lengths**	**Material**	**"A" Ref.**	**"B" Ref.**	**"C" Ref.**	**Panel Thickness Range**	**GAP Ref.**
NGSG-2	SNGSG-2	Nylon, RMS-21	.172 (4.4)	.031 (0.8)	.109 (2.8)	.037 (0.9) - .071 (1.8)	.048 (1.2)
NGSG-2.5	SNGSG-2.5					.072 (1.8) - .105 (2.7)	.060 (1.5)
NGSG-3	SNGSG-3		.188 (4.8)	.047 (1.2)	.156 (4.0)	.106 (2.7) - .164 (4.2)	.106 (2.7)
PGSG-2	SPGSG-2	Polyethylene, RMS-06	.172 (4.4)	.031 (0.8)	.109 (2.8)	.037 (0.9) - .071 (1.8)	.048 (1.2)
PGSG-6*	SPGSG-6*		.160 (4.1)	.025 (0.6)	.060 (1.5)		
PGSG-2.5	SPGSG-2.5		.172 (4.4)	.031 (0.8)	.109 (2.8)	.072 (1.8) - .105 (2.7)	.060 (1.5)
PGSG-7*	SPGSG-7*		.188 (4.8)	.035 (0.9)	.100 (2.5)		
PGSG-3	SPGSG-3			.047 (1.2)	.156 (4.0)	.106 (2.7) - .164 (4.2)	.106 (2.7)
PGSG-8*	SPGSG-8*			.035 (0.9)	.156 (4.0)		
***Part No. -6, -7 & -8 are extra flexible**							



Features

- Adhesive provides self retaining grip

Downloaded from Arrow.com.

ACCESSORIES

SHR
Slit Harness Wrap


• UL #E208749





Features

- Easy to use. Simply feed the wires into the tools, feed the wrap over the horn and zip
- Allows easy breakout of wires
- Provides abrasion protection




Material: See Chart • Color: See Chart


Part No.	A Ref.	Max. Bundle Dia.	B Ref.	C Ref.	Standard Lengths	Material / Color	Installation Tool Part No.	Installation Tool Material
SHR-08-6NB	.31 (8.0)	.39 (10.0)	.032 (0.8)	.39 (10.0)	100m (328 ft)	Nylon (RMS-88) / Black	CAT-08-PP	Polypropylene
SHR-15-6NB	.59 (15.0)	.63 (16.0)	.032 (0.8)	.55 (14.0)	50m (164 ft)		CAT-15-PP	
SHR-20-6NB	.79 (20.0)	.90 (23.0)	.035 (0.9)	.67 (17.0)	30m (98 ft)		CAT-20-PP	
SHR-25-6NB	.98 (25.0)	.98 (25.0)	.039 (1.0)	.79 (20.0)	20m (65 ft)		CAT-25-PP	
SHR-32-6NB	1.25 (32)	1.25 (32)	.050 (1.3)	.98 (24.9)	15m (49 ft)		CAT-32-PP	
SHR-08-6V0B	.31 (8.0)	.39 (10.0)	.032 (0.8)	.39 (10.0)	100m (328 ft)	Flame Retardant Nylon (RMS-95) / Black	CAT-08-PP	
SHR-15-6V0B	.59 (15.0)	.63 (16.0)	.032 (0.8)	.55 (14.0)	50m (164 ft)		CAT-15-PP	
SHR-20-6V0B	.79 (20.0)	.90 (23.0)	.035 (0.9)	.67 (17.0)	30m (98 ft)		CAT-20-PP	
SHR-25-6V0B	.98 (25.0)	.98 (25.0)	.039 (1.0)	.79 (20.0)	20m (65 ft)		CAT-25-PP	
SHR-32-6V0B	1.25 (32)	1.25 (32)	.050 (1.3)	.98 (24.9)	15m (49 ft)		CAT-32-PP	
SHR-08-PPB	.31 (8.0)	.39 (10.0)	.032 (0.8)	.39 (10.0)	100m (328 ft)	Polypropylene (RMS-94) / Black	CAT-08-PP	
SHR-15-PPB	.59 (15.0)	.63 (16.0)	.032 (0.8)	.55 (14.0)	50m (164 ft)		CAT-15-PP	
SHR-20-PPB	.79 (20.0)	.90 (23.0)	.035 (0.9)	.67 (17.0)	30m (98 ft)		CAT-20-PP	
SHR-25-PPB	.98 (25.0)	.98 (25.0)	.039 (1.0)	.79 (20.0)	20m (65 ft)		CAT-25-PP	
SHR-32-PPB	1.25 (32)	1.25 (32)	.050 (1.3)	.98 (24.9)	15m (49 ft)		CAT-32-PP	


Available in various colors by special order.
Tool available in bulk packages of 100 / box. To order add -BU to the end of the part number.
Tool for sizes -20, -25 and -32 available in glass filled nylon for frequent use. To order, replace -PP with -IX


CAT Installation Tool



Sample kits are available that include the -08 size of the wrap with the CAT tool. They are available free from the Richco Sample Department.







Note:

- To use the SHR, insert cables into the CAT tool. Rotate the tool shut, locking in the cables. Slide the tubing over the horn and zip the tool along the cables locking them in.

Material: Polypropylene • Color: Orange

Part No.	Standard Pack: 10		
	"A" Ref	Max. Bundle Dia. "B"	To be used with
CAT-08-PP	2.80 (71.0)	.37 (9.5)	SHR-08-YYY*
CAT-15-PP	3.19 (81.0)	.63 (16.0)	SHR-15-YYY*
CAT-20-PP	3.94 (100.0)	.79 (20.0)	SHR-20-YYY*
CAT-25-PP	4.45 (113.0)	.96 (24.5)	SHR-25-YYY*
CAT-32-PP	5.67 (144.0)	1.22 (31.0)	SHR-32-YYY*

*YYY-SHR material


Downloaded from Arrow.com.


RX
Richflex Flexible Channel


Features


- Available with or without adhesive

Material: Polypropylene • Color: Grey				
Part No.	Ext. Dim. "A" x "A" in (mm)	Type	Int. Section in2 (mm2)	Standard Packing (pcs)
RX1313-0	.492 x .492 (12.5 x 12.5)	VMHDY40	.171 (110)	112
RX1313-4		AMHD40		
RX1616-0	.630 x .630 (16 x 16)	VMHDY40	.287 (185)	84
RX1616-4		AMHD40		
RX2020-0	.787 x .787 (20 x 20)	VMHDY40	.496 (320)	112
RX2020-4		AMHD40		
RX2525-0	.984 x .984 (25 x 25)	VMHDY40	.775 (500)	70
RX2525-4		AMHD40		
RX3030-0	1.181 x 1.181 (30 x 30)	VMHDY40	1.116 (720)	50
RX3030-4		AMHD40		
RX4040-0	1.575 x 1.575 (40 x 40)	VMHDY40	2.046 (1320)	50
RX4040-4		AMHD40		
RX5050-0	1.969 x 1.969 (50 x 50)	VMHDY40	3.162 (2040)	32
RX5050-4		AMHD40		
Part Type Code: A - Adhesive Backing; D - UL94V2; H - Halogen Presence Insignificant (<70%); M - Polypropylene; V - Screw Mount; 40 - Gray RAL7040.				












SRWD-OPEN SLOT



Mounting Style #1



SRWDN-NARROW SLOT



Mounting Style #2

Material: PVC (UL #E161178) (CSA #LR40012-7) • Color: Gray				
Part No.	"A"	"B"	Standard Pack	Mounting Style
SRWDN-0820	.75 (19.1)	2.0 (50.8)	78' (1981.2)	1
SRWDN-1015	1.0 (25.4)	1.5 (38.1)		
SRWDN-1020		2.0 (50.8)		
SRWDN-1030		3.0 (76.2)	52' (1320.8)	
SRWDN-1515	1.5 (38.1)	1.5 (38.1)	78' (1981.2)	
SRWDN-1520		2.0 (50.8)	52' (1320.8)	
SRWDN-1530		3.0 (76.2)		
SRWDN-2015	2.0 (50.8)	1.5 (38.1)		
SRWDN-2020		2.0 (50.8)		
SRWDN-2030		3.0 (76.2)		
SRWDN-3015	3.0 (76.2)	1.5 (38.1)		2
SRWDN-3020		2.0 (50.8)		
SRWDN-3030		3.0 (76.2)		
SRWDN-4020	4.0 (101.6)	2.0 (50.8)	26' (660.4)	
SRWDN-4030		3.0 (76.2)		
Parts also available in White, Black and Blue by special order. To order, add suffix W for White, BL for Blue, and B for Black				

SRWD/SRWDN
Slotted Richco Wiring Duct

Features

- Holds breakout wires while providing flexibility for adding or removing wires later
- Simply deflect the plastic fingers to insert or remove wires
- Non-slip cover is easy to use and included with base
- Parts are 6-1/2' (1.98m) long
- Material is serviceable from -40°F – 140°F (-40°C – 60°C)
- Fingers are scored for easy break out



Material: PVC (UL #E161178) (CSA #LR40012-7) • Color: Gray				
Part No.	"A"	"B"	Standard Pack	Mounting Style
SRWD-0820	.75 (19.1)	2.0 (50.8)	78' (1981.2)	1
SRWD-1015	1.0 (25.4)	1.5 (38.1)		
SRWD-1020		2.0 (50.8)		
SRWD-1030		3.0 (76.2)	52' (1320.8)	
SRWD-1040		4.0 (101.6)		
SRWD-1515	1.5 (38.1)	1.5 (38.1)	78' (1981.2)	
SRWD-1520		2.0 (50.8)	52' (1320.8)	
SRWD-1530		3.0 (76.2)		
SRWD-1540		4.0 (101.6)		
SRWD-2010	2.0 (50.8)	1.0 (25.4)	78' (1981.2)	
SRWD-2015		1.5 (38.1)	52' (1320.8)	
SRWD-2020		2.0 (50.8)		
SRWD-2030		3.0 (76.2)		
SRWD-2040		4.0 (101.6)	26' (660.4)	
SRWD-3015	3.0 (76.2)	1.5 (38.1)	52' (1320.8)	2
SRWD-3020		2.0 (50.8)		
SRWD-3030		3.0 (76.2)		
SRWD-3040		4.0 (101.6)	26' (660.4)	
SRWD-4020	4.0 (101.6)	2.0 (50.8)		
SRWD-4030		3.0 (76.2)		
SRWD-4040		4.0 (101.6)		
SRWD-4050		5.0 (127.0)		
Parts also available in White, Black and Blue by special order. To order, add suffix W for White, BL for Blue, and B for Black				

Downloaded from Arrow.com.