




Part Number : [734154670](#)

Product Description : SSMCX Jack, Straight, PCB Receptacle, Edge Mount, Brass Body, Gold (Au) Plated, Tray, 50 Ohms

Series Number : 73413

Status : Active

Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

[734154670 sd.pdf](#)

[895420040-000.pdf](#)

3D Models and Design Files


[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73413
Description	SSMCX Jack, Straight, PCB Receptacle, Edge Mount, Brass Body, Gold (Au) Plated, Tray, 50 Ohms
Product Name	SSMCX
Style	PCB
Type	Ultra-microminiature
UPC	822348896912

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 170 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	0.257/g
Orientation	Straight
Packaging Type	Tray

Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Edge Mount
PCB Thickness - Recommended	N/A
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	2
Max-Temp	260

This document was generated on May 21, 2026