



## TP1438, Vinyl Ring Terminal For 16 - 14 AWG

By Burndy  
Catalog # [TP1438](#)

Vinyl Ring Terminal For 16 - 14 AWG



## Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serrations in the inner barrel provides added holding strength and better conductivity

## Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

## Specifications

|  |                      |
|--|----------------------|
| Buy American Compliant Certification - cULus | Contact Manufacturer |
| EU RoHS Indicator                            | No                   |
| Certification - UL Recognized                | Yes                  |
| Industry Standard(s)                         | No                   |
| Certification - ETL                          | UL467                |
| Standards - Industry Standards Met           | UL486                |
| Standards - RoHS Compliance Status           | CM                   |
| Certification - CSA Approved                 | Yes                  |
| UL Listed                                    | Yes                  |

## Conductor

|                 |   |
|-----------------|---|
| Conductor Size  | 16 - 14 AWG   |
| Conductor Type  | <ul style="list-style-type: none"><li>CU C Solid-Size</li><li>CU C Str-Size</li></ul> |
| Conductor Range | #16 AWG to #14 AWG  |

## Configuration

|                                      |               |
|--------------------------------------|---------------|
| Physical Attribute - Number of Holes | 1             |
| Connector Type                       | Ring Terminal |

## Current

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

## Dimensions

|                                    |           |
|------------------------------------|-----------|
| Package Length                     | 0.000 in  |
| Package Width                      | 0.000 in  |
| Package Weight                     | 0.000 lb. |
| Dimension - L Length Overall mm    | 31 mm     |
| Dimension - Pad Width inch         | 0.53 in   |
| Package Height                     | 0.000 in  |
| Dimension - Hole Size fraction     | 2/5       |
| Dimension - Hole Size inch         | 0.40 in   |
| Dimension - Strip Length inch      | 13/64 in  |
| Dimension - Stud Size inch         | 3/8 in    |
| Dimension - B Length fraction      | 13/50 in  |
| Dimension - B Length inch          | 0.26 in   |
| Dimension - Z inch                 | 0.45 in   |
| Dimension - Bolt Size fraction     | 3/8       |
| Cable Insulation Diameter Maximum  | 0.190 in  |
| Dimension - Length Overall inch    | 1.21 in   |
| Dimension - Diameter Max Size inch | 0.19 in   |

## General

|                                  |                |
|----------------------------------|----------------|
| Insulation Type                  | Vinyl          |
| Trade Name                       | VINYLUG™       |
| Insulation                       | Y              |
| Sub Brand                        | VINYLUG        |
| Color Code                       | Blue           |
| Physical Attribute - Tongue Type | Ring           |
| Plated                           | Y              |
| Feature - Barrel Style           | Shrouded       |
| Type                             | Ring Tongue    |
| UPC 12 Digit                     | 781810085530   |
| UPC 14 Digit GTIN                | 00781810085530 |
| Material                         | Copper         |
| Plating Type                     | Tin            |
| UPC                              | 781810085530   |

## Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 100   |
| Carton Quantity       | 1200  |
| Pallet Quantity       | 99999 |

## Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved  
BRDY-TP1438-SPEC-EN | REV 4/2026