





features

- Designed to reduce noise at high frequencies
- Standard EIA packages: 1J, 2A, 2B
- Nickel barrier with solder overcoat for excellent solderability
- Magnetically shielded
- Marking: Black body color with no marking
- Products with lead-free terminations meet EU RoHS requirements

dimensions and construction



Type (Inch Size Code)	Dimensions inches (mm)			
	L	W	t	d
1J (0603)	.063±.006 (1.6±0.15)	.031±.006 (0.8±0.15)	.031±.006 (0.8±0.15)	.014±.006 (0.36±0.15)
2A (0805)	.079±.008 (2.0±0.2)	.047±.008 (1.20±0.2)	.035±.008 (0.9±0.2)	.02±.012 (0.51±0.30)
2B (1206)	.126±.008 (3.2±0.2)	.063±.008 (1.6±0.2)	.043±.008 (1.1±0.2)	.02±.012 (0.51±0.30)

ordering information

New Part #	CZP	2A	F	T	TD	500	P
	Type	Size	Permeability Code	Termination Material	Packaging	Impedance	Tolerance
		1J 2A 2B	F P	T: Sn	TD: 7" paper tape (1J, 2A - 4,000 pieces/reel) TE: 7" embossed plastic (2B - 3,000 pieces/reel)	2 significant figures + 1 multiplier	P: ±25%

For further information on packaging, please refer to Appendix A.

applications and ratings

Part Designation	Impedance @ 100MHz (Ω)	DC Resistance Maximum (Ω)	Allowable DC Current Maximum (mA)	Operating Temperature Range
CZP1JFTTD300P	30	0.03	3000	-55°C to +125°C
CZP1JFTTD400P	40	0.04		
CZP1JFTTD600P	60			
CZP1JFTTD800P	80			
CZP1JFTTD121P	120	0.10	2000	
CZP1JFTTD181P	180			
CZP1JFTTD221P	220			
CZP1JFTTD301P	300	0.10	2000	
CZP1JFTTD501P	500	0.15	1500	
CZP1JFTTD601P	600	0.20	1000	
CZP2AFTTD300P	30	0.015	3000	-55°C to +125°C
CZP2AFTTD400P	40	0.03	2000	
CZP2AFTTD450P	45			
CZP2AFTTD500P	50	0.04	3000	
CZP2AFTTD600P	60	0.025		
CZP2AFTTD800P	80	0.04	2000	
CZP2AFTTD121P	120		3000	
CZP2AFTTD151P	150	0.05		
CZP2AFTTD221P	220			
CZP2AFTTD301P	300	0.15	1000	
CZP2AFTTD601P	600	0.20		
CZP2AFTTD102P	1000			
CZP2BFTTE190P	19	0.02	3000	-55°C to +125°C
CZP2BFTTE300P	30			
CZP2BFTTE500P	50	0.025		
CZP2BFTTE800P	80	0.03	2000	
CZP2BFTTE900P	90	0.10	1000	
CZP2BFTTE101P	100			
CZP2BFTTE121P	120			
CZP2BFTTE221P	220	0.08	2000	
CZP2BPTTE700P	70	0.20	3000	
CZP2BFTTE601P	600		1000	
CZP2BPTTE101P	100	0.03	3000	
CZP2BPTTE121P	120	0.04		
CZP2BPTTE601P	600	0.10	1500	

For complete environmental specifications, please refer to pages 256-257.