


SK2236


THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO POSITRONIC AND IT'S SUBSIDIARIES. POSITRONIC BELIEVES THE DATA ON THIS DRAWING TO BE RELIABLE, SINCE THE TECHNICAL INFORMATION IS GIVEN FREE OF CHARGE, THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.

DATE	REV	REVISION RECORD	APP	DR	CK
9-17-01	B	ECO 18311	RCW	YK	MZ
3-30-06	C	ECO 25732		ME	









CONTACT HOLE PATTERN

NOTES:
1. MATERIALS AND FINISHES:
   INSULATOR: GLASS FILLED POLYESTER, UL 94V-0, COLOR BLUE.
   CONTACTS: PRECISION MACHINED COPPER ALLOY, GOLD FLASH OVER NICKEL PLATE.
   MOUNTING BRACKET: BRASS WITH TIN PLATE.
   PUSH-ON FASTENERS: SPRING TEMPERED COPPER ALLOY, TIN PLATE.
2. ELECTRICAL CHARACTERISTICS:
   CONTACT CURRENT RATING: 21 AMPS. PER UL 1977.
   INITIAL CONTACT RESISTANCE: 0.0016 OHMS MAX. PER IEC 512-2, TEST 2b.
   INSULATOR RESISTANCE: 5 G OHMS PER IEC 512-2, TEST 3a, METHOD A.
   WORKING VOLTAGE: 600 VAC.
3. WORKING TEMPERATURE: -55°C TO +125°C.
4. DIMENSIONS ARE IN INCHES [MILLIMETERS].

POSITRONIC INDUSTRIES INC.
www.connectpositronic.com
FSCM 28198

DECIMAL TOL. ± 0.015 [0.38]	PCS SERIES	SCALE N.T.S.	DRAWN BY Y. KELLEYBREW
			APPROVED BY RCW
	TITLE PLB16M4BN0A1		
ANGULAR TOL. ± 5°	DATE 9-17-01	DRAWING NUMBER SK2236	REV. C

Downloaded from Arrow.com.