

UL1363a, Paragraph 14.1(d) States "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.

Safe-IT UL 1363A Medical-Grade Power Strip for Patient-Care Vicinity, 6x 20A Hospital-Grade Outlets, Safety Covers, 7 ft. Cord

MODEL NUMBER: **PS607HG20AOEM**



Supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations in operating rooms and patient-care vicinities.

Description

The PS607HG20AOEM Medical-Grade Power Strip supplies power to movable plug-connected components mounted to a rack, table or pedestal in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V, 50/60 Hz power strip features a NEMA 5-20P-HG hospital-grade plug and six NEMA 5-20R-HG hospital-grade outlets. Integrated locking safety covers protect unused outlets from debris and damage and prevent unauthorized connections.

The power strip is protected by a antimicrobial powder coating. Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Two built-in resettable 20A circuit breakers control power to all outlets and protect the power strip against overloads. The switchless design prevents the power strip from being accidentally shut off. The seven-foot (2.1-meter) power cord provides ample reach to the AC power source.

Mounting tabs and flanges let you install the PS607HG20AOEM on a wide variety of surfaces, such as IV poles, mobile carts, crash carts and mobile medical workstations. The all-metal housing ensures safety and is guaranteed to last a long time in demanding environments.

Features

Power Distribution Anywhere in Any Medical Facility Ideal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. For use on IV poles, mobile carts, crash carts and mobile workstations, when properly mounted. 120V, 50/60 Hz power strip complies with UL 1363A specifications.

Exclusive Antimicrobial Protection Antimicrobial coating helps resist the growth of bacteria, viruses, fungi, mold and mildew. Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Versatile Medical-Grade Solution 6 NEMA 5-20R-HG hospital-grade outlets provide consistent power.

Highlights

- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Approved for use in patient-care vicinities when properly mounted
- Complies with UL 1363A & NFPA 99 specifications
- 6 NEMA 5-20R-HG outlets with integrated locking safety covers
- 7 ft. (2.1 m) cord with NEMA 5-20P-HG plug reaches nearby outlets

Package Includes

- PS607HG20AOEM UL 1363A Medical-Grade Power Strip, 7-ft. (2.13 m) cord
- Owner's manual

ft. (2.1 m) power cord with NEMA 5-20P-HG hospital-grade plug provides ample reach to the power source
Rugged, all-metal housing for long life in demanding environments

Premium Safety Features Integrated locking outlet safety covers block access to unused outlets Dual resettable built-in 20A circuit breakers protect against dangerous overloads Switchless design prevents accidental shutoff

Ready to Use Right Out of the Box Built-in mounting tabs and flanges for easy installation on a variety of surfaces

Specifications

| OVERVIEW | |
|------------------------------------|--|
| UPC Code | 037332203656 |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 20A 120V |
| Input Plug Features | Hospital Grade Plug |
| Input Cord Gauge Type | 12 gauge; SJT |
| Voltage Compatibility (VAC) | 120 |
| Input Plug Type | NEMA 5-20P-HG |
| Input Cord Length (ft.) | 7 |
| Right-Angle Plug | No |
| Input Cord Length (m) | 2.13 |
| Integrated Cord Clip | No |
| OUTPUT | |
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (6) 5-20R-HG |
| Circuit Breaker (amps) | 20 |
| Overload Protection | 2 x 20amp breakers (1 line, 1 neutral) |
| Transformer Accommodation | (2) Yes |
| Outlet Orientation | Single row of 6 |
| Right-Angle Outlets | No |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | No power switch |
| PHYSICAL | |

| | |
|--|---|
| Color | White |
| Material of Construction | Metal |
| Power Cord Color | White |
| Form Factors Supported | IV poles, mobile carts, crash carts and mobile medical workstations |
| Housing Color | White |
| Included Mounting Accessories | Mounting tabs and flanges |
| Mounting Holes or Slots | Yes |
| Outlets Measurement (Center to Center) | 1.52 in. |
| Receptacle Color | White |
| Shipping Dimensions (hwd / in.) | 2.10 x 5.80 x 14.40 |
| Shipping Dimensions (hwd / cm) | 5.33 x 14.73 x 36.58 |
| Shipping Weight (lbs.) | 3.20 |
| Shipping Weight (kg) | 1.45 |
| Unit Dimensions (hwd / in.) | 1.500 x 13.750 x 2.500 |
| Unit Dimensions (hwd / cm) | 34.93 x 6.35 x 3.81 |
| Unit Weight (lbs.) | 4.00 |
| Unit Weight (kg) | 1.81 |
| Mounting Details | Includes flanges |
| FEATURES & SPECIFICATIONS | |
| Rotatable Outlets | No |
| Antimicrobial | Yes |
| Built-In Circuit Breaker | Yes |
| Antibacterial | No |
| Built-in Cable Management | No |
| STANDARDS & COMPLIANCE | |
| Product Certifications | UL 1363A |
| Product Compliance | NFPA 99: 10.2.3.6; RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

TRIPP-LITE

by **EATON**

1000 Eaton Boulevard

Cleveland, OH 44122

United States

TRIPP-LITE

by **EATON**

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks

are the property of their respective owners.