

60×60×25 mm

San Ace 60L 9LG type



General Specifications

- Material Frame: Aluminum, Impeller: Plastic (Flammability: UL 94V-1)
- Expected life See the table below. (L10 life: 90% survival rate for continuous operation in free air at 60°C, rated voltage)
Expected life at 40°C is for reference only.
- Motor protection function Locked rotor burnout protection, Reverse polarity protection
For details, please refer to p. 599.
- Dielectric strength 50/60 Hz, 500 VAC, for 1 minute (between lead wire conductors and frame)
- Insulation resistance 10 MΩ or more with a 500 VDC megger (between lead wire conductors and frame)
- Sound pressure level (SPL) At 1 m away from the air inlet
- Storage temperature -30 to +70°C (Non-condensing)
- Lead wire ⊕Red ⊖Black Sensor Yellow Control Brown
- Mass 100 g

Specifications

The models listed below **have pulse sensors with PWM control function.**

Model no.	Rated voltage [V]	Operating voltage range [V]	PWM duty cycle* [%]	Rated current [A]	Rated input [W]	Rated speed [min ⁻¹]	Max. airflow [m³/min] [CFM]	Max. static pressure [Pa] [inchH ₂ O]	SPL [dB (A)]	Operating temperature [°C]	Expected life [h]
» 9LG0612P4S001	12	10.8 to 13.2	100	0.67	8.04	11000	1.4 49.4	300 1.204	53	-20 to +70	180000/60°C (215000/40°C)
» 9LG0612P4J001			20	0.06	0.72	2900	0.36 12.7	20.8 0.083	20		
» 9LG0612P4H001			100	0.39	4.68	8650	1.1 38.8	182 0.73	47		
» 9LG0612P4M001			20	0.03	0.36	1150	0.13 4.8	3.3 0.013	14		
» 9LG0612P4S001			100	0.17	2.04	6150	0.78 27.5	97 0.389	35		
» 9LG0612P4J001			20	0.03	0.36	1350	0.17 6.0	4.7 0.018	14		
» 9LG0612P4H001	24	21.6 to 26.4	100	0.09	1.08	4200	0.53 18.7	45 0.18	24		
» 9LG0612P4M001			20	0.03	0.36	900	0.11 3.8	2.0 0.008	14		
» 9LG0624P4S001			100	0.34	8.16	11000	1.4 49.4	300 1.204	53		
» 9LG0624P4J001			20	0.03	0.72	2900	0.36 12.7	20.8 0.083	20		
» 9LG0624P4H001			100	0.19	4.56	8650	1.1 38.8	182 0.73	47		
» 9LG0624P4M001			20	0.02	0.48	2200	0.28 9.8	12.0 0.048	17		
» 9LG0624P4S001	48	36 to 72	100	0.08	1.92	6150	0.78 27.5	97 0.389	35		
» 9LG0624P4J001			20	0.02	0.48	1300	0.16 5.6	4.3 0.017	14		
» 9LG0624P4H001			100	0.04	0.96	4200	0.53 18.7	45 0.18	24		
» 9LG0624P4M001			20	0.01	0.24	800	0.1 3.5	1.6 0.006	14		
» 9LG0648P4S001			100	0.18	8.64	11000	1.4 49.4	305 1.224	53		
» 9LG0648P4J001			20	0.02	0.96	2900	0.36 12.7	20.8 0.083	20		
» 9LG0648P4H001	48	36 to 72	100	0.1	4.8	8650	1.1 38.8	182 0.73	47		
» 9LG0648P4M001			20	0.02	0.96	2100	0.26 9.1	10.7 0.042	17		
» 9LG0648P4S001			100	0.06	2.88	6150	0.78 27.5	97 0.389	35		
» 9LG0648P4J001			20	0.02	0.96	1000	0.12 4.2	2.5 0.01	14		
» 9LG0648P4H001	48	36 to 72	100	0.04	1.92	4200	0.53 18.7	45 0.18	24		
» 9LG0648P4M001			20	0.02	0.96	650	0.08 2.8	1.0 0.004	14		

* PWM input frequency is 25 kHz; models without specifications at 0% PWM duty cycle have zero fan speed at 0%.


Note 1: Sensor and control options are available for selection. Refer to the table on p. 634.

Note 2: The » mark indicates Short Lead Time Service applicable models. See p. 654 for details.


Airflow - Static Pressure Characteristics / PWM Duty - Speed Characteristics Example

9LG0612P4S001 With pulse sensor with PWM control function


PWM duty cycle



Operating voltage range




PWM duty - Speed characteristics example




9LG0612P4J001 With pulse sensor with PWM control function


PWM duty cycle



Operating voltage range




PWM duty - Speed characteristics example




9LG0612P4H001 With pulse sensor with PWM control function


PWM duty cycle



Operating voltage range




PWM duty - Speed characteristics example




9LG0612P4M001 With pulse sensor with PWM control function


PWM duty cycle



Operating voltage range



PWM duty - Speed characteristics example




DC

Long Life Fan 60 mm sq.


Airflow - Static Pressure Characteristics / PWM Duty - Speed Characteristics Example

9LG0624P4S001 With pulse sensor with PWM control function


PWM duty cycle



Operating voltage range




PWM duty - Speed characteristics example




9LG0624P4J001 With pulse sensor with PWM control function


PWM duty cycle



Operating voltage range




PWM duty - Speed characteristics example




9LG0624P4H001 With pulse sensor with PWM control function


PWM duty cycle



Operating voltage range




PWM duty - Speed characteristics example




9LG0624P4M001 With pulse sensor with PWM control function


PWM duty cycle



Operating voltage range



PWM duty - Speed characteristics example




DC
Long Life Fan 60 mm sq.


Airflow - Static Pressure Characteristics / PWM Duty - Speed Characteristics Example

9LG0648P4S001 With pulse sensor with PWM control function


PWM duty cycle



Operating voltage range




PWM duty - Speed characteristics example




9LG0648P4J001 With pulse sensor with PWM control function


PWM duty cycle



Operating voltage range




PWM duty - Speed characteristics example




9LG0648P4H001 With pulse sensor with PWM control function


PWM duty cycle



Operating voltage range




PWM duty - Speed characteristics example




9LG0648P4M001 With pulse sensor with PWM control function


PWM duty cycle



Operating voltage range





PWM duty - Speed characteristics example



DC

Long Life Fan 60 mm sq.



Options			
Finger guards		page: p. 584	Resin finger guards
Model no.: 109-139E, 109-139H			page: p. 591
Model no.: 109-1003G			
Resin filter kits		page: p. 592	
Model no.: 109-1003F13 (13PPI), 109-1003F20 (20PPI), 109-1003F30 (30PPI), 109-1003F40 (40PPI)			