

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1554216004](#)
Status: **Active**
Overview: [Flamar Standard Cables for Industrial Automation](#)
Description: Flamar Ethernet 5e Network Cable, WSOR Jacket, Braided Shielding Overall, 8 Circuits, 4x(2x0.14mm²) / 4x(2x26 AWG), 7.20mm Diameter, 300.0m Length, Teal

Documents:
[Product Specification 1554216001-P1E \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable
Series	155421
Bending Radius - Minimum	> 15xOD
Color - Cable Jacket	Teal
Comments	3 reels of 100.0m each
Crimp Quality Equipment	Yes
Geographic Area	Global
Material - Outer Jacket	WSOR
Outer Jacket Diameter	7.20mm (.283")
Overview	Flamar Standard Cables for Industrial Automation
Product Literature Order No	987651-3992
Product Name	Flamar
Protocol	EtherNet 5e
UPC	889056464949
Physical	
Cable Length	300.0m
Circuits (Loaded)	8
Insulation	PE
Net Weight	0.010/g
Packaging Type	Reel
Temperature Range - Operating	-10°C to +60°C
Wire Size AWG	26
Wire Size mm²	0.14
Wire/Cable Type	UL AWM 21215 / CSA
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V
Material Info	
Engineering Number	3X100M
Reference - Drawing Numbers	
Product Specification	1554216001-P1E



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS **China RoHS**
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[155421](#) Series

Use With
Micro-Change® (M12) [130047](#) , [120100](#) , [130034](#) , [120071](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION