

6	5	4	3	2	1																																																																																																
APPROVED: _____			<table><tr><td>Rev</td><td>AWO #</td><td>Description</td><td>Date</td><td>Appr</td></tr><tr><td>-</td><td></td><td>RELEASED</td><td>4/13/06</td><td></td></tr><tr><td>A</td><td></td><td>PART REVISION</td><td>4/19/06</td><td></td></tr><tr><td>B</td><td></td><td>ADDED DIM.</td><td>3/18/15</td><td>AY/RT</td></tr><tr><td>C</td><td></td><td>UPDATE DRAWING</td><td>4/13/18</td><td>AY/MY</td></tr></table>			Rev	AWO #	Description	Date	Appr	-		RELEASED	4/13/06		A		PART REVISION	4/19/06		B		ADDED DIM.	3/18/15	AY/RT	C		UPDATE DRAWING	4/13/18	AY/MY																																																																							
Rev	AWO #	Description	Date	Appr																																																																																																	
-		RELEASED	4/13/06																																																																																																		
A		PART REVISION	4/19/06																																																																																																		
B		ADDED DIM.	3/18/15	AY/RT																																																																																																	
C		UPDATE DRAWING	4/13/18	AY/MY																																																																																																	
DATE: _____ TITLE: _____																																																																																																					
SPECIFICATIONS:			Positions: 2 thru 20																																																																																																		
Material:			A = .098 [2.50] x No. of Spaces																																																																																																		
Insulator: Nylon 66, rated UL 94V-0			B = .098 [2.50] x No. of Positions + .091 [2.30]																																																																																																		
Insulator color: Natural			C = .098 [2.50] x No. of Positions + .028 [0.70]																																																																																																		
Electrical:																																																																																																					
Rated Voltage: 250V AC/DC																																																																																																					
Rated Current: 3A AC/DC																																																																																																					
Contact Resistance: 20 mohms max.																																																																																																					
Insulation resistance: 1,000 Mohms min.																																																																																																					
Withstand voltage: 1000V AC for 1 minute.																																																																																																					
Temperature Rating:																																																																																																					
-25°C to +85°C																																																																																																					
Environmental:																																																																																																					
Lead free, RoHS compliant																																																																																																					
			<table><tr><td colspan="2">UNLESS OTHERWISE SPECIFIED</td><td colspan="2">ADAM TECH</td><td colspan="2">909 Rahway Avenue, Union, NJ 07083</td></tr><tr><td colspan="2">ALL DIMENSIONS ARE INCHES [MM]</td><td colspan="2">INTERCONNECTS</td><td colspan="2">Phone: 908-687-5000</td></tr><tr><td colspan="2">TOLERANCES: EXCEPT AS NOTED</td><td colspan="2"></td><td colspan="2">Fax: 908-687-5710</td></tr><tr><td colspan="2">INCHES</td><td colspan="2">HOLES</td><td colspan="2"></td></tr><tr><td>.X ± .10</td><td>Ø.X ± .10</td><td colspan="2"></td><td colspan="2"></td></tr><tr><td>.XX ± .020</td><td>Ø.XX ± .015</td><td colspan="2"></td><td colspan="2"></td></tr><tr><td>.XXX ± .015</td><td>Ø.XXX ± .010</td><td colspan="2"></td><td colspan="2"></td></tr><tr><td colspan="2">APPROVALS</td><td colspan="2">DATE</td><td colspan="2">TITLE</td></tr><tr><td>DRAWN</td><td>LFJ</td><td colspan="2">4/13/06</td><td colspan="2">WIRE TO BOARD PITCH: 2.5MM</td></tr><tr><td>CHECKED</td><td></td><td colspan="2"></td><td colspan="2">CRIMP HOUSING STRAIGHT TYPE</td></tr><tr><td>APPROVED</td><td></td><td colspan="2"></td><td colspan="2">SIZE X</td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2">PART NO. 25CH-B-XX</td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2">REV. C</td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2">REF: S00124T</td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2">SCALE: NTS</td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2">SHEET 1 OF 1</td></tr></table>			UNLESS OTHERWISE SPECIFIED		ADAM TECH		909 Rahway Avenue, Union, NJ 07083		ALL DIMENSIONS ARE INCHES [MM]		INTERCONNECTS		Phone: 908-687-5000		TOLERANCES: EXCEPT AS NOTED				Fax: 908-687-5710		INCHES		HOLES				.X ± .10	Ø.X ± .10					.XX ± .020	Ø.XX ± .015					.XXX ± .015	Ø.XXX ± .010					APPROVALS		DATE		TITLE		DRAWN	LFJ	4/13/06		WIRE TO BOARD PITCH: 2.5MM		CHECKED				CRIMP HOUSING STRAIGHT TYPE		APPROVED				SIZE X						PART NO. 25CH-B-XX						REV. C						REF: S00124T						SCALE: NTS						SHEET 1 OF 1	
UNLESS OTHERWISE SPECIFIED		ADAM TECH		909 Rahway Avenue, Union, NJ 07083																																																																																																	
ALL DIMENSIONS ARE INCHES [MM]		INTERCONNECTS		Phone: 908-687-5000																																																																																																	
TOLERANCES: EXCEPT AS NOTED				Fax: 908-687-5710																																																																																																	
INCHES		HOLES																																																																																																			
.X ± .10	Ø.X ± .10																																																																																																				
.XX ± .020	Ø.XX ± .015																																																																																																				
.XXX ± .015	Ø.XXX ± .010																																																																																																				
APPROVALS		DATE		TITLE																																																																																																	
DRAWN	LFJ	4/13/06		WIRE TO BOARD PITCH: 2.5MM																																																																																																	
CHECKED				CRIMP HOUSING STRAIGHT TYPE																																																																																																	
APPROVED				SIZE X																																																																																																	
				PART NO. 25CH-B-XX																																																																																																	
				REV. C																																																																																																	
				REF: S00124T																																																																																																	
				SCALE: NTS																																																																																																	
				SHEET 1 OF 1																																																																																																	
5	4	3	2	1																																																																																																	