


- Compact open frame power supply with pin connectors
- Universal input range 90 to 264 VAC
- Convection cooled (no-fan)
- Operating temperature range: -20°C to +70°C
- Internal EN55032 class B filter
- Short circuit, overvoltage and overload protection
- IEC/EN/UL 62368-1 safety approvals
- Compliance to EN 61000-3-2
- 3-year product warranty



The TXO 120 is a compact 120 Watt AC/DC open frame module with reinforced I/O isolation designed for a wide range of cost sensitive applications. Excellent temperature behaviour allows the TXO 120 to deliver 100 Watt up to +50°C with convection cooling and 120 Watt up to +50°C with forced air cooling, while going up to +70°C with derating. The TXO 120 series features short circuit protection, over current limitation and overvoltage protection and complies with European EMC standards and the Low Voltage Directive (LVD).

Models					
Order Code	Output Power max.	Output Voltage nom.	Output Current max. (Forced air cooling)	Output Current max. (Natural convection)	Efficiency typ.
TXO 120-112-J	120 W	12 VDC	10'000 mA	8'330 mA	92 %
TXO 120-115-J		15 VDC	8'000 mA	6'660 mA	92 %
TXO 120-124-J		24 VDC	5'000 mA	4'160 mA	92 %
TXO 120-148-J		48 VDC	2'500 mA	2'080 mA	92 %

Options	
TCI 130-DC	- Optional Cable: www.tracopower.com/overview/tci130-dc
TCI-AC1	- Optional Cable: www.tracopower.com/overview/tci-ac1
on demand (backorder with MOQ non stocking item)	- Optional model with 36 VDC and 3'330 mA - Optional model with 56 VDC and 2'140 mA

Note - Total output power must not exceed 100 W for convection cooling applications

Input Specifications

Input Voltage	Operational Range: 90 - 264 VAC (Full Range) Rated Range: 100 - 240 VAC (Full Range)
Input Frequency	Operational Range: 47 - 63 Hz Certified: 50/60 Hz
Power Consumption	- No load & Vin = 230 VAC - No load & Vin = 115 VAC 150 mW max. 150 mW max.
Input Current	- Full load & Vin = 230 VAC - Full load & Vin = 115 VAC 650 mA max. 1'200 mA max.
Input Inrush Current	- At 230 VAC - At 115 VAC 100 A max. 60 A max.
Power Factor	- At 230 VAC - At 115 VAC 0.9 min. (Active Power Factor Correction) 0.95 min. (Active Power Factor Correction)
Input Protection	T 3.15 A / 250 VAC (Internal Fuse in L)
Recommended Input Fuse	3'150 mA (slow blow) (The need of an external fuse has to be assessed in the final application.)

Output Specifications

Voltage Set Accuracy	±2% max.
Regulation	- Input Variation (Vmin - Vmax) - Load Variation (10 - 100%) 0.5% max. 3% max.
Ripple and Noise (20 MHz Bandwidth)	12 VDC model: 150 mVp-p typ. (w/ 10 µF Alu 0.1 µF MLCC) 15 VDC model: 150 mVp-p typ. (w/ 10 µF Alu 0.1 µF MLCC) 24 VDC model: 240 mVp-p typ. (w/ 10 µF Alu 0.1 µF MLCC) 36 VDC model: 360 mVp-p typ. (w/ 10 µF Alu 0.1 µF MLCC) 48 VDC model: 480 mVp-p typ. (w/ 10 µF Alu 0.1 µF MLCC) 56 VDC model: 560 mVp-p typ. (w/ 10 µF Alu 0.1 µF MLCC)
Capacitive Load	12 VDC model: 10'000 µF max. 15 VDC model: 8'000 µF max. 24 VDC model: 5'000 µF max. 36 VDC model: 3'300 µF max. 48 VDC model: 2'500 µF max. 56 VDC model: 2'200 µF max.
Minimum Load	Not required
Temperature Coefficient	±0.05 %/K max.
Hold-up Time	- At 230 VAC - At 115 VAC 16 ms min. 16 ms min.
Start-up Time	- At 230 VAC - At 115 VAC 2 s max. 2 s max.
Short Circuit Protection	Continuous, Automatic recovery
Output Current Limitation	110 - 170% of Iout max.
Overvoltage Protection	110 - 160% of Vout nom. (Latch mode)
Transient Response	- Response Deviation - Response Time 3% typ. / 5% max. (50% to 75% Load Step) 2.5 ms typ. / 4 ms max. (50% to 75% Load Step)

Safety Specifications

Standards	- IT / Multimedia Equipment - Certification Documents EN 62368-1 IEC 62368-1 UL 62368-1 www.tracopower.com/txo120-safety-cert
Protection Class	Class I & II (Prepared): Reinforced Insulation See application note: www.tracopower.com/overview/txo120

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

Energy Source	- Output, acc. to 62368-1	ES1
Power Source	- Output, acc. to 62368-1	PS3
Pollution Degree		PD 2
Over Voltage Category		OVC II

EMC Specifications

EMI (Emissions)	- Conducted Emissions	EN 55032 class A (internal filter) EN 55032 class B (internal filter) FCC 47 Part 15 class A (internal filter) FCC 47 Part 15 class B (internal filter)
	- Radiated Emissions	EN 55032 class A (internal filter) FCC 47 Part 15 class A (internal filter)
	- Harmonic Current Emissions	EN 61000-3-2, class A
	- Voltage Fluctuations & Flicker	EN 61000-3-3
EMS (Immunity)	- Electrostatic Discharge	EN 55035 (Multimedia)
		Air: EN 61000-4-2, ± 8 kV, perf. criteria A Contact: EN 61000-4-2, ± 4 kV, perf. criteria A
	- RF Electromagnetic Field	EN 61000-4-3, 3 V/m, perf. criteria A
		EN 61000-4-4, ± 1 kV, perf. criteria A
	- EFT (Burst) / Surge	L to L: EN 61000-4-5, ± 1 kV, perf. criteria A
		EN 61000-4-6, 3 Vrms, perf. criteria A
	- Conducted RF Disturbances	Continuous: EN 61000-4-8, 1 A/m, perf. criteria A
		230 VAC / 50 Hz: EN 61000-4-11
	- PF Magnetic Field	30%, 25 periods, perf. criteria A
		>95%, 0.5 periods, perf. criteria A
EMC / Environmental	- Voltage Dips & Interruptions	>95%, 250 periods, perf. criteria B
		www.tracopower.com/txo120-emc-cert

General Specifications


Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-20°C to +70°C
	- Approved Ambient Temp.	62368-1: +70°C max. (for 50% load) 62368-1: +50°C max. (for 100% load)
	- Storage Temperature	-40°C to +85°C
Power Derating	- High Temperature	2.5 %/K above 50°C
		See application note: www.tracopower.com/txo120-cc
Cooling System	- Option 1	Forced air cooling (with external fan, 10 CFM)
	- Option 2	Natural convection (20 LFM)
Altitude During Operation		2'000 m max.
Regulator Topology		LLC Converter
Switching Frequency		100 kHz typ. (PFM)
Insulation System		Reinforced Insulation
Working Voltage (rated)		464 VAC
Isolation Test Voltage	- Input to Output, 60 s	3'000 VAC (4'242 VDC)
Creepage	- Input to Output	3 mm min.
Clearance	- Input to Output	6 mm min.
Isolation Resistance	- Input to Output, 500 VDC	100 MΩ min.
Leakage Current (at 264 VAC / 60 Hz)	- Touch Current	300 μA max.
Reliability	- Calculated MTBF	100'000 h (MIL-HDBK-217F, ground benign)
Washing Process		Not allowed
Environment	- Vibration	2.4 g, 3 axis, random waveform, 30 min
	- Mechanical Shock	20 g, 3 axis, 6 shocks
Housing Type		Open Frame
Mounting Type		Chassis Mount
Connection Type		Pin Connector

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

Weight	111 g
Environmental Compliance	- REACH Declaration www.tracopower.com/info/reach-declaration.pdf REACH SVHC list compliant REACH Annex XVII compliant www.tracopower.com/info/rohs-declaration.pdf Exemptions: 7(a) (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).) - RoHS Declaration - SCIP Reference Number
	76709c82-3075-4be0-9ccb-c2736d06f3be

Additional Information	
Supporting Documents	www.tracopower.com/overview/txo120
Frequently Asked Questions	www.tracopower.com/glossary-faq
Glossary	www.tracopower.com/info/glossary.pdf
Service Portal	www.tracoserviceportal.com

Outline Dimensions



Pin connectors			
Input (CN1)		Output (CN2)	
Pin	Function	Pin	Function
1	AC (N)	1	+Vout
3	AC (L)	2	
		3	-Vout
		4	

Input (CN1): JST series, B3P-VH(LF)(SN), 3.96mm mates with JST crimp terminal: SVH-21T-P1.1 or equivalent and terminal housing: VHR-3N or equivalent

Output (CN2): JST series, B4P-VH(LF)(SN), 3.96mm mates with JST crimp terminal: SVH-21T-P1.1 or equivalent and terminal housing: VHR-4N or equivalent