


## CLA1B-WKW/MKW: PLCC4 White LEDs



### PRODUCT DESCRIPTION

The CLA1B is packaged in an industry standard footprint. With an improved package to provide high reliability & performance. They are designed to work under a wide range of environmental conditions. This high reliability feature makes them ideally suited to be used under illumination application conditions.

The wide viewing-angle makes these LEDs ideally suited for Linear Lighting, panel lighting and general illumination applications.

### FEATURES

- Size (mm): 3.2 x 2.8
- Color Temperatures (K):  
Cool White CLA1B-WKW :  
(4700 - 8300)  
Warm White CLA1B-MKW :  
(2500 - 4700)
- Luminous Flux (lm)  
CLA1B-WKW: (6.3 - 13.9)  
CLA1B-MKW: (6.3 - 13.9)
- CRI  
Typical CRI for Cool White is 75  
Typical CRI for Warm White is 80
- Lead - Free
- RoHS Compliant

### APPLICATIONS

- Linear Lighting
- Channel Letter
- Panel Lighting
- General Illumination

**ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^\circ\text{C}$ )**

| Items                                                 | Symbol     | Absolute Maximum Rating | Unit               |
|-------------------------------------------------------|------------|-------------------------|--------------------|
| Forward Current                                       | $I_F$      | 80                      | mA                 |
| Peak Forward Current <sup>Note 1</sup>                | $I_{FP}$   | 100                     | mA                 |
| Reverse Voltage                                       | $V_R$      | 5                       | V                  |
| Power Dissipation                                     | $P_D$      | 304                     | mW                 |
| Operation Temperature                                 | $T_{opr}$  | -40 ~ +100              | $^\circ\text{C}$   |
| Storage Temperature                                   | $T_{stg}$  | -40 ~ +100              | $^\circ\text{C}$   |
| Junction Temperature                                  | $T_J$      | 110                     | $^\circ\text{C}$   |
| Junction/Ambient                                      | $R_{THJA}$ | 220                     | $^\circ\text{C/W}$ |
| Junction/Solder Point                                 | $R_{THJS}$ | 120                     | $^\circ\text{C/W}$ |
| Electrostatic Discharge Classification (MIL-STD-883E) | ESD        | 2000V                   |                    |

Note:

1. Pulse width  $\leq 0.1$  msec, duty  $\leq 1/10$ .

**TYPICAL ELECTRICAL & OPTICAL CHARACTERISTICS ( $T_A = 25^\circ\text{C}$ )**

| Characteristics          | Color     | Symbol   | Condition     | Unit          | Minimum | Typical | Maximum |
|--------------------------|-----------|----------|---------------|---------------|---------|---------|---------|
| Forward Voltage          | Cool/Warm | $V_F$    | $I_F = 30$ mA | V             |         | 3.2     | 3.8     |
| Reverse Current          | Cool/Warm | $I_R$    | $V_R = 5$ V   | $\mu\text{A}$ |         |         | 10      |
| Luminous Flux            | Cool      | $\Phi_V$ | $I_F = 30$ mA | lm            | 6.3     | 9.6     |         |
|                          | Warm      | $\Phi_V$ | $I_F = 30$ mA | lm            | 6.3     | 8.6     |         |
| Luminous Intensity       | Cool      | $I_V$    | $I_F = 30$ mA | mcd           | 2800    | 3177    |         |
|                          | Warm      | $I_V$    | $I_F = 30$ mA | mcd           | 2520    | 3023    |         |
| Chromaticity Coordinates | Cool      | x        | $I_F = 30$ mA |               |         | 0.3452  |         |
|                          |           | y        | $I_F = 30$ mA |               |         | 0.3556  |         |
|                          | Warm      | x        | $I_F = 30$ mA |               |         | 0.4343  |         |
|                          |           | y        | $I_F = 30$ mA |               |         | 0.4043  |         |

\* Continuous reverse voltage can cause LED damage.

## FLUX BIN LIMIT

| Cool White / Warm White (30 mA) - CLA1B-WKW/MKW |              |           |           |
|-------------------------------------------------|--------------|-----------|-----------|
| Bin Code                                        | Sub-Bin Code | Min. (lm) | Max. (lm) |
| D0                                              | -            | 6.3       | 8.2       |
| E0                                              | -            | 8.2       | 10.7      |
| F0                                              | F1           | 10.7      | 12.3      |
|                                                 | F2           | 12.3      | 13.9      |

\* Tolerance of measurement of luminous flux is  $\pm 10\%$

## VOLTAGE BIN LIMIT

| Cool White / Warm White (30 mA) - CLA1B-WKW/MKW |          |          |
|-------------------------------------------------|----------|----------|
| Bin Code                                        | Min. (V) | Max. (V) |
| 28                                              | 3.0      | 3.2      |
| 29                                              | 3.2      | 3.4      |
| 2a                                              | 3.4      | 3.6      |
| 2b                                              | 3.6      | 3.8      |

\* Tolerance of measurement of voltage is  $\pm 0.05V$

## COLOR BIN LIMIT

## Cool White / Warm White (30 mA) - CLA1B-WKW/MKW

| Region | x      | y      | Region | x      | y      | Region | x      | y      | Region | x      | y      |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0A     | 0.2950 | 0.2970 | 0B     | 0.2920 | 0.3060 | 0C     | 0.2984 | 0.3133 | 0D     | 0.2984 | 0.3133 |
|        | 0.2920 | 0.3060 |        | 0.2895 | 0.3135 |        | 0.2962 | 0.3220 |        | 0.3048 | 0.3207 |
|        | 0.2984 | 0.3133 |        | 0.2962 | 0.3220 |        | 0.3028 | 0.3304 |        | 0.3068 | 0.3113 |
|        | 0.3009 | 0.3042 |        | 0.2984 | 0.3133 |        | 0.3048 | 0.3207 |        | 0.3009 | 0.3042 |
| 0R     | 0.2980 | 0.2880 | 0S     | 0.2895 | 0.3135 | 0T     | 0.2962 | 0.3220 | 0U     | 0.3037 | 0.2937 |
|        | 0.2950 | 0.2970 |        | 0.2870 | 0.3210 |        | 0.2937 | 0.3312 |        | 0.3009 | 0.3042 |
|        | 0.3009 | 0.3042 |        | 0.2937 | 0.3312 |        | 0.3005 | 0.3415 |        | 0.3068 | 0.3113 |
|        | 0.3037 | 0.2937 |        | 0.2962 | 0.3220 |        | 0.3028 | 0.3304 |        | 0.3093 | 0.2993 |
| 1A     | 0.3048 | 0.3207 | 1B     | 0.3028 | 0.3304 | 1C     | 0.3115 | 0.3391 | 1D     | 0.3130 | 0.3290 |
|        | 0.3130 | 0.3290 |        | 0.3115 | 0.3391 |        | 0.3205 | 0.3481 |        | 0.3213 | 0.3373 |
|        | 0.3144 | 0.3186 |        | 0.3130 | 0.3290 |        | 0.3213 | 0.3373 |        | 0.3221 | 0.3261 |
|        | 0.3068 | 0.3113 |        | 0.3048 | 0.3207 |        | 0.3130 | 0.3290 |        | 0.3144 | 0.3186 |
| 1R     | 0.3068 | 0.3113 | 1S     | 0.3005 | 0.3415 | 1T     | 0.3099 | 0.3509 | 1U     | 0.3144 | 0.3186 |
|        | 0.3144 | 0.3186 |        | 0.3099 | 0.3509 |        | 0.3196 | 0.3602 |        | 0.3221 | 0.3261 |
|        | 0.3161 | 0.3059 |        | 0.3115 | 0.3391 |        | 0.3205 | 0.3481 |        | 0.3231 | 0.3120 |
|        | 0.3093 | 0.2993 |        | 0.3028 | 0.3304 |        | 0.3115 | 0.3391 |        | 0.3161 | 0.3059 |
| 2A     | 0.3215 | 0.3350 | 2B     | 0.3207 | 0.3462 | 2C     | 0.3290 | 0.3538 | 2D     | 0.3290 | 0.3417 |
|        | 0.3290 | 0.3417 |        | 0.3290 | 0.3538 |        | 0.3376 | 0.3616 |        | 0.3371 | 0.3490 |
|        | 0.3290 | 0.3300 |        | 0.3290 | 0.3417 |        | 0.3371 | 0.3490 |        | 0.3366 | 0.3369 |
|        | 0.3222 | 0.3243 |        | 0.3215 | 0.3350 |        | 0.3290 | 0.3417 |        | 0.3290 | 0.3300 |
| 2R     | 0.3222 | 0.3243 | 2S     | 0.3196 | 0.3602 | 2T     | 0.3290 | 0.3690 | 2U     | 0.3290 | 0.3300 |
|        | 0.3290 | 0.3300 |        | 0.3290 | 0.3690 |        | 0.3381 | 0.3762 |        | 0.3366 | 0.3369 |
|        | 0.3290 | 0.3180 |        | 0.3290 | 0.3538 |        | 0.3376 | 0.3616 |        | 0.3361 | 0.3245 |
|        | 0.3231 | 0.3120 |        | 0.3207 | 0.3462 |        | 0.3290 | 0.3538 |        | 0.3290 | 0.3180 |
| 3A     | 0.3371 | 0.3490 | 3B     | 0.3376 | 0.3616 | 3C     | 0.3463 | 0.3687 | 3D     | 0.3451 | 0.3554 |
|        | 0.3451 | 0.3554 |        | 0.3463 | 0.3687 |        | 0.3551 | 0.3760 |        | 0.3533 | 0.3620 |
|        | 0.3440 | 0.3427 |        | 0.3451 | 0.3554 |        | 0.3533 | 0.3620 |        | 0.3515 | 0.3487 |
|        | 0.3366 | 0.3369 |        | 0.3371 | 0.3490 |        | 0.3451 | 0.3554 |        | 0.3440 | 0.3427 |
| 3R     | 0.3366 | 0.3369 | 3S     | 0.3381 | 0.3762 | 3T     | 0.3480 | 0.3840 | 3U     | 0.3440 | 0.3428 |
|        | 0.3440 | 0.3428 |        | 0.3480 | 0.3840 |        | 0.3571 | 0.3907 |        | 0.3515 | 0.3487 |
|        | 0.3429 | 0.3307 |        | 0.3463 | 0.3687 |        | 0.3551 | 0.3760 |        | 0.3495 | 0.3339 |
|        | 0.3361 | 0.3245 |        | 0.3376 | 0.3616 |        | 0.3463 | 0.3687 |        | 0.3429 | 0.3307 |
| 4A     | 0.3530 | 0.3597 | 4B     | 0.3548 | 0.3736 | 4C     | 0.3641 | 0.3804 | 4D     | 0.3615 | 0.3659 |
|        | 0.3615 | 0.3659 |        | 0.3641 | 0.3804 |        | 0.3736 | 0.3874 |        | 0.3702 | 0.3722 |
|        | 0.3590 | 0.3521 |        | 0.3615 | 0.3659 |        | 0.3702 | 0.3722 |        | 0.3670 | 0.3578 |
|        | 0.3512 | 0.3465 |        | 0.3530 | 0.3597 |        | 0.3615 | 0.3659 |        | 0.3590 | 0.3521 |

- Tolerance of measurement of the color coordinates is  $\pm 0.01$

## COLOR BIN LIMIT

## Cool White / Warm White (30 mA) - CLA1B-WKW/MKW

| Region | x      | y      | Region | x      | y      | Region | x      | y      | Region | x      | y      |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 4R     | 0.3512 | 0.3465 | 4S     | 0.3571 | 0.3907 | 4T     | 0.3668 | 0.3957 | 4U     | 0.3590 | 0.3521 |
|        | 0.3590 | 0.3521 |        | 0.3668 | 0.3957 |        | 0.3771 | 0.4034 |        | 0.3670 | 0.3578 |
|        | 0.3567 | 0.3389 |        | 0.3641 | 0.3804 |        | 0.3736 | 0.3874 |        | 0.3640 | 0.3440 |
|        | 0.3495 | 0.3339 |        | 0.3548 | 0.3736 |        | 0.3641 | 0.3804 |        | 0.3567 | 0.3389 |
| 5A1    | 0.3670 | 0.3578 | 5A2    | 0.3686 | 0.3649 | 5A3    | 0.3744 | 0.3685 | 5A4    | 0.3726 | 0.3612 |
|        | 0.3686 | 0.3649 |        | 0.3702 | 0.3722 |        | 0.3763 | 0.3760 |        | 0.3744 | 0.3685 |
|        | 0.3744 | 0.3685 |        | 0.3763 | 0.3760 |        | 0.3825 | 0.3798 |        | 0.3804 | 0.3721 |
|        | 0.3726 | 0.3612 |        | 0.3744 | 0.3685 |        | 0.3804 | 0.3721 |        | 0.3783 | 0.3646 |
| 5B1    | 0.3702 | 0.3722 | 5B2    | 0.3719 | 0.3797 | 5B3    | 0.3782 | 0.3837 | 5B4    | 0.3763 | 0.3760 |
|        | 0.3719 | 0.3797 |        | 0.3736 | 0.3874 |        | 0.3802 | 0.3916 |        | 0.3782 | 0.3837 |
|        | 0.3782 | 0.3837 |        | 0.3802 | 0.3916 |        | 0.3869 | 0.3958 |        | 0.3847 | 0.3877 |
|        | 0.3763 | 0.3760 |        | 0.3782 | 0.3837 |        | 0.3847 | 0.3877 |        | 0.3825 | 0.3798 |
| 5C1    | 0.3825 | 0.3798 | 5C2    | 0.3847 | 0.3877 | 5C3    | 0.3912 | 0.3917 | 5C4    | 0.3887 | 0.3836 |
|        | 0.3847 | 0.3877 |        | 0.3869 | 0.3958 |        | 0.3937 | 0.4001 |        | 0.3912 | 0.3917 |
|        | 0.3912 | 0.3917 |        | 0.3937 | 0.4001 |        | 0.4006 | 0.4044 |        | 0.3978 | 0.3958 |
|        | 0.3887 | 0.3836 |        | 0.3912 | 0.3917 |        | 0.3978 | 0.3958 |        | 0.3950 | 0.3875 |
| 5D1    | 0.3783 | 0.3646 | 5D2    | 0.3804 | 0.3721 | 5D3    | 0.3863 | 0.3758 | 5D4    | 0.3840 | 0.3681 |
|        | 0.3804 | 0.3721 |        | 0.3825 | 0.3798 |        | 0.3887 | 0.3836 |        | 0.3863 | 0.3758 |
|        | 0.3863 | 0.3758 |        | 0.3887 | 0.3836 |        | 0.3950 | 0.3875 |        | 0.3924 | 0.3794 |
|        | 0.3840 | 0.3681 |        | 0.3863 | 0.3758 |        | 0.3924 | 0.3794 |        | 0.3898 | 0.3716 |
| 6A1    | 0.3889 | 0.3690 | 6A2    | 0.3915 | 0.3768 | 6A3    | 0.3981 | 0.3800 | 6A4    | 0.3953 | 0.3720 |
|        | 0.3915 | 0.3768 |        | 0.3941 | 0.3848 |        | 0.4010 | 0.3882 |        | 0.3981 | 0.3800 |
|        | 0.3981 | 0.3800 |        | 0.4010 | 0.3882 |        | 0.4080 | 0.3916 |        | 0.4048 | 0.3832 |
|        | 0.3953 | 0.3720 |        | 0.3981 | 0.3800 |        | 0.4048 | 0.3832 |        | 0.4017 | 0.3751 |
| 6B1    | 0.3941 | 0.3848 | 6B2    | 0.3968 | 0.3930 | 6B3    | 0.4040 | 0.3966 | 6B4    | 0.4010 | 0.3882 |
|        | 0.3968 | 0.3930 |        | 0.3996 | 0.4015 |        | 0.4071 | 0.4052 |        | 0.4040 | 0.3966 |
|        | 0.4040 | 0.3966 |        | 0.4071 | 0.4052 |        | 0.4146 | 0.4089 |        | 0.4113 | 0.4001 |
|        | 0.4010 | 0.3882 |        | 0.4040 | 0.3966 |        | 0.4113 | 0.4001 |        | 0.4080 | 0.3916 |
| 6C1    | 0.4080 | 0.3916 | 6C2    | 0.4113 | 0.4001 | 6C3    | 0.4186 | 0.4037 | 6C4    | 0.4150 | 0.3950 |
|        | 0.4113 | 0.4001 |        | 0.4146 | 0.4089 |        | 0.4222 | 0.4127 |        | 0.4186 | 0.4037 |
|        | 0.4186 | 0.4037 |        | 0.4222 | 0.4127 |        | 0.4299 | 0.4165 |        | 0.4259 | 0.4073 |
|        | 0.4150 | 0.3950 |        | 0.4186 | 0.4037 |        | 0.4259 | 0.4073 |        | 0.4221 | 0.3984 |
| 6D1    | 0.4017 | 0.3751 | 6D2    | 0.4048 | 0.3832 | 6D3    | 0.4116 | 0.3865 | 6D4    | 0.4082 | 0.3782 |
|        | 0.4048 | 0.3832 |        | 0.4080 | 0.3916 |        | 0.4150 | 0.3950 |        | 0.4116 | 0.3865 |
|        | 0.4116 | 0.3865 |        | 0.4150 | 0.3950 |        | 0.4221 | 0.3984 |        | 0.4183 | 0.3898 |
|        | 0.4082 | 0.3782 |        | 0.4116 | 0.3865 |        | 0.4183 | 0.3898 |        | 0.4147 | 0.3814 |

- Tolerance of measurement of the color coordinates is  $\pm 0.01$



## COLOR BIN LIMIT

## Cool White / Warm White (30 mA) - CLA1B-WKW/MKW

| Region | x      | y      | Region | x      | y      | Region | x      | y      | Region | x      | y      |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 7A1    | 0.4147 | 0.3814 | 7A2    | 0.4183 | 0.3898 | 7A3    | 0.4242 | 0.3919 | 7A4    | 0.4203 | 0.3833 |
|        | 0.4183 | 0.3898 |        | 0.4221 | 0.3984 |        | 0.4281 | 0.4006 |        | 0.4242 | 0.3919 |
|        | 0.4242 | 0.3919 |        | 0.4281 | 0.4006 |        | 0.4342 | 0.4028 |        | 0.4300 | 0.3939 |
|        | 0.4203 | 0.3833 |        | 0.4242 | 0.3919 |        | 0.4300 | 0.3939 |        | 0.4259 | 0.3853 |
| 7B1    | 0.4221 | 0.3984 | 7B2    | 0.4259 | 0.4073 | 7B3    | 0.4322 | 0.4096 | 7B4    | 0.4281 | 0.4006 |
|        | 0.4259 | 0.4073 |        | 0.4299 | 0.4165 |        | 0.4364 | 0.4188 |        | 0.4322 | 0.4096 |
|        | 0.4322 | 0.4096 |        | 0.4364 | 0.4188 |        | 0.4430 | 0.4212 |        | 0.4385 | 0.4119 |
|        | 0.4281 | 0.4006 |        | 0.4322 | 0.4096 |        | 0.4385 | 0.4119 |        | 0.4342 | 0.4028 |
| 7C1    | 0.4342 | 0.4028 | 7C2    | 0.4385 | 0.4119 | 7C3    | 0.4449 | 0.4141 | 7C4    | 0.4403 | 0.4049 |
|        | 0.4385 | 0.4119 |        | 0.4430 | 0.4212 |        | 0.4496 | 0.4236 |        | 0.4449 | 0.4141 |
|        | 0.4449 | 0.4141 |        | 0.4496 | 0.4236 |        | 0.4562 | 0.4260 |        | 0.4513 | 0.4164 |
|        | 0.4403 | 0.4049 |        | 0.4449 | 0.4141 |        | 0.4513 | 0.4164 |        | 0.4465 | 0.4071 |
| 7D1    | 0.4259 | 0.3853 | 7D2    | 0.4300 | 0.3939 | 7D3    | 0.4359 | 0.3960 | 7D4    | 0.4316 | 0.3873 |
|        | 0.4300 | 0.3939 |        | 0.4342 | 0.4028 |        | 0.4403 | 0.4049 |        | 0.4359 | 0.3960 |
|        | 0.4359 | 0.3960 |        | 0.4403 | 0.4049 |        | 0.4465 | 0.4071 |        | 0.4418 | 0.3981 |
|        | 0.4316 | 0.3873 |        | 0.4359 | 0.3960 |        | 0.4418 | 0.3981 |        | 0.4373 | 0.3893 |
| 8A1    | 0.4373 | 0.3893 | 8A2    | 0.4418 | 0.3981 | 8A3    | 0.4475 | 0.3994 | 8A4    | 0.4428 | 0.3906 |
|        | 0.4418 | 0.3981 |        | 0.4465 | 0.4071 |        | 0.4523 | 0.4085 |        | 0.4475 | 0.3994 |
|        | 0.4475 | 0.3994 |        | 0.4523 | 0.4085 |        | 0.4582 | 0.4099 |        | 0.4532 | 0.4008 |
|        | 0.4428 | 0.3906 |        | 0.4475 | 0.3994 |        | 0.4532 | 0.4008 |        | 0.4483 | 0.3919 |
| 8B1    | 0.4465 | 0.4071 | 8B2    | 0.4513 | 0.4164 | 8B3    | 0.4573 | 0.4178 | 8B4    | 0.4523 | 0.4085 |
|        | 0.4513 | 0.4164 |        | 0.4562 | 0.4260 |        | 0.4624 | 0.4274 |        | 0.4573 | 0.4178 |
|        | 0.4573 | 0.4178 |        | 0.4624 | 0.4274 |        | 0.4687 | 0.4289 |        | 0.4634 | 0.4193 |
|        | 0.4523 | 0.4085 |        | 0.4573 | 0.4178 |        | 0.4634 | 0.4193 |        | 0.4582 | 0.4099 |
| 8C1    | 0.4582 | 0.4099 | 8C2    | 0.4634 | 0.4193 | 8C3    | 0.4695 | 0.4207 | 8C4    | 0.4641 | 0.4112 |
|        | 0.4634 | 0.4193 |        | 0.4687 | 0.4289 |        | 0.4750 | 0.4304 |        | 0.4695 | 0.4207 |
|        | 0.4695 | 0.4207 |        | 0.4750 | 0.4304 |        | 0.4813 | 0.4319 |        | 0.4756 | 0.4221 |
|        | 0.4641 | 0.4112 |        | 0.4695 | 0.4207 |        | 0.4756 | 0.4221 |        | 0.4700 | 0.4126 |
| 8D1    | 0.4483 | 0.3919 | 8D2    | 0.4532 | 0.4008 | 8D3    | 0.4589 | 0.4021 | 8D4    | 0.4538 | 0.3931 |
|        | 0.4532 | 0.4008 |        | 0.4582 | 0.4099 |        | 0.4641 | 0.4112 |        | 0.4589 | 0.4021 |
|        | 0.4589 | 0.4021 |        | 0.4641 | 0.4112 |        | 0.4700 | 0.4126 |        | 0.4646 | 0.4034 |
|        | 0.4538 | 0.3931 |        | 0.4589 | 0.4021 |        | 0.4646 | 0.4034 |        | 0.4593 | 0.3944 |

- Tolerance of measurement of the color coordinates is  $\pm 0.01$

## CIE CHROMATICITY DIAGRAM



## ORDER CODE TABLE

| Color      | Kit Number         | Luminous Flux (lm) |      | Color Bin Code                                                                                                              |
|------------|--------------------|--------------------|------|-----------------------------------------------------------------------------------------------------------------------------|
|            |                    | Min.               | Max. |                                                                                                                             |
| Cool White | CLA1B-WKW-XD0F0503 | 6.3                | 13.9 | 1A0,1B0,1C0,1D0,2A0,2B0,2C0,2D0                                                                                             |
|            | CLA1B-WKW-XD0F0513 |                    |      | 0A0,0B0,0C0,0D0,0R0,0S0,0T0,0U0,<br>1A0,1B0,1C0,1D0,1S0,1T0,1R0,1U0,<br>2A0,2B0,2C0,2D0,2R0,2S0,2T0,2U0,<br>3S0,3B0,3A0,3R0 |
|            | CLA1B-WKW-XD0F0DT3 |                    |      | 0A0,0B0,0C0,0D0,0R0,0S0,0T0,0U0,<br>1A0,1B0,1C0,1D0,1R0,1S0,1T0,1U0                                                         |
|            | CLA1B-WKW-XD0F0DV3 |                    |      | 1A0,1B0,1C0,1D0,1R0,1S0,1T0,1U0,<br>2A0,2B0,2C0,2D0,2R0,2S0,2T0,2U0                                                         |
|            | CLA1B-WKW-XD0F0DY3 |                    |      | 2A0,2B0,2C0,2D0,2R0,2S0,2T0,2U0,<br>3A0,3B0,3C0,3D0,3R0,3S0,3T0,3U0                                                         |
|            | CLA1B-WKW-XD0F0DZ3 |                    |      | 2C0,2D0, 2T0,2U0,<br>3A0,3B0,3C0,3D0,3R0,3S0,3T0,3U0,<br>4A0,4B0,4R0,4S0                                                    |
|            | CLA1B-WKW-XD0F0E13 |                    |      | 1A0,1B0,1C0,1D0                                                                                                             |
|            | CLA1B-WKW-XD0F0E23 |                    |      | 2A0,2B0,2C0,2D0                                                                                                             |
|            | CLA1B-WKW-XD0F0E33 |                    |      | 3A0,3B0,3C0,3D0                                                                                                             |
|            | CLA1B-WKW-XE0F0503 | 8.2                | 13.9 | 1A0,1B0,1C0,1D0,2A0,2B0,2C0,2D0                                                                                             |
|            | CLA1B-WKW-XE0F0513 |                    |      | 0A0,0B0,0C0,0D0,0R0,0S0,0T0,0U0,<br>1A0,1B0,1C0,1D0,1S0,1T0,1R0,1U0,<br>2A0,2B0,2C0,2D0,2R0,2S0,2T0,2U0,<br>3S0,3B0,3A0,3R0 |
|            | CLA1B-WKW-XE0F0DT3 |                    |      | 0A0,0B0,0C0,0D0,0R0,0S0,0T0,0U0,<br>1A0,1B0,1C0,1D0,1R0,1S0,1T0,1U0                                                         |
|            | CLA1B-WKW-XE0F0DV3 |                    |      | 1A0,1B0,1C0,1D0,1R0,1S0,1T0,1U0,<br>2A0,2B0,2C0,2D0,2R0,2S0,2T0,2U0                                                         |
|            | CLA1B-WKW-XE0F0DY3 |                    |      | 2A0,2B0,2C0,2D0,2R0,2S0,2T0,2U0,<br>3A0,3B0,3C0,3D0,3R0,3S0,3T0,3U0                                                         |
|            | CLA1B-WKW-XE0F0DZ3 |                    |      | 2C0,2D0, 2T0,2U0,<br>3A0,3B0,3C0,3D0,3R0,3S0,3T0,3U0,<br>4A0,4B0,4R0,4S0                                                    |
|            | CLA1B-WKW-XE0F0E13 |                    |      | 1A0,1B0,1C0,1D0                                                                                                             |
|            | CLA1B-WKW-XE0F0E23 |                    |      | 2A0,2B0,2C0,2D0                                                                                                             |
|            | CLA1B-WKW-XE0F0E33 |                    |      | 3A0,3B0,3C0,3D0                                                                                                             |

## Notes:

- The above kit numbers represent order codes that include multiple flux-bin and color-bin codes. Only one flux-bin code and one color-bin code will be shipped on each bulk. Single flux-bin code and single color-bin codes will not be orderable.
- Please refer to the [HB LED Lamp Reliability Test Standards](#) document for reliability test conditions.
- Please refer to the [HB LED Lamp Soldering & Handling](#) document for information about how to use this LED product safely.



## ORDER CODE TABLE

| Color      | Kit Number         | Luminous Flux (lm) |      | Color Bin Code                                                                                          |
|------------|--------------------|--------------------|------|---------------------------------------------------------------------------------------------------------|
|            |                    | Min.               | Max. |                                                                                                         |
| Warm White | CLA1B-MKW-XD0E0F53 | 6.3                | 10.7 | 4C0,4D0,<br>5A1,5A2,5A3,5A4,5B1,5B2,5B3,5B4                                                             |
|            | CLA1B-MKW-XD0E0F63 |                    |      | 5C1,5C2,5C3,5C4,5D1,5D2,5D3,5D4,<br>6A1,6A2,6A3,6A4,6B1,6B2,6B3,6B4                                     |
|            | CLA1B-MKW-XD0E0F73 |                    |      | 6C1,6C2,6C3,6C4,6D1,6D2,6D3,6D4,<br>7A1,7A2,7A3,7A4,7B1,7B2,7B3,7B4                                     |
|            | CLA1B-MKW-XD0E0F83 |                    |      | 7C1,7C2,7C3,7C4,7D1,7D2,7D3,7D4,<br>8A1,8A2,8A3,8A4,8B1,8B2,8B3,8B4                                     |
|            | CLA1B-MKW-XD0E0E53 |                    |      | 5A1,5A2,5A3,5A4,5B1,5B2,5B3,5B4,<br>5C1,5C2,5C3,5C4,5D1,5D2,5D3,5D4                                     |
|            | CLA1B-MKW-XD0E0E63 |                    |      | 6A1,6A2,6A3,6A4,6B1,6B2,6B3,6B4,<br>6C1,6C2,6C3,6C4,6D1,6D2,6D3,6D4                                     |
|            | CLA1B-MKW-XD0E0E73 |                    |      | 7A1,7A2,7A3,7A4,7B1,7B2,7B3,7B4,<br>7C1,7C2,7C3,7C4,7D1,7D2,7D3,7D4                                     |
|            | CLA1B-MKW-XD0E0E83 |                    |      | 8A1,8A2,8A3,8A4,8B1,8B2,8B3,8B4,<br>8C1,8C2,8C3,8C4,8D1,8D2,8D3,8D4                                     |
|            | CLA1B-MKW-XD0E0A33 |                    |      | 4A0,4B0,4C0,4D0,<br>5A1,5A2,5A3,5A4,5B1,5B2,5B3,5B4                                                     |
|            | CLA1B-MKW-XD0E0A43 |                    |      | 4C0,4D0,<br>5A1,5A2,5A3,5A4,5B1,5B2,5B3,5B4,<br>5C1,5C2,5C3,5C4,5D1,5D2,5D3,5D4                         |
|            | CLA1B-MKW-XD0E0A53 |                    |      | 5A1,5A2,5A3,5A4,5B1,5B2,5B3,5B4,<br>5C1,5C2,5C3,5C4,5D1,5D2,5D3,5D4,<br>6A1,6A2,6A3,6A4,6B1,6B2,6B3,6B4 |
|            | CLA1B-MKW-XD0E0A63 |                    |      | 5C1,5C2,5C3,5C4,5D1,5D2,5D3,5D4,<br>6A1,6A2,6A3,6A4,6B1,6B2,6B3,6B4,<br>6C1,6C2,6C3,6C4,6D1,6D2,6D3,6D4 |
|            | CLA1B-MKW-XD0E0A73 |                    |      | 6A1,6A2,6A3,6A4,6B1,6B2,6B3,6B4,<br>6C1,6C2,6C3,6C4,6D1,6D2,6D3,6D4,<br>7A1,7A2,7A3,7A4,7B1,7B2,7B3,7B4 |
|            | CLA1B-MKW-XD0E0A83 |                    |      | 6C1,6C2,6C3,6C4,6D1,6D2,6D3,6D4,<br>7A1,7A2,7A3,7A4,7B1,7B2,7B3,7B4,<br>7C1,7C2,7C3,7C4,7D1,7D2,7D3,7D4 |
|            | CLA1B-MKW-XD0E0A93 |                    |      | 7A1,7A2,7A3,7A4,7B1,7B2,7B3,7B4,<br>7C1,7C2,7C3,7C4,7D1,7D2,7D3,7D4,<br>8A1,8A2,8A3,8A4,8B1,8B2,8B3,8B4 |
|            | CLA1B-MKW-XD0E0AA3 |                    |      | 7C1,7C2,7C3,7C4,7D1,7D2,7D3,7D4,<br>8A1,8A2,8A3,8A4,8B1,8B2,8B3,8B4,<br>8C1,8C2,8C3,8C4,8D1,8D2,8D3,8D4 |

## Notes:

- The above kit numbers represent order codes that include multiple flux-bin and color-bin codes. Only one flux-bin code and one color-bin code will be shipped on each bulk. Single flux-bin code and single color-bin codes will not be orderable.
- Please refer to the [HB LED Lamp Reliability Test Standards](#) document for reliability test conditions.
- Please refer to the [HB LED Lamp Soldering & Handling](#) document for information about how to use this LED product safely.

## ORDER CODE TABLE

| Color      | Kit Number         | Luminous Flux (lm) |      | Color Bin Code                                                                                          |
|------------|--------------------|--------------------|------|---------------------------------------------------------------------------------------------------------|
|            |                    | Min.               | Max. |                                                                                                         |
| Warm White | CLA1B-MKW-XD0F0F53 | 6.3                | 13.9 | 4C0,4D0,<br>5A1,5A2,5A3,5A4,5B1,5B2,5B3,5B4                                                             |
|            | CLA1B-MKW-XD0F0F63 |                    |      | 5C1,5C2,5C3,5C4,5D1,5D2,5D3,5D4,<br>6A1,6A2,6A3,6A4,6B1,6B2,6B3,6B4                                     |
|            | CLA1B-MKW-XD0F0F73 |                    |      | 6C1,6C2,6C3,6C4,6D1,6D2,6D3,6D4,<br>7A1,7A2,7A3,7A4,7B1,7B2,7B3,7B4                                     |
|            | CLA1B-MKW-XD0F0F83 |                    |      | 7C1,7C2,7C3,7C4,7D1,7D2,7D3,7D4,<br>8A1,8A2,8A3,8A4,8B1,8B2,8B3,8B4                                     |
|            | CLA1B-MKW-XD0F0E53 |                    |      | 5A1,5A2,5A3,5A4,5B1,5B2,5B3,5B4,<br>5C1,5C2,5C3,5C4,5D1,5D2,5D3,5D4                                     |
|            | CLA1B-MKW-XD0F0E63 |                    |      | 6A1,6A2,6A3,6A4,6B1,6B2,6B3,6B4,<br>6C1,6C2,6C3,6C4,6D1,6D2,6D3,6D4                                     |
|            | CLA1B-MKW-XD0F0E73 |                    |      | 7A1,7A2,7A3,7A4,7B1,7B2,7B3,7B4,<br>7C1,7C2,7C3,7C4,7D1,7D2,7D3,7D4                                     |
|            | CLA1B-MKW-XD0F0E83 |                    |      | 8A1,8A2,8A3,8A4,8B1,8B2,8B3,8B4,<br>8C1,8C2,8C3,8C4,8D1,8D2,8D3,8D4                                     |
|            | CLA1B-MKW-XD0F0A33 |                    |      | 4A0,4B0,4C0,4D0,<br>5A1,5A2,5A3,5A4,5B1,5B2,5B3,5B4                                                     |
|            | CLA1B-MKW-XD0F0A43 |                    |      | 4C0,4D0,<br>5A1,5A2,5A3,5A4,5B1,5B2,5B3,5B4,<br>5C1,5C2,5C3,5C4,5D1,5D2,5D3,5D4                         |
|            | CLA1B-MKW-XD0F0A53 |                    |      | 5A1,5A2,5A3,5A4,5B1,5B2,5B3,5B4,<br>5C1,5C2,5C3,5C4,5D1,5D2,5D3,5D4,<br>6A1,6A2,6A3,6A4,6B1,6B2,6B3,6B4 |
|            | CLA1B-MKW-XD0F0A63 |                    |      | 5C1,5C2,5C3,5C4,5D1,5D2,5D3,5D4,<br>6A1,6A2,6A3,6A4,6B1,6B2,6B3,6B4,<br>6C1,6C2,6C3,6C4,6D1,6D2,6D3,6D4 |
|            | CLA1B-MKW-XD0F0A73 |                    |      | 6A1,6A2,6A3,6A4,6B1,6B2,6B3,6B4,<br>6C1,6C2,6C3,6C4,6D1,6D2,6D3,6D4,<br>7A1,7A2,7A3,7A4,7B1,7B2,7B3,7B4 |
|            | CLA1B-MKW-XD0F0A83 |                    |      | 6C1,6C2,6C3,6C4,6D1,6D2,6D3,6D4,<br>7A1,7A2,7A3,7A4,7B1,7B2,7B3,7B4,<br>7C1,7C2,7C3,7C4,7D1,7D2,7D3,7D4 |
|            | CLA1B-MKW-XD0F0A93 |                    |      | 7A1,7A2,7A3,7A4,7B1,7B2,7B3,7B4,<br>7C1,7C2,7C3,7C4,7D1,7D2,7D3,7D4,<br>8A1,8A2,8A3,8A4,8B1,8B2,8B3,8B4 |
|            | CLA1B-MKW-XD0F0AA3 |                    |      | 7C1,7C2,7C3,7C4,7D1,7D2,7D3,7D4,<br>8A1,8A2,8A3,8A4,8B1,8B2,8B3,8B4,<br>8C1,8C2,8C3,8C4,8D1,8D2,8D3,8D4 |

## Notes:

- The above kit numbers represent order codes that include multiple flux-bin and color-bin codes. Only one flux-bin code and one color-bin code will be shipped on each bulk. Single flux-bin code and single color-bin codes will not be orderable.
- Please refer to the [HB LED Lamp Reliability Test Standards](#) document for reliability test conditions.
- Please refer to the [HB LED Lamp Soldering & Handling](#) document for information about how to use this LED product safely.

## GRAPHS

The data below are collected from statistical figures that do not necessarily correspond to the actual parameters of each single LED. Hence, these data will be changed without further notice.




FIG.1 FORWARD CURRENT VS. FORWARD VOLTAGE.




FIG.2 RELATIVE LUMINOUS FLUX VS. FORWARD CURRENT




FIG.3 REVERSE CURRENT VS. REVERSE VOLTAGE.




FIG.4 RELATIVE LUMINOUS INTENSITY VS. WAVELENGTH.




FIG.5 MAXIMUM FORWARD DC CURRENT VS AMBIENT TEMPERATURE ( $T_{jmax}=110^{\circ}\text{C}$ )





FIG.6 FAR FIELD PATTERN

## MECHANICAL DIMENSIONS

All dimensions are in mm.



## NOTES

### RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Cree LED representative or from the [Product Ecology](#) section of the Cree LED website.


### Vision Advisory

**WARNING:** Do not look at an exposed lamp in operation. Eye injury can result.

## KIT NUMBER SYSTEM


Cree LED lamps are tested and sorted into performance bins. A bin is specified by ranges of color, forward voltage, and brightness. Sorted LEDs are packaged for shipping in various convenient options.

Cree LEDs are sold by order codes in combinations of bins called kits. Order codes are configured in the following manner:



## REFLOW SOLDERING


- The CLA1B-WKW/MKW is rated as a MSL 5a product.
- The recommended floor life out of bag is 24hrs.
- The temperature profile is as below.



Use only with CLA1B-WKW MKW

| Solder                                               |
|------------------------------------------------------|
| Average ramp-up rate = 4°C/s max                     |
| Preheat temperature = 150°C ~200°C                   |
| Preheat time = 120s max                              |
| Ramp-down rate = 6°C/s max                           |
| Peak temperature = 250°C max                         |
| Time within 5°C of actual Peak Temperature = 10s max |
| Duration above 217°C is 60s max                      |

- The packaging sizes of these SMD products are very small and the resin is still soft after solidification. Users are required to handle with care. Never touch the resin surface of SMD products.
- To avoid damaging the product's surface and interior device, it is recommended to choose a special nozzle to pick up the SMD products during the process of SMT production. If handling is necessary, take special care when picking up these products. The following method is necessary:
- Please refer to the [HB LED Lamp Soldering & Handling](#) document for information about how to use this LED product safely.



## PACKAGING

- The LEDs are packed in cardboard boxes after packaging in normal or anti-electrostatic bags.
- Cardboard boxes will be used to protect the LEDs from mechanical shock during transportation.
- The boxes are not water resistant, and they must be kept away from water and moisture.
- The reel pack is applied in SMD LED.
- Max 2000 pcs per reel.

