



Part Number : [1200010722](#)
Product Description : Micro-Change (M12)
Single-Ended Cordset, 4 Poles, Female (90°) to
Pigtail, 20 AWG, 5.0m (16.40') Length
Series Number : 120001
Status : Obsolete
Product Category : Circular Industrial
Cordsets
Engineering Number : 804001J11M050



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Circular Industrial Cordsets
Series	120001
Description	Micro-Change (M12) Single-Ended Cordset, 4 Poles, Female (90°) to Pigtail, 20 AWG, 5.0m (16.40') Length
IP Rating	IP67, IP68
Product Name	Micro-Change (M12)
Type	Single Ended
UPC	883906487867

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	6.10mm (.240")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Gray
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Teflon Nickel-plated Brass
Material - O-Ring	Viton
Material - Plating Mating	Gold
Net Weight	308.247/g

Orientation	90° to Pigtail
Poles	4
Temperature Range - Operating	0° to +75°C
Wire/Cable Type	Unshielded PVC
Wire Size (AWG)	20

This document was generated on Apr 26, 2025