

Step-Down Transformer

APC 208V/120V 10KVA Step down Transformer



APC Step-Down Transformer, Input: 208V, Input Connections: Hard Wire 3-wire (2PH + G), Output: 120V, 208V, 240V, Output Connections: Hard Wire 3-wire (2PH + G), Hard Wire 4-wire (2PH + N + G), NEMA L14-30R, NEMA L5-20R

Includes: Documentation CD, Hardwire panel, Installation guide, Rack Mounting brackets, User Manual

Standard Lead Time: Special Order - Call for Quoted Lead Times

APTF10KT01

Email Technical Specifications

Printer Friendly



Product Category

- Rack Power Distribution (6)
- Row Power Distribution (6)
- Room Power Distribution (1)
- Transfer Switches (2)



Return to Power Distribution

More Images

Technical Specifications

Product Overview

Documentation

Options

Output

Nominal Output Voltage 120V, 208V, 240V

Maximum Total Current Draw per Phase 60A

Output Connections (1) Hard Wire 3-wire (2PH + G)
(1) Hard Wire 4-wire (2PH + N + G)
(2) NEMA L14-30R
(2) NEMA L5-20R



Always on Outlets 4

Overload Protection Yes

Input

Nominal Input Voltage 208V

Input Frequency 45 - 65 Hz

Input Connections Hard Wire 3-wire (2PH + G)

Acceptable Input Voltage 200-240 VAC

Maximum Line Current per phase 60A

Maximum Input Current per phase 60A

Load Capacity 10 kVA

Physical

Net Weight 100.00 KG

Maximum Height 175.00 mm

Maximum Width 432.00 mm

Maximum Depth 749.00 mm

Shipping Weight 125.00 KG

Shipping Height 406.00 mm

Shipping Width 600.00 mm

Shipping Depth 1000.00 mm

Color Black

Environmental

Operating Environment 0 - 40 °C

Operating Relative Humidity 0 - 95%

Operating Elevation 0-3000 meters

Storage Temperature -25 - 65 °C

Storage Relative Humidity 0 - 95%

Storage Elevation 0-15000 meters

Conformance

Regulatory Approvals C-tick, CE, CSA, GOST, UL Listed, VDE

Standard Warranty 2 years repair or replace

Sustainable Offer Status

RoHS Compliant

REACH REACH: Contains No SVHCs