

2122DH3PG Product Details



2122DH3PG
(1-1423154-0)
TE Internal Number: 1-1423154-0
 Active
 [Add to Part List](#)

Time Delay Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- 2100 Miniature Timing Series
- Time Delay Relay
- Input Voltage = 48 VDC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Rating = 10A @ 120 VAC

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Time Delay Relay
- Termination Type = "AN" Connector

Electrical Characteristics:

- Input Voltage (VDC) = 48
- Contact Rating = 10A @ 120 VAC

Body Related Features:

- [Series](#) = 2100 Miniature Timing

Contact Related Features:

- Mounting Options = Panel Mount
- Mode of Operation = Off-Delay
- Delay Time = 2 seconds to 60 seconds
- Type of Control = Screw
- Repeatability, Max. = $\pm 5\%$ @ 25°C, $\pm 7\%$ @ 85°C, $\pm 8\%$ @ 55°C
- Approved Standards = CE Approved
- Option = Hermetically Sealed
- Approx. Dimensions (L x W x H) (mm [in]) = 63.50 x 38.60 x 123.90 [2.501 x 1.520 x 4.881]

Configuration Related Features:

- [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- Multiple Timing Ranges = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

Conditions for Usage:

- Temperature Range (°C) = -55 – +85

Other:

- Brand = Agastat