

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	25[mm]
Max. Air Flow:	37.8[CFM]
Max. Air Flow:	1.07[m3 per min]
Max. Static Pressure:	0.64[In H2O]
Max. Static Pressure:	159[Pa]
Fan Speed:	7500[RPM]
Noise:	47[dB]
Life Expectancy:	60 degree C 40,000 Hours AA/EA[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	10[V]
Operating Voltage - Upper:	26.4[V]
Current:	0.18[A]
Input Power:	4.3[W]
Mass:	56[g]
Tach / Locked Rotor Output:	No
Status:	Active