

STD10N60M6

Datasheet

N-channel 600 V, 520 mΩ typ., 6.4 A MDmesh M6 Power MOSFET in a DPAK package



DPAK



Features

Order code	V_{DS} @ T_{Jmax}	$R_{DS(on)}$ max.	I_D
STD10N60M6	650 V	600 mΩ	6.4 A

- Reduced switching losses
- Lower $R_{DS(on)}$ per area vs previous generation
- Low gate input resistance
- 100% avalanche tested
- Zener-protected

Applications

- Switching applications
- LLC converters, resonant converters
- Boost PFC converters

Description

The new MDmesh M6 technology incorporates the most recent advancements to the well-known and consolidated MDmesh family of SJ MOSFETs. STMicroelectronics builds on the previous generation of MDmesh devices through its new M6 technology, which combines excellent $R_{DS(on)}$ per area improvement with one of the most effective switching behaviors available, as well as a user-friendly experience for maximum end-application efficiency.

Product status link
STD10N60M6

Product summary	
Order code	STD10N60M6
Marking	10N60M6
Package	DPAK
Packing	Tape and reel

Downloaded from Arrow.com.

1 Electrical ratings

Table 1. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{GS}	Gate-source voltage	±25	V
I_D	Drain current (continuous) at T_C = 25 °C	6.4	A
	Drain current (continuous) at T_C = 100 °C	4	A
I_{DM} (1)	Drain current (pulsed)	16.6	A
P_{TOT}	Total power dissipation at T_C = 25 °C	60	W
dv/dt(2)	Peak diode recovery voltage slope	15	V/ns
dv/dt(3)	MOSFET dv/dt ruggedness	100	V/ns
T_j	Operating junction temperature range	-55 to 150	°C
T_{stg}	Storage temperature range		

1. *Pulse width limited by package.*
2. *I_{SD} ≤ 6.4 A, di/dt ≤ 400 A/µs, V_{DD} = 400 V, $V_{DS(peak)}$ < $V_{(BR)DSS}$.*
3. *V_{DS} ≤ 480 V.*

Table 2. Thermal data

Symbol	Parameter	Value	Unit
$R_{thj\text{-}case}$	Thermal resistance junction-case	2.08	°C/W
$R_{thj\text{-}pcb}$ (1)	Thermal resistance junction-pcb	50	°C/W

1. *When mounted on an 1 inch² FR-4, 2 Oz copper board.*

Table 3. Avalanche characteristics

Symbol	Parameter	Value	Unit
I_{AR}	Avalanche current, repetitive or non-repetitive (pulse width limited by T_{jmax})	1.4	A
E_{AS}	Single pulse avalanche energy (starting T_j = 25 °C, I_D = I_{AR}, V_{DD} = 50 V)	120	mJ

Downloaded from Arrow.com.

2 Electrical characteristics

(T_C = 25 °C unless otherwise specified)

Table 4. On /off states

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{(BR)DSS}$	Drain-source breakdown voltage	V_{GS} = 0 V, I_D = 1 mA	600			V
I_{DSS}	Zero gate voltage drain current	V_{GS} = 0 V, V_{DS} = 600 V			1	µA
		V_{GS} = 0 V, V_{DS} = 600 V, T_C=125 °C (1)			100	µA
I_{GSS}	Gate-body leakage current	V_{DS} = 0 V, V_{GS} = ±25 V			±5	µA
$V_{GS(th)}$	Gate threshold voltage	V_{DS} = V_{GS}, I_D = 250 µA	3.25	4	4.75	V
$R_{DS(on)}$	Static drain-source on-resistance	V_{GS} = 10 V, I_D = 3.2 A		520	600	mΩ

1. *Defined by design, not subject to production test.*

Table 5. Dynamic

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
C_{iss}	Input capacitance	V_{DS} = 100 V, f = 1 MHz, V_{GS} = 0 V	-	338	-	pF
C_{oss}	Output capacitance		-	26.2	-	pF
C_{rss}	Reverse transfer capacitance		-	3.88	-	pF
$C_{oss\ eq.}$ (1)	Equivalent output capacitance	V_{DS}= 0 to 480 V, V_{GS}= 0 V	-	59	-	pF
R_G	Intrinsic gate resistance	f = 1 MHz, I_D=0 A	-	7	-	Ω
Q_g	Total gate charge	V_{DD} = 480 V, I_D = 6.4 A, V_{GS} = 0 to 10 V (see Figure 14. Test circuit for gate charge behavior)	-	8.8	-	nC
Q_{gs}	Gate-source charge		-	2.7	-	nC
Q_{gd}	Gate-drain charge		-	4.8	-	nC

1. *$C_{oss\ eq.}$ is defined as a constant equivalent capacitance giving the same charging time as C_{oss} when V_{DS} increases from 0 to 80% V_{DSS}*

Table 6. Switching times

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$t_{d(on)}$	Turn-on delay time	V_{DD} = 300 V, I_D = 3.2 A, R_G = 4.7 Ω, V_{GS} = 10 V (see Figure 13. Test circuit for resistive load switching times and Figure 18. Switching time waveform)	-	11	-	ns
t_r	Rise time		-	8	-	ns
$t_{d(off)}$	Turn-off delay time		-	23	-	ns
t_f	Fall time		-	10	-	ns

Downloaded from Arrow.com.

Table 7. Source-drain diode

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
I_{SD} (1)	Source-drain current		-		6.4	A
I_{SDM} (2) (1)	Source-drain current (pulsed)		-		16.6	A
V_{SD} (3)	Forward on voltage	I_{SD} = 6.4 A, V_{GS} = 0 V	-		1.6	V
t_{rr}	Reverse recovery time	I_{SD} = 6.4 A, di/dt = 100 A/µs	-	155		ns
Q_{rr}	Reverse recovery charge	V_{DD} = 60 V (see Figure 15. Test circuit for inductive load switching and diode recovery times)	-	0.813		µC
I_{RRM}	Reverse recovery current		-	10.5		A
t_{rr}	Reverse recovery time	I_{SD} = 6.4 A, di/dt = 100 A/µs	-	250		ns
Q_{rr}	Reverse recovery charge	V_{DD} = 60 V, T_j = 150 °C	-	1.35		µC
I_{RRM}	Reverse recovery current	(see Figure 15. Test circuit for inductive load switching and diode recovery times)	-	10.8		A

1. *Limited by package.*
2. *Pulse width limited by safe operating area.*
3. *Pulsed: pulse duration = 300 µs, duty cycle 1.5%.*

Downloaded from Arrow.com.

2.1 Electrical characteristics (curves)

Figure 1. Safe operating area




Figure 2. Thermal impedance




Figure 3. Output characteristics




Figure 4. Transfer characteristics




Figure 5. Gate charge vs gate-source voltage





Figure 6. Static drain-source on-resistance



Downloaded from Arrow.com.

Figure 7. Capacitance variations




Figure 8. Normalized gate threshold voltage vs. temperature




Figure 9. Normalized on-resistance vs temperature




Figure 10. Source-drain diode forward characteristics




Figure 11. Normalized $V_{(BR)DSS}$ vs temperature





Figure 12. Output capacitance stored energy



Downloaded from Arrow.com.

3 Test circuits

Figure 13. Test circuit for resistive load switching times




Figure 14. Test circuit for gate charge behavior




Figure 15. Test circuit for inductive load switching and diode recovery times




Figure 16. Unclamped inductive load test circuit




Figure 17. Unclamped inductive waveform





Figure 18. Switching time waveform




Downloaded from Arrow.com.

4 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

4.1 DPAK (TO-252) type C package information

Figure 19. DPAK (TO-252) type C package outline



0068772_C_27


Downloaded from Arrow.com.

Table 8. **DPAK (TO-252) type C mechanical data**

Dim.	mm		
	Min.	Typ.	Max.
A	2.20	2.30	2.38
A1	0.90	1.01	1.10
A2	0.00		0.10
b	0.72		0.85
b4	5.13	5.33	5.46
c	0.47		0.60
c2	0.47		0.60
D	6.00	6.10	6.20
D1	5.25		
E	6.50	6.60	6.70
E1	4.70		
e	2.186	2.286	2.386
H	9.80	10.10	10.40
L	1.40	1.50	1.70
L1		2.90 REF	
L2	0.90		1.25
L3		0.51 BSC	
L4	0.60	0.80	1.00
L6		1.80 BSC	
θ1	5°	7°	9°
θ2	5°	7°	9°
V2	0°		8°

Downloaded from Arrow.com.


Figure 20. **DPAK (TO-252) recommended footprint (dimensions are in mm)**



Downloaded from Arrow.com.


4.2 DPAK (TO-252) packing information

Figure 21. **DPAK (TO-252) tape outline**



Downloaded from Arrow.com.

Figure 22. **DPAK (TO-252) reel outline**



AM06038v1

Table 9. **DPAK (TO-252) tape and reel mechanical data**

Tape			Reel		
Dim.	mm		Dim.	mm	
	Min.	Max.		Min.	Max.
A0	6.8	7	A		330
B0	10.4	10.6	B	1.5	
B1		12.1	C	12.8	13.2
D	1.5	1.6	D	20.2	
D1	1.5		G	16.4	18.4
E	1.65	1.85	N	50	
F	7.4	7.6	T		22.4
K0	2.55	2.75			
P0	3.9	4.1	Base qty.		2500
P1	7.9	8.1	Bulk qty.		2500
P2	1.9	2.1			
R	40				
T	0.25	0.35			
W	15.7	16.3			

Downloaded from Arrow.com.

Revision history

Table 10. **Document revision history**

Date	Revision	Changes
22-May-2019	1	First release.
26-Jun-2019	2	Added Figure 21. DPAK (TO-252) recommended footprint (dimensions are in mm).
08-May-2020	3	Deleted section DPAK (TO-252) type A package information.

Downloaded from Arrow.com.

Contents

1 **Electrical ratings** 2

2 **Electrical characteristics** 3

2.1 Electrical characteristics (curves) 5

3 **Test circuits** 7

4 **Package information** 8

4.1 DPAK (TO-252) type C package information 8

4.2 DPAK (TO-252) packing information 11

Revision history 13

Downloaded from Arrow.com.

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2020 STMicroelectronics – All rights reserved

Downloaded from Arrow.com.