



Pushing Performance  
Since 1945

# M12 PushPull male D-cod 4-pol crimpflang



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 881 1433
Specification	M12 PushPull male D-cod 4-pol crimpflang
HARTING eCatalogue	<a href="https://b2b.harting.com/21038811433">https://b2b.harting.com/21038811433</a>

## Identification

Category	Connectors
Series	Circular connectors M12
Identification	PushPull
Element	Cable connector
Specification	Straight

## Version

Termination method	Crimp termination
Gender	Male
Shielding	Shielded Shield connection with crimp flange
Number of contacts	4
Coding	D-coding
Locking type	Outer PushPull
Details	Please order crimp contacts separately. Please order crimp flange set separately.
Details	For Fast Ethernet applications only

## Technical characteristics

Conductor cross-section	0.13 ... 0.82 mm²
Conductor cross-section	AWG 26 ... AWG 18
Wire outer diameter	≤2.3 mm
Rated current	4 A



**Pushing Performance**  
Since 1945

## Technical characteristics

Rated voltage	48 V AC
	60 V DC
Rated impulse voltage	1.5 kV
Pollution degree	3
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Overvoltage category	III
Data rate	10 Mbit/s
	100 Mbit/s
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Limiting temperature	-40 ... +85 °C
Mating cycles	$\geq 500$
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Isolation group	I ( $600 \leq \text{CTI}$ )

## Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (hood/housing)	Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)



Pushing Performance  
Since 1945

Specifications and approvals

Specifications	IEC 61076-2-101
	IEC 61076-2-010

Commercial data

Packaging size	1
Net weight	53.6 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140226937
ETIM	EC002635
eCl@ss	27440116 Circular connector (for field assembly)