

1734328-1 Product Details



1734328-1

TE Part Number: 1734328-1

Active

Add to Part List

Universal Serial Bus (USB) Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Size = Mini
- AB Series
- Receptacle
- Without Locking Feature

View all Features | Find Similar Products

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product
- Request Samples

NEW!

Documentation & Additional Information	
Product Drawings: - MINI USB CONN., TYPE AB, RCPT, 5 POS., RIGHT ANGLE, SMT (PDF, English) Catalog Pages/Data Sheets: - None Available Product Specifications: - MINI USB SERIES. (PDF, English) Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: (CAD Format & Compression Information) 2D Drawing (DXF, Version A) 3D Model (IGES, Version A) 3D Model (STEP, Version A) List all Documents	Additional Information: - Product Line Information Related Products: - Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - Product Type = Connector - Size = Mini - Gender = Receptacle - Number of Ports = 1 - Orientation = Right Angle - PCB Thickness (mm [in]) = 1.57 [0.062] - Number of Positions = 5 Mechanical Attachment: - Mount Location = Top Termination Related Features: - Termination Method = Solder to PC Board Body Related Features: - Series = AB - Locking Feature = Without - Panel Ground = Without - PCB Retention Method = SMT Hold Down - Shell Plating = Nickel over Copper - Pick and Place Cover = Without - Locating Posts = With	Contact Related Features: - Contact Termination Type = Surface Mount - Contact Mating Area Plating Material = Gold - Contact Mating Area Plating Thickness = 30 Microinches Housing Related Features: - Housing Color = Black Industry Standards: - RoHS/ELV Compliance = RoHS compliant, ELV compliant - Lead Free Solder Processes = Reflow solder capable to 245°C, Reflow solder capable to 260°C - RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: - Terminate To = Printed Circuit Board Packaging Related Features: - Packaging Method = Tray Other: - Brand = AMP