



Part Number : [2074790004](#)
Product Description : KK Plus 396 Header,
3.96mm Pitch, Vertical, Fully Shrouded, Tin
(Sn) Plating, 4 Circuits, with Peg
Series Number : 207479
Status : Active
Product Category : PCB Headers and
Receptacles



Documents & Resources

Drawings

[2074790004_sd.pdf](#)
[2074790000-PK-000.pdf](#)

3D Models and Design Files

[2074790004_stp.zip](#)
[SYM-207479-0004-001.zip](#)

Specifications

[2074580000-AS-000.pdf](#)
[2074580000-PS-000.pdf](#)
[2074580000-PS-CH-000.pdf](#)
[2074580000-PS-ES-000.pdf](#)
[2074580000-PS-JP-000.pdf](#)
[2074580000-PS-SK-000.pdf](#)
[2074580000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	207479
Description	KK Plus 396 Header, 3.96mm Pitch, Vertical, Fully Shrouded, Tin (Sn) Plating, 4 Circuits, with Peg
Application	Power, Wire-to-Board
Component Type	PCB Header
Product Name	KK Plus
UPC	191130109890

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	11.0A
Voltage - Maximum	350V AC/DC

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black

Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	2.090/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PC Tail Length	3.50mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK Plus 396 Single Row Receptacle Housings	<u>207458</u>

This document was generated on Apr 07, 2025