



Pushing Performance
Since 1945

Han 1 HC-M-TC350



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 001 3001
Specification	Han 1 HC-M-TC350
HARTING eCatalogue	https://harting.com/09110013001

Identification

Category	Inserts
Series	Han [®] HC Modular
Identification	350

Version

Termination method	Crimp termination
Gender	Male
Details	Please order crimp contacts separately.
Details	The vibration and shock resistance can only be met if the cables are fixed at an appropriate distance. Instructions for the spacing of strain relief can be found in the document in eCatalogue under the section Instructions.

Technical characteristics

Conductor cross-section	25 ... 120 mm ²
Wire outer diameter	≤22 mm
Rated current	350 A
Rated voltage	2,000 V
Rated impulse voltage	12 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Vibration resistance	Category 2 acc. to IEC 61373



Pushing Performance
Since 1945

Technical characteristics

Shock resistance	Category 2 acc. to IEC 61373
------------------	------------------------------

Material properties

Material (insert)	Polycarbonate (PC) Polyamide (PA)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	a4a9de28-6060-4c0d-b79b-5842f7db41be
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R23 (HL 1-3) R22 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	30 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140016125
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522