



**Part Number :** [349600200](#)

**Product Description :** Mini50 Unsealed 2 Bay Right-Angle Headers, 68 Circuits, Bay A 34 Circuit Hybrid, Polarization A, Black; Bay B 34 Circuit Hybrid, Polarization B, Gray; Tray

**Series Number :** 34960

**Status :** Obsolete

**Product Category :** PCB Headers and Receptacles



---

## Documents and Resources

### Drawings

[349600200 sd.pdf](#)

[PK-31302-070-001.pdf](#)

### Specifications

[349590001-AS-CH-000.pdf](#)


[PS-34959-001-001.pdf](#)

[TS-34961-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Obsolete
Category	PCB Headers and Receptacles
Series	34960
Description	Mini50 Unsealed 2 Bay Right-Angle Headers, 68 Circuits, Bay A 34 Circuit Hybrid, Polarization A, Black; Bay B 34 Circuit Hybrid, Polarization B, Gray; Tray
Application	Automotive, Power, Signal, Wire-to-Board
Comments	0.50mm blades = 4.0A; 1.20mm blades = 16.0A
Component Type	PCB Header
Product Name	Mini50
UPC	887191714967

### Electrical

Current - Maximum per Contact	16.0A, 4.0A
Voltage - Maximum	500V DC

### Physical

Breakaway	No
Circuits (Loaded)	68
Circuits (maximum)	68
Color - Resin	Black, Gray

Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	SPS
Net Weight	13.790/g
Number of Rows	3
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	No
PC Tail Length	2.75mm
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Mini50 Unsealed Receptacle Housings	<u>34959</u>

---

This document was generated on Apr 13, 2026