

4


3

2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
EH			H1	REVISED PER ECO-11-005140	31MAR11	RK	HMR

D



C

- CABLE CERTIFIED TO:
-UL CABLE STYLE: 2678
- CABLE PHYSICAL SPECIFICATIONS:
 - TEMPERATURE RATING: -20°C TO +105°C
 - FLAMMABILITY:
-UL: VW1
 - INSULATION: GRAY FLAME RETARDANT FLEXIBLE PVC
 - CONDUCTORS: #30 AWG 7/38 STRANDED TINNED COPPER
- ELECTRICAL REQUIREMENTS:
 - VOLTAGE: 150 VOLTS
 - IMPEDANCE: 66 OHMS
 - CAPACITANCE: 23 pF/FT AT 1 KHZ
 - PROPAGATION DELAY: 1.55 ns/FT
 - INSULATION RESISTANCE: 10¹⁰ OHMS/10 FT
 - CROSSTALK: 10 FT SAMPLE 5 ns RISE TIME (GND, SIG, GND)
NEAR END: 2.8%
FAR END: 4.5%

B

- 4 RED EDGE MARK ON CONDUCTOR #1
- 5 LENGTH PER REEL: 100 FT, REEL MAY CONTAIN SEPARATE LENGTHS
20 FT MIN PER LENGTH
- 6 LENGTH PER REEL: 500 FT, CONTINUOUS.
7. CABLE SURFACE PRINTED PER UL AND CSA REQUIREMENTS.

A

- 8 DIMENSION A TOLERANCES
0-68 POSN +.005-.003
69-100 POSN + .007- .003

6	.400	.375	16	5-57131-0	
5	.400	.400	16	4-57131-9	
6	.675	.700	28	4-57131-7	
5	.675	.700	28	4-57131-6	
6	.625	.650	26	2-57131-6	
5	.625	.650	26	2-57131-5	
↑	2.475	2.500	100	2-57131-4	
	1.975	2.000	80	2-57131-3	
	1.775	1.800	72	2-57131-2	
	1.675	1.700	68	2-57131-1	
	1.475	1.500	60	2-57131-0	
	1.225	1.250	50	1-57131-9	
	1.075	1.100	44	1-57131-8	
	.975	1.000	40	1-57131-7	
	.875	.900	36	1-57131-6	
	.725	.750	30	1-57131-5	
	.575	.600	24	1-57131-4	
	5	.475	.500	20	1-57131-3
	6	1.775	1.800	72	1-57131-2
	↑	1.675	1.700	68	1-57131-1
		1.225	1.250	50	1-57131-0
		1.075	1.100	44	57131-9
.575		.600	24	57131-8	
.875		.900	36	57131-7	
.725		.750	30	57131-6	
2.475		2.500	100	57131-5	
1.975		2.000	80	57131-4	
1.475		1.500	60	57131-3	
.975		1.000	40	57131-2	
6	.475	.500	20	57131-1	
REEL LENGTH	DIMENSION A	DIMENSION B	NO. OF CONDS	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.GROENDYK 05MAY93	TE Connectivity		
		CHK L.CONLEY 05MAY93			
		APVD M.RUBERA 05MAY93			
		PRODUCT SPEC			
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPLICATION SPEC	NAME		
	0 PLC ± 1 PLC ±.1 2 PLC ±.02 3 PLC ±.005 4 PLC ±.0005 ANGLES ± FINISH	WEIGHT	CABLE, F RBN, .025CL, 30AWG, 7/38 STRD, TND, PVC INSUL		
MATERIAL		CUSTOMER DRAWING	SIZE A2	CAGE CODE 00779	DRAWING NO 57131
			RESTRICTED TO		
			SCALE NTS	SHEET 1 OF 1	REV H1

D

C

I

B

A