

Terminal Part Number: 15336260
Surface Plating: SN
Material Thickness [mm]: 0,30
Cross Section [mm²]: 2,00 | 3,00

This document is non-contractual
and for information only.

For more information, please
consult your local sales office



Cable Type codes: 1005
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 2,45 - 3,25
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1005 2,00		2,58	200	1,60	0,05	2,85	0,10	2,80	0,10	3,60	0,10
1005 3,00		3,13	240	1,80	0,05	2,85	0,10	3,40	0,10	3,70	0,10

Cable type code legend:

1005:

Industry Designator: SAE
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PVC, PVDF, XLPE
Insul. Wall Designator: THIN



Crimp Information Sheet

DELPHI

Terminal Part Number: 15336260
Surface Plating: SN
Material Thickness [mm]: 0,30
Cross Section [mm²]: 1,50 | 2,00 | 2,50

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*

Cable Type codes: 2010
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ [mm]: 2,00 - 3,00
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2010 1,50		2,20	200	1,70	0,05	2,60	0,10	2,90	0,10	3,60	0,10
2010 2,00		2,46	230	1,80	0,05	2,60	0,10	3,00	0,10	3,60	0,10
2010 2,50		2,80	250	1,90	0,05	2,60	0,10	3,10	0,10	3,60	0,10

Cable type code legend:

2010: ACW0219, FIAT T2 FLRY, FL RENAULT R1, FL RENAULT R3, FLR
(AGP0219), FLR2X-A, FLR4Y-A, FLR9Y, FLRX-B, FLRY-A, FLRYB, FLRY-B



Industry Designator: DIN

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PA, POLYOLEFIN, PP, PVC, SYNTHRESIN, XLCOPOLY, XLPBT, XLPE,
XLPE/PVDF, XLPVC

Insul. Wall Designator: THIN



Terminal Part Number: 15336260
Surface Plating: SN
Material Thickness [mm]: 0,30
Cross Section [mm²]: 1,50 | 2,50

This document is non-contractual
and for information only.



For more information, please
consult your local sales office

Cable Type codes: 2017
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 2,00 - 3,00
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2017 1,50		2,20	200	1,70	0,05	2,60	0,10	2,90	0,10	3,60	0,10
2017 2,50		2,80	250	1,90	0,05	2,60	0,10	3,10	0,10	3,60	0,10

Cable type code legend:

2017: FLR41X-B, FLRY-A
Industry Designator: DIN
Conductor Material: COPPER
Conductor Plating: SN
Insul. Material: PA, PP, PVC, XLPE
Insul. Wall Designator: THIN



Terminal Part Number: 15336260
Surface Plating: SN
Material Thickness [mm]: 0,30
Cross Section [mm²]: 2,00

*This document is non-contractual
and for information only.*



*For more information, please
consult your local sales office*

Cable Type codes: 3003
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 2,50 - 2,80
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
3003 2,00		2,65	180	1,60	0,05	2,80	0,10	2,90	0,10	3,60	0,10

Cable type code legend:

3003: AVSS
Industry Designator: JIS/JA
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PVC, X-PVC
Insul. Wall Designator: THIN



Terminal Part Number: 15336260
Surface Plating: SN
Material Thickness [mm]: 0,30
Cross Section [mm²]: 1,25

*This document is non-contractual
and for information only.*



*For more information, please
consult your local sales office*

Cable Type codes: 3004
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 2,00 - 2,20
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
3004 1,25		2,10	135	1,40	0,05	2,80	0,10	2,70	0,10	3,60	0,10

Cable type code legend:

3004: AVSS
Industry Designator: JIS/JA
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PVC, XLPE, X-PVC
Insul. Wall Designator: THIN



Terminal Part Number: 15336260
Surface Plating: SN
Material Thickness [mm]: 0,30
Cross Section [mm²]: 1,50 | 2,50

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable Type codes: 8000
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 2,20 - 3,00
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
8000 1,50		2,30	160	1,50	0,05	2,80	0,10	2,70	0,10	3,60	0,10
8000 2,50		2,85	225	1,75	0,05	2,85	0,10	2,90	0,10	3,60	0,10

Cable type code legend:

8000:

Industry Designator: N/G
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: SYNTHRESIN
Insul. Wall Designator: THIN

