



**Pushing Performance**  
Since 1945

# Set PP LC duplex MM GOF



Image is for illustration purposes only. Please refer to product description.

Part number	09 57 402 0500 000
Specification	Set PP LC duplex MM GOF

## Identification

Category	Connectors
Series	HARTING PushPull (V4)
Identification	LC duplex
Element	Connector sets
Description of the contact	Multimode

## Version

Number of contacts	2
Locking type	PushPull

## Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥200
Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	5.8 ... 7.2 mm

## Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption



**Pushing Performance**  
Since 1945

## Material properties

RoHS exemptions	6(b) / 6(b)-II: Lead as an alloying element in aluminium containing up to 0,4 % lead by weight / Lead as an alloying element in aluminium for machining purposes with a lead content up to 0,4 % by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide Lead Nickel Naphthalene
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	59 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140072596
eCl@ss	27440114 Rectangular connector (for field assembly)