



CW-B7571

REV	DOCUMENT	CHANGED BY	CHECK
3	202161	TSM 19JAN01	SAV
4	207439	TSM 13FEB03	SAV



CHARACTERISTICS		ELECTRICAL DATA		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:		DRAWN		TSM		19 JAN 01		Honeywell							
OPERATING FORCE---- 73 GRAMS MAX		CONTACT ARRANGEMENT S P D T		☒ US (inch) CUSTOMARY ☐ SI (mm) METRIC		CHECK		SAV		19 JAN 01									
RELEASE FORCE ----- 5 GRAMS MIN		21A 1HP 125, 250, 277 VAC 2HP 250, 277 VAC 16 (4) 250 1E5 μ ~ CE UL ® CS		NO PLACE X ±.040 ±1		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.						TITLE SWITCH, BASIC							
DIFFERENTIAL TRAVEL----- .038 MAX				ONE PLACE .X ±.030 ±0,4															
OVERTRAVEL ----- .092 MIN				TWO PLACE .XX ±.015 ±0,15		DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED						SIZE		DWG TYPE		DRAWING NAME		REV	
RELEASE TRAVEL ----- .022 MIN				THREE PLACE .XXX ±.005 ±								THIRD ANGLE PROJECTION		B		I		V7-1V19E9-269	
						PTC 2D		ASME Y14.5M-1994		SCALE 2 : 1		WEIGHT		SHEET 1 OF 1					