



Pushing Performance  
Since 1945

## ix Type A 4x2xAWG26/7 PUR 7.5m




Image is for illustration purposes only. Please refer to product description.

Part number	33 48 010 1804 075
Specification	ix Type A 4x2xAWG26/7 PUR 7.5m
HARTING eCatalogue	<a href="https://harting.com/33480101804075">https://harting.com/33480101804075</a>

### Identification

Category	System cabling
Series	HARTING ix Industrial®
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING ix Industrial® Type A
Connector 2	HARTING ix Industrial® Type A
Type of cable	Copper cable (round)

### Version

Cable length	7.5 m
Number of cores	8
Core structure	4x 2x AWG 26/7
Termination method	IDC insulation displacement termination
Coding	Type A

### Technical characteristics

Transmission characteristics	Cat. 6A Class E <sub>A</sub> up to 500 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s



Pushing Performance  
Since 1945

Technical characteristics

Limiting temperature	-40 ... +80 °C unmoved
	-40 ... +80 °C moved

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Yellow

Specifications and approvals

Specifications	IEC 60332-1-2 Flame retardancy
	IEC 60754-1 Halogen freeness
	EN 60811-404 Oil resistance
	UN/ECE-R 118 fire protection for rolling stock

Commercial data

Packaging size	1
Net weight	300 g
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140259591
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600