

Vibro Motor Click



PID: MIKROE-2826

Vibro Motor click features a compact size Eccentric Rotating Mass (ERM) motor, labeled as [C1026B002F](#). This type of motor is often used for haptic feedback on many small handheld devices, such as the cellphones, pagers, RFID scanners and similar devices. This motor contains a small eccentric weight on its rotor, so while rotating it also produces vibration effect. This kind of motors is sometimes referred to as coin motors, due to its shape.

Besides the vibration motor, the click is also equipped with the DMG3420U, a small MOSFET, which is used to drive the motor. The Vibro Motor click is an ideal solution for adding a simple, one pin driven haptic feedback on any design.

Vibro Motor click features a compact size Eccentric Rotating Mass (ERM) motor, labeled as [C1026B002F](#). This type of motor is often used for haptic feedback on many small handheld devices, such as the cellphones, pagers, RFID scanners and similar devices. This motor contains a small eccentric weight on its rotor, so while rotating it also produces vibration effect. This kind of motors is sometimes referred to as coin motors, due to its shape.

Besides the vibration motor, the click is also equipped with the DMG3420U, a small MOSFET, which is used to drive the motor. The Vibro Motor click is an ideal solution for adding a simple, one pin driven haptic feedback on any design.

How does it work?

The click uses the DMG3420U MOSFET to drive the ERM motor, since the MCU itself cannot provide enough power for the motor driving. The circuit also contains a protection diode, which

Mikroe produces entire development toolchains for all major microcontroller architectures.

Committed to excellency, we are dedicated to helping engineers bring the project development up to speed and achieve outstanding results.



ISO 27001: 2013 certification of informational security management system.
ISO 14001: 2015 certification of environmental management system.
OHSAS 18001: 2008 certification of occupational health and safety management system.



ISO 9001: 2015 certification of quality management system (QMS).

is used to protect the transistor from the reverse voltage, since the motor represents an inductive load and turning off its current can produce a kickback voltage that can damage the transistor.

The gate of the MOSFET is driven by the PWM signal, routed through the PWM pin of the mikroBUS™. The PWM signal toggles the gate of the MOSFET with the pulses of a certain width. As a result, the current through the motor is varied depending on the pulse width of the PWM signal, which directly affects the speed of the motor, effectively controlling the vibration force that way. The small, eccentric weight attached to the rotor of the coin motor, generates the centrifugal force while it rotates, which in turn results with the wobbling effect of the motor itself. The faster the rotation is, the bigger the force gets. Controlling the motor speed allows for the vibration intensity to be controlled.

MikroElektronika library contains functions that are used to easily drive the motor by changing the PWM pulse width, saving time for the application firmware development.

Specifications

Type	Haptic
Applications	An ideal solution for adding a simple, one pin driven haptic feedback on any design.
On-board modules	C1026B002F Eccentric Rotating Mass (ERM) motor
Key Features	Low power consumption, compact size
Interface	PWM
Feature	No ClickID
Compatibility	mikroBUS™
Click board size	M (42.9 x 25.4 mm)
Input Voltage	3.3V

Pinout diagram

This table shows how the pinout on **Vibro Motor click** corresponds to the pinout on the mikroBUS™ socket (the latter shown in the two middle columns).

Notes	Pin					Pin	Notes
	NC	1	AN	PWM	16	PWM	Motor speed control
	NC	2	RST	INT	15	NC	
	NC	3	CS	RX	14	NC	
	NC	4	SCK	TX	13	NC	
	NC	5	MISO	SCL	12	NC	
	NC	6	MOSI	SDA	11	NC	
Power supply	3V3	7	3.3V	5V	10	NC	

Mikroe produces entire development toolchains for all major microcontroller architectures.

Committed to excellency, we are dedicated to helping engineers bring the project development up to speed and achieve outstanding results.



ISO 27001: 2013 certification of informational security management system.
ISO 14001: 2015 certification of environmental management system.
OHSAS 18001: 2008 certification of occupational health and safety management system.



ISO 9001: 2015 certification of quality management system (QMS).

Ground	GND	8	GND	GND	9	GND	Ground
--------	------------	---	-----	-----	---	------------	--------

Vibro Motor click specifications

Description	Min	Typ	Max	Unit
Rated ERM motor speed	9000			RPM
Bracket deflection strength		9.8		N
Mechanical noise			50	dB
Operating Temperature	-20		+60	°C

Onboard settings and indicators

Label	Name	Default	Description
VM	Vibro motor	-	Vibration motor
PWR	Power LED	-	Power LED indicator

Software support

We provide an example for Vibro Motor click on our [LibStock](#) page, as well as a demo application (example), developed using MikroElektronika [compilers](#). The demo can run on all the main MikroElektronika [development boards](#).

Examples description

This demo application demonstrates how to control Vibro Motor click by using the MCU's PWM module. The demo application is composed of two sections:

- systemInit - Initializes the PWM module
- applicationTask - Sequential call of each pattern with 1 second delay in between

Additional functions:

void vibromotor_pattern1(uint8_t loops)- Long vibration pattern - 1 second vibration + 1 second delay

void vibromotor_pattern2(uint8_t loops)- Short vibration pattern - 200 ms vibration + 500 ms delay

The full application code and ready to use projects can be found on our [LibStock](#) page.

Other mikroE Libraries used in the example:

- PWM

Additional notes and information

Depending on the development board you are using, you may need [USB UART click](#), [USB UART 2 click](#) or [RS232 click](#) to connect to your PC, for development systems with no UART to USB interface available on the board. The terminal available in all MikroElektronika [compilers](#), or

Mikroe produces entire development toolchains for all major microcontroller architectures.

Committed to excellency, we are dedicated to helping engineers bring the project development up to speed and achieve outstanding results.



ISO 27001: 2013 certification of informational security management system.
ISO 14001: 2015 certification of environmental management system.
OHSAS 18001: 2008 certification of occupational health and safety management system.



ISO 9001: 2015 certification of quality management system (QMS).

any other terminal application of your choice, can be used to read the message.

mikroSDK

This click board is supported with mikroSDK, the MikroElektronika Software Development Kit. To download mikroSDK visit [LibStock](#). For more information about SDK, visit the [official page](#).

Resources

[mikroBUS™ standard specifications](#)

[Click board™ Catalog](#)

[Click Boards™](#)

Downloads

[Vibro Motor click example on Libstock](#)

[C1026B002F datasheet](#)

[Vibro Motor click schematic](#)

[Vibro Motor click 2D and 3D files](#)

Mikroe produces entire development toolchains for all major microcontroller architectures.

Committed to excellency, we are dedicated to helping engineers bring the project development up to speed and achieve outstanding results.



ISO 27001: 2013 certification of informational security management system.
 ISO 14001: 2015 certification of environmental management system.
 OHSAS 18001: 2008 certification of occupational health and safety management system.



ISO 9001: 2015 certification of quality management system (QMS).