

Product data sheet

Specifications



APC Smart-UPS On-Line, 10kVA/
10kW, Rackmount 10U, 208V, 2x
L5-20R+4x L6-20R+2x L6-30R+2x
L14-30R NEMA, NMC, W/
transformer 208V/240V to 120V, W/
rail kit

SRT10KRMXLT-10KTF

Overview

Lead time Usually in Stock

Main

Main Input Voltage	208 V AC 1 phase 240 V AC 1 phase
Input voltage	240 V
Input voltage limits	100...275 V adjustable (half load)
Number of input connectors	1 hard wire 3-wire (2P + E)
Network frequency	40...70 Hz auto-sensing
Output voltage	120 V 1 phase 208 V 1 phase 240 V 1 phase
Output voltage	240 V
Rated power in W	10000 W
rated power in VA	10000 VA
Output connection type	2 NEMA L5-20R 4 NEMA L6-20R 2 NEMA L6-30R 2 NEMA L14-30R
Output connector type	Hard wire 3-wire (2P + E) for 1 zone(s) Hard wire 4-wire (2P + N + E) for 1 zone(s)
Bypass type	Internal bypass (automatic and manual)
Crest factor	3 : 1
Harmonic distortion	Less than 2 %
Maximum configurable power in VA	10000 VA
Maximum configurable power in W	10000 W
UPS type	On-Line
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Complementary

Battery type	Lead-acid internal included
Emergency power off	Yes




Free slots	1
Preinstalled device	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity
UPS connectivity	Serial port USB port Embedded network management card 3
Surge energy rate	480 J
Number of rack unit	10U
Colour	Black
Height	438 mm
Width	432 mm
Depth	749 mm
Net weight	211.37 kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted
Two post mountable	0
USB compatible	Yes
Mounting position	Horizontal
Mounting mode	Rack-mounted with included kit
Provided equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack mounting brackets Rack mounting support rails Temperature probe USB cable Warranty card Web/SNMP management card
Number of power module filled slots	0
Number of power module free slots	0
Additional specification	High density
Redundant	No
Range of product	Smart-UPS On-Line
Product or component type	Uninterruptible power supply (UPS)

Environment

Product certifications	ENERGY STAR V2.0 (USA) FCC part 15 class A UL 1778
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0...15240 m
IP degree of protection	IP20
Relative humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing

Acoustic level	55 dBA
Heat dissipation	2490 Btu/h
Operating altitude	0...10000 ft

Batteries & Runtime

Run Time	View Runtime Graph 
Efficiency	View Efficiency Graph 
Battery type	Lead-acid battery
Battery voltage	+/- 192 V (split battery referenced to neutral)
Extended runtime	1
Number of battery filled slots	0
Battery recharge time	1.5 h
Number of battery replacement quantity	2
Battery life	3...5 year(s)
Replacement battery	APCRBC140 
Battery charger power	1191 W rated

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	86.7 cm
Package 1 Width	100 cm
Package 1 Length	60 cm
Package 1 Weight	254.47 kg

Contractual warranty

Warranty (in months)	24 Battery 36 UPS
----------------------	-------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	22 229 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	3 153 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	35 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	19 011 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	31 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov



Energy efficiency



ENERGY STAR®

ENERGY STAR UPS V2.0 (USA)

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	65
End of life manual availability	End of Life Information
Removable battery	User replaceable
Take-back	No

Image of product / Alternate images

Alternative





