


SKKT 330, SKKH 330



SEMIPACK® 3

Thyristor / Diode Modules

SKKH 330

SKKT 330

Features

- Heat transfer through aluminium nitride ceramic isolated metal baseplate
- Precious metal pressure contacts for high reliability
- Thyristor with amplifying gate
- UL recognized, file no. E 63 532


Typical Applications*

- DC motor control (e. g. for machine tools)
- Temperature control (e. g. for ovens, chemical processes)
- Professional light dimming (studios, theaters)

1) See the assembly instruction

V_{RSM} V	V_{RRM}, V_{DRM} V	$I_{TRMS} = 510 \text{ A}$ (maximum value for continuous operation) $I_{TAV} = 330 \text{ A}$ (sin. 180; $T_c = 80 \text{ °C}$)		
900	800	SKKT 330/08E	SKKH 330/08E	
1300	1200	SKKT 330/12E	SKKH 330/12E	
1700	1600	SKKT 330/16E	SKKH 330/16E	
1900	1800	SKKT 330/18E	SKKH 330/18E	

Symbol	Conditions	Values	Units
I_{TAV}	sin. 180; $T_c = 85 (100) \text{ °C}$;	305 (225)	A
I_D	P16/200F; $T_a = 35 \text{ °C}$; B2 / B6	520 / 650	A
I_{RMS}	P16/200F; $T_a = 35 \text{ °C}$; W1 / W3	585 / 3 * 485	A
I_{TSM}	$T_{vj} = 25 \text{ °C}$; 10 ms	9500	A
	$T_{vj} = 130 \text{ °C}$; 10 ms	8000	A
i^2t	$T_{vj} = 25 \text{ °C}$; 8,3 ... 10 ms	451000	A²s
	$T_{vj} = 130 \text{ °C}$; 8,3 ... 10 ms	320000	A²s
V_T	$T_{vj} = 25 \text{ °C}$; $I_T = 750 \text{ A}$	max. 1,4	V
$V_{T(TO)}$	$T_{vj} = 130 \text{ °C}$	max. 0,8	V
r_T	$T_{vj} = 130 \text{ °C}$	max. 0,6	mΩ
I_{DD}, I_{RD}	$T_{vj} = 130 \text{ °C}$; $V_{RD} = V_{RRM}$; $V_{DD} = V_{DRM}$	max. 85	mA
t_{gd}	$T_{vj} = 25 \text{ °C}$; $I_G = 1 \text{ A}$; $di_G/dt = 1 \text{ A/μs}$	1	μs
t_{gr}	$V_D = 0,67 * V_{DRM}$	2	μs
$(di/dt)_{cr}$	$T_{vj} = 130 \text{ °C}$	max. 250	A/μs
$(dv/dt)_{cr}$	$T_{vj} = 130 \text{ °C}$	max. 1000	V/μs
t_q	$T_{vj} = 130 \text{ °C}$	50 ... 150	μs
I_H	$T_{vj} = 25 \text{ °C}$; typ. / max.	150 / 500	mA
I_L	$T_{vj} = 25 \text{ °C}$; $R_G = 33 \text{ Ω}$; typ. / max.	300 / 2000	mA
V_{GT}	$T_{vj} = 25 \text{ °C}$; d.c.	min. 3	V
I_{GT}	$T_{vj} = 25 \text{ °C}$; d.c.	min. 200	mA
V_{GD}	$T_{vj} = 130 \text{ °C}$; d.c.	max. 0,25	V
I_{GD}	$T_{vj} = 130 \text{ °C}$; d.c.	max. 10	mA
$R_{th(j-c)}$	cont.; per thyristor / per module	0,11 / 0,055	K/W
$R_{th(f-c)}$	sin. 180; per thyristor / per module	0,116 / 0,058	K/W
$R_{th(j-c)}$	rec. 120; per thyristor / per module	0,13 / 0,065	K/W
$R_{th(c-s)}$	per thyristor / per module	0,04 / 0,02	K/W
T_{vj}		- 40 ... + 130	°C
T_{stg}		- 40 ... + 130	°C
V_{isol}	a. c. 50 Hz; r.m.s.; 1 s / 1 min.	3600 / 3000	V~
M_s	to heatsink	5 ± 15 % ¹⁾	Nm
M_t	to terminals	9 ± 15 %	Nm
a		5 * 9,81	m/s²
m	approx.	600	g
Case	SKKT SKKH	A 73b A 76b	



SKKT



SKKH




Fig. 1L Power dissipation per thyristor vs. on-state current




Fig. 1R Power dissipation per thyristor vs. ambient temp.




Fig. 2L Power dissipation per module vs. rms current




Fig. 2R Power dissipation per module vs. case temp.




Fig. 3L Power dissipation of two modules vs. direct current














Fig. 3R Power dissipation of two modules vs. case temp.

SKKT 330, SKKH 330





This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, chapter IX.

***IMPORTANT INFORMATION AND WARNINGS**

The specifications of SEMIKRON products may not be considered as guarantee or assurance of product characteristics ("Beschaffenheitsgarantie"). The specifications of SEMIKRON products describe only the usual characteristics of products to be expected in typical applications, which may still vary depending on the specific application. Therefore, products must be tested for the respective application in advance. Application adjustments may be necessary. The user of SEMIKRON products is responsible for the safety of their applications embedding SEMIKRON products and must take adequate safety measures to prevent the applications from causing a physical injury, fire or other problem if any of SEMIKRON products become faulty. The user is responsible to make sure that the application design is compliant with all applicable laws, regulations, norms and standards. Except as otherwise explicitly approved by SEMIKRON in a written document signed by authorized representatives of SEMIKRON, SEMIKRON products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury. No representation or warranty is given and no liability is assumed with respect to the accuracy, completeness and/or use of any information herein, including without limitation, warranties of non-infringement of intellectual property rights of any third party. SEMIKRON does not assume any liability arising out of the applications or use of any product; neither does it convey any license under its patent rights, copyrights, trade secrets or other intellectual property rights, nor the rights of others. SEMIKRON makes no representation or warranty of non-infringement or alleged non-infringement of intellectual property rights of any third party which may arise from applications. Due to technical requirements our products may contain dangerous substances. For information on the types in question please contact the nearest SEMIKRON sales office. This document supersedes and replaces all information previously supplied and may be superseded by updates. SEMIKRON reserves the right to make changes.