

Han PP Power L plug metal fix coding



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 431 0401
Specification	Han PP Power L plug metal fix coding
HARTING eCatalogue	https://b2b.harting.com/09354310401

Identification

Category	Connectors
Series	Han® PushPull (V14)
Identification	Power L
Element	Connector sets
Specification	AIDA compliant With fixed coding Finger safe
Features	Intuitive locking mechanism field assembly without tools

Version

Termination method	Spring clamp termination
Shielding	Unshielded
Number of contacts	5
Locking type	PushPull

Technical characteristics

Conductor cross-section	0.75 ... 2.5 mm²
Conductor cross-section	AWG 18 ... AWG 13
Rated current	16 A
Rated voltage	24 V
Rated impulse voltage	4 kV
Pollution degree	3



Pushing Performance
Since 1945

Technical characteristics

Stripping length	10 mm Conductors 44 mm cable jacket
Tightening torque	3 Nm
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	9 ... 13 mm

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side Sn over Ni Termination side
Material (hood/housing)	Metal
Material (O-ring)	NBR
Material (internal seal)	NBR
Material (cable seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-117 Variant 14 (V14)
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079 UL 1059 XCFR2.E314677 CSA-C22.2 No. 158-10 XCFR8.E314677
PROFINET	Yes

Commercial data

Packaging size	1
----------------	---



Pushing Performance
Since 1945

Commercial data

Net weight	96.2 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140054523
eCl@ss	27440114 Rectangular connector (for field assembly)

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.
Measuring and testing techniques acc. to IEC 60512-5-2

