




DWG. NO.

SYM.	DCN NO.	DESCRIPTION	DATE	DRAWN	CHECKED	APP' D	APP' D



DESCRIPTION	APPLICABLE WIRE		AWG# MARK
	WIRE SIZE	OUTER DIA. OF INSUL.	
D02-22-22S-10000	AWG#22~24	1.3 ^{DIA.} MAX.	22
D02-22-26S-10000	AWG#26~28	1.1 ^{DIA.} MAX.	26

NOTE 1. CONTACT TO BE SUPPLIED IN REELED FORM.

(10,000 CONTACT/REEL)

2. NUMBER OF CONTACTS TO BE SHOWN ON THIS PORTION.

3. LABEL SHOWING PART NUMBER & Q'TY TO BE PUT
ON THIS PORTION.

3	SOCKET CONTACT	10000	COPPER ALLOY	GOLD OVER NICKEL	
2	PAPER TAPE	1	PAPER		
1	MAGAZINE	1	PAPER		
ITEM	DESCRIPTION	Q'TY	MATERIAL	FINISH	REMARKS
REFERENCE DOCUMENT		DATE	SCALE	JAE-CONNECTOR CON	
JACS-3050-2		30. OCT. '90	10:1	JAE-CONNECTOR CON Reference Only	
MATERIAL	DRAWN	TITLE			
	H. KATO	D02-22-22S-10000			
	CHECKED	D02-22-26S-10000			
TREATMENT	APP'D	DWG. NO.			
FINISH	APP'D	S J 0 2 1 5 0 8 - E			

CDS-1201

SIZE 37 A3

DDCF-116A

DIMENSIONS ARE IN MILLIMETERS	
TOLERANCES ON: [INCHES]	
<u>DIMENSION</u>	<u>ANGLES</u>
. ± 0.3	° ±
.X ± 0.3	°X ±
.XX ±	
.XXX ±	
.XXXX ±	
	<u>CONCENTRICITY</u>
	WITHIN T. 1. R.

JAE-CONNECTOR.COM

Reference Only

MUSASHINO, AKISHIMA-SHI
TOKYO, JAPAN

DWG.	NQ.
------	-----

SJ021508-E