


CBRLDSH2-40

**SURFACE MOUNT  
HIGH DENSITY  
2 AMP SILICON  
SCHOTTKY BRIDGE RECTIFIER**



**LPDIP CASE**



[www.centrasemi.com](http://www.centrasemi.com)

**DESCRIPTION:**

The CENTRAL SEMICONDUCTOR CBRLDSH2-40 is a full wave Schottky bridge rectifier mounted in a low profile epoxy surface mount molded case, utilizing glass passivated chips.

**MARKING CODE: CL40**

**APPLICATIONS:**

- Input rectification
- Polarity protection
- Steering diode array

**FEATURES:**

- Low leakage current (5.5 $\mu$ A TYP @  $V_{RRM}$ )
- High 2.0A current rating
- Low  $V_F$  Schottky diodes (480mV TYP @  $I_F=2.0A$ )
- Low profile package (1.6mm MAX)

**MAXIMUM RATINGS:** ( $T_A=25^{\circ}C$  unless otherwise noted)

Peak Repetitive Reverse Voltage

DC Blocking Voltage

RMS Reverse Voltage

Average Forward Current ( $T_L=50^{\circ}C$ )

Peak Forward Surge Current

Operating Junction Temperature

Storage Temperature

Thermal Resistance

**SYMBOL**

$V_{RRM}$

$V_R$

$V_{R(RMS)}$

$I_O$

$I_{FSM}$

$T_J$

$T_{stg}$

$\Theta_{JA}$

40

40

28

2.0

50

-55 to +125

-55 to +150

95

**UNITS**

V

V

V

A

A

$^{\circ}C$

$^{\circ}C$

$^{\circ}C/W$

**ELECTRICAL CHARACTERISTICS PER DIODE:** ( $T_A=25^{\circ}C$  unless otherwise noted)

**SYMBOL**      **TEST CONDITIONS**

$I_R$        $V_R=40V$

$I_R$        $V_R=40V, T_A=100^{\circ}C$

$V_F$        $I_F=2.0A$

$C_J$        $V_R=4.0V, f=1.0MHz$

**TYP**

5.5

2.0

480

155

**MAX**

100

20

500

250

**UNITS**

$\mu A$

mA

mV


pF

R1 (26-November 2012)

**CBRLDSH2-40**  
**SURFACE MOUNT**  
**HIGH DENSITY**  
**2 AMP SILICON**  
**SCHOTTKY BRIDGE RECTIFIER**



**LPDIP CASE - MECHANICAL OUTLINE**



R0

DIMENSIONS				
SYMBOL	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.019	0.028	0.50	0.70
B	0.007	0.012	0.20	0.30
C	0.153	0.162	3.90	4.10
D	0.167	0.179	4.25	4.55
E	0.248	0.264	6.30	6.70
F	0.023	0.028	0.60	0.70
G	0.045	0.058	1.15	1.45
H	0.190	0.203	4.85	5.15
J	0.002	0.006	0.05	0.15

LPDIP (REV: R0)

**MARKING CODE: CL40**

R1 (26-November 2012)

[www.centrasemi.com](http://www.centrasemi.com)

**CBRLDSH2-40**

**SURFACE MOUNT**





**HIGH DENSITY**

**2 AMP SILICON**

**SCHOTTKY BRIDGE RECTIFIER**



**TYPICAL ELECTRICAL CHARACTERISTICS**



R1 (26-November 2012)

[www.centrasemi.com](http://www.centrasemi.com)

## OUTSTANDING SUPPORT AND SUPERIOR SERVICES



---

### PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

---

### DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2<sup>nd</sup> day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

---

### REQUESTING PRODUCT PLATING

1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

---

### CONTACT US

#### Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.  
145 Adams Avenue  
Hauppauge, NY 11788 USA  
Main Tel: (631) 435-1110  
Main Fax: (631) 435-1824  
Support Team Fax: (631) 435-3388  
[www.centrasemi.com](http://www.centrasemi.com)

**Worldwide Field Representatives:**  
[www.centrasemi.com/wwreps](http://www.centrasemi.com/wwreps)

**Worldwide Distributors:**  
[www.centrasemi.com/wwdistributors](http://www.centrasemi.com/wwdistributors)

---

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: [www.centrasemi.com/terms](http://www.centrasemi.com/terms)