




Similar to illustration

- Features:**
- Switched-mode power supply with PowerBoost and TopBoost
 - Switch off the output and minimize power consumption via stand-by input
 - Output monitoring via DC OK contact
 - Suitable for both parallel and series operation
 - Natural convection cooling when horizontally mounted
 - Encapsulated for use in control cabinets
 - Electrically isolated output voltage (SELV) per UL 60950-1; PELV per EN 60204

Technical data			
Input		Output	
Phases	2 / 3	Nominal output voltage $U_{o\,nom}$	24 VDC (SELV)
Nominal input voltage $U_{i\,nom}$	(2 / 3) x 400 ... 500 VAC	Output voltage range	22.8 ... 28.8 VDC (adjustable)
Input voltage range	(2 / 3) x 340 ... 550 VAC; 480 ... 780 VDC	Default Setting	24 VDC
Nominal mains frequency range	50 ... 60 Hz; 0 Hz	Nominal output current $I_{o\,nom}$	40 A (24 VDC)
Input current I_i	$\leq 3 \times 2 \text{ A}$ (340 VAC; 40 ADC)	Nominal output power	960 W
Discharge current	$\leq 1 \text{ mA}$	Deviation	$\leq 1 \%$
Inrush current	$\leq 30 \text{ A}$	Residual ripple	$\leq 70 \text{ mV}$ (peak-to-peak)
Power factor correction (PFC)	Passive	Current limitation	$1.1 \times I_{o\,nom}$ (typ.)
Mains failure hold-up time	$\geq 15 \text{ ms}$ (3 x 400 VAC)	Overload behavior	TopBoost/PowerBoost/Constant current mode
		PowerBoost	60 ADC (4 s); 50 ADC (16 s)
		TopBoost	100 ADC (50 ms)

Signaling and Communication	
Signaling	1 x DC OK LED (green) 1 x Error LED (red) 1 x Stand-by input 1 x DC OK relay contact (changeover contact)
Operation status indicator	Green LED (DC OK) Red LED (error)

Efficiency/Power Losses	
Power loss P_i	$\leq 7 \text{ W}$; $\leq 61.5 \text{ W}$ (nominal load)
Efficiency (typ.)	93.6 %

Isolation voltage (pri.-sec.)	4.242 kVDC
Isolation voltage (pri.-PE)	2.2 kVDC
Isolation voltage (sec.-PE)	0.7 kVDC
Protection class	I
Protection type	IP20; per EN 60529
Resistance to reverse feed	≤ 35 VDC
Overvoltage category	II
Pollution degree	2
Transient suppression (primary)	Varistor
Short-circuit-protected	Yes
Open-circuit-proof	Yes
Parallel operation	Yes
Series operation	Yes
MTBF	> 500,000 h (per IEC 61709)

Connection 1	
Connection type	Input
Connection technology	CAGE CLAMP®
WAGO connector	WAGO 231 Series
Solid conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Fine-stranded conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Connection 2	
Connection type	Output
Connection technology	Push-in CAGE CLAMP®
WAGO connector	WAGO 831 Series
Solid conductor	0.5 ... 10 mm² / 20 ... 8 AWG
Fine-stranded conductor	0.5 ... 10 mm² / 20 ... 8 AWG
Strip length	13 ... 15 mm / 0.51 ... 0.59 inches

Connection type	Signaling
Connection technology	CAGE CLAMP®
WAGO connector	WAGO 733 Series
Solid conductor	0.08 ... 0.5 mm² / 28 ... 20 AWG
Fine-stranded conductor	0.08 ... 0.5 mm² / 28 ... 20 AWG
Strip length	5 ... 6 mm / 0.2 ... 0.24 inches

Width	128 mm / 5.039 inches
Height	171 mm / 6.732 inches
Depth from upper-edge of DIN-rail	205 mm / 8.071 inches
Note (dimensions)	Height with connector



Mechanical data	
Mounting type	DIN-35 rail

Material data	
Weight	2500 g

Environmental requirements	
Ambient temperature (operation)	-25 ... +55 °C (Device starts at -40 °C (type-tested))
Ambient temperature (storage)	-25 ... +85 °C
Relative humidity	5 ... 96 % (no condensation permissible)
Derating	-5 %/K (> 45 °C)
Climatic category	3K3 (per EN 60721)

Standards and Specifications	
Conformity marking	CE
Standards/specifications	EN 61010-1 EN 61010-2-201 EN 61204-3 EN 61558-2-16 UL 60950 UL 508

Commercial data	
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821594444
Customs tariff number	85044083900

Product Classification	
UNSPSC	39121004
eCl@ss 10.0	27-04-07-01
eCl@ss 9.0	27-04-07-01
ETIM 9.0	EC002540
ETIM 10.0	EC002540
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption



Approvals / Certificates

General approvals			Declarations of conformity and manufacturer's declarations		
EAC EAC					
Approval	Standard	Certificate Name	Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 004/2011	EAC CoC 03078	EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
EAC GZO Almaty Standart	TP TC 020/2011	EAC CoC 03081			
UL Underwriters Laboratories Inc.	UL 508	E255817			

Downloads

Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 787-844/000-002	

Documentation

Bid Text			
787-844/000-002	04.07.2019	xml 7.65 KB	
787-844/000-002	04.07.2019	docx 20.48 KB	

CAD/CAE-Data

CAD data		CAE data	
2D/3D Models 787-844/000-002		EPLAN Data Portal 787-844/000-002	
		WSCAD Universe 787-844/000-002	

Engineering-Software

Configuration and Commissioning Software			
WAGO Line Length Calculation	1.3.5 09.12.2019	exe 329.50 KB	

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marker



Item No.: 2009-145
Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white



Item No.: 248-501
Mini-WSB marking card; as card; not stretchable; plain; snap-on type; white



Item No.: 793-5501
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; white



Item No.: 793-501
WMB marking card; as card; not stretchable; plain; snap-on type; white



Item No.: 2009-115
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

1.1.1.2 Marking strip



Item No.: 2009-110
Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white



Item No.: 210-831
Marking strips; on reel; 2.3 mm wide; plain; Self-adhesive; white



Item No.: 210-832
Marking strips; on reel; 3 mm wide; plain; Self-adhesive; white

1.1.2 Mounting adapter

1.1.2.1 DIN-rail adapter



Item No.: 787-897
Carrier rail adapter made of zinc die-cast; for mounting 787-8xx devices to a DIN 35 rail; gray



Item No.: 787-896
Carrier rail adapter; for mounting 787-8xx devices to a DIN 35 rail; gray

1.1.2.2 Wall-mount adapter



Item No.: 787-895
Mounting carrier; for screw fixing of 787-8xx devices on mounting plate or wall without DIN 35 rail; gray

1.1.3 Tool

1.1.3.1 Operating tool



Item No.: 210-719
Operating tool; Blade: 2.5 x 0.4 mm; with a partially insulated shaft



Item No.: 210-720
Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured



Item No.: 210-721
Operating tool; Blade: 5.5 x 0.8 mm; with a partially insulated shaft; multicoloured



Item No.: 210-769
SCREWDRIVER; green