





PRODUCT NUMBER	PITCH
YK551xx0x0J0G	11.00 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

MATERIALS & ELECTRICAL
 RATED VOLTAGE & CURRENT: 300 V, 30 A
 WITHSTAND VOLTAGE: AC 2000 V/Min
 INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
 OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
 SCREW TORQUE VALUE: 9.5 Lb-In.
 WIRE RANGE: 22-10AWG str/sol
 1) HOUSING: Thermoplastic, UL 94 V-0 BLACK
 2) TERMINAL: BRASS, 0.8t
 3) TERMINAL SCREWS: STEEL, M4
 APPROVAL:

DIMENSION

Dim A	N×11.0±2.0
Dim B	(N-1)×11.0

N=Number of poles

Poles	Tolerance
2p-4p	±0.30
5p-8p	±0.40
9p-16p	±0.50
17p-23p	±0.60
24p-32p	±0.80

PART NO.: YK 551xx 0 x 0 J0G

No. of poles
 02 2 poles
 03 3 poles
 ...
 32 32 poles

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
 (lead<4%)
 In copper Alloy

mat'l. code				surface	tolerance	projection	product family	
ltr	ecn	no	dr	date	ASME Y14.5	ASME Y14.5	TERMINAL BLOCK	
					tolerances unless otherwise specified		title	
					angles	X.±0.5	TERMINAL BLOCK	
					flatness	X.X±0.3	BARRIER TYPE	
					X'±1"	X.XX±0.1	scale	
					dr	EVAN LU 061614	dwg no	
					enr	EVAN LU 061614	sheet 1 of 1	
					chr	HANKE FENG 061614	YK551xx0x0J0G	
					appd	SHI JUN 061614	size	
							A4	
							type	
							CUSTOMER Drawing	
sheet index	revision	A						
	sheet	1						