
© – TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECN–25–354023	18NOV2025	SN	DR



1 WIRE RANGE IS FOR 1/0 AWG. STANDARD WIRE CROSS SECTIONAL AREA RANGE: 83,700–119,500 CMA, STRANDED WIRE.

2 TERMINAL BODY MATERIAL THK IS 1.778±0.076[0.070±0.003].

3 RECOMMENDED OPERATING TEMP –65°C [–85°F] TO +200°C [392°F] FOR HEAT SHRINK TUBING

4 HEAT SHRINK TUBING SHELF LIFE OF 144 MONTHS FROM DATE CODE ON LABEL

△5 TERMINAL BODY PRODUCT SPECIFICATION 108–32046. APPLICATION SPECIFICATION 114–2162.

QTY	PART NO	DESCRIPTION
1	1–1196717–9	HIGH AND LOW TEMPERATURE CROSS LINKED FLUOROPOLYMER HEAT SHRINK TUBING 15.88[0.625] MIN ID X 44.45±3.05 [1.75±0.12] RT555–5/8–0–SP
1	321867–2	TERMINAL BODY: COPPER PER ASTM B152 ANNEALED FINISH: NICKEL PLATE 0.00762 [0.000300] MIN EXT THK PER SAE AMS QQ–N–290

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± 0.127 [0.005]
4 PLC ± –
ANGLES ± 1°

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DWN JR RUTH 08DEC09
CHK T MICHIELUTTI 08DEC09
APVD T MICHIELUTTI 08DEC09
PRODUCT SPEC — 5
APPLICATION SPEC — 5
WEIGHT —

TE Connectivity

NAME
–
HEAT RESISTANT TERMINAL KIT
WIRE SIZE: 1/0 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C–696646	—

CUSTOMER DRAWING

SCALE 3:1 SHEET 1 OF 1 REV C

1470–19 (1/15)

Downloaded from Arrow.com.