


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/04/07	
A		REVISED DIMENSION	8/30/11	
B		UPDATE DRAWING	11/25/19	AY/RC
C		UPDATE SPEC.	8/24/21	WX/TL


D

D



C

C



B

B

SPECIFICATIONS:

Material:

Insulator: Nylon66, rated UL 94V-0

Insulator color: Natural

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Voltage rating: 130 VAC/DC



Current rating: 2A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min


Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:


Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



RECOMMENDED P.C.B. LAYOUT



Positions: 4 thru 40

A = .079 [2.00] x No. of Positions per Row +.075 [1.90]

B = .079 [2.00] x No. of Space

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

DRAWN SS 12/04/07

CHECKED

APPROVED

ADAM
TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710TITLE: .079 [2.00] DOUBLE ROW, SHROUDED
HEADER, RIGHT ANGLE, PCB, TIN PLATEDSIZE X PART NO. 2SHD-C-XX-TR REV. C
REF: S00015T SCALE: NTS SHEET 1 OF 1THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH