





- 1 WIRE INSULATION: .324-356 DIA
- 2 THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.
- 3 FLASH PERMITTED $\pm .020$
- 4 STAMP "AMP 4 AL 13-78" SIZE AND LOCATION APPROX AS SHOWN



BODY: COPPER ASTM-B187 ANNEALED TIN PL PER ASTM B-545 .000150 MIN THK INSERT & FUNNEL: BRASS ASTM B36 NICKEL PL SAE AMS QQ-N-290A, DATED JULY 2000, .000100 MIN THK	696872-1
MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN JR RUTH 21OCT05	 TE Connectivity			
			CHK MJ SPICER 21OCT05				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .01 3 PLC ± .008 4 PLC ± - ANGLES ± -	APVD MJ SPICER 21OCT05	NAME WIRE TERMINAL, RING TONGUE, SEALED COPALUM, WIRE SIZE: 4 ALUMINUM			
			PRODUCT SPEC —				
			APPLICATION SPEC —				
			SIZE A2				CAGE CODE 00779
MATERIAL SEE TABLE		FINISH SEE TABLE	WEIGHT 18.5 GRAMS				
CUSTOMER DRAWING			SCALE 2:1			SHEET 1 of 1	REV F