



**Part Number :** [1300170021](#)

**Product Description :** Mini-Change Field Attachable, Male Connector, 4 Pole, Cable Range: 5.08-11.43mm Outside Diameter with External Threads, Stainless Steel

**Series Number :** 130017

**Status :** Active

**Product Category :** Circular Industrial Connectors

**Engineering Part Number :** 1A4006-348



---

## Documents and Resources

### Drawings

[1300170021\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

## Part Details

### General

Status	Active
Category	Circular Industrial Connectors
Series	130017
Description	Mini-Change Field Attachable, Male Connector, 4 Pole, Cable Range: 5.08-11.43mm Outside Diameter with External Threads, Stainless Steel
Approvals	cCSAus certified
IP Rating	IP67
Product Name	Mini-Change
Type	Field Attachable Connector
UPC	78678853658

### Agency

CSA	LR6837
-----	--------

### Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	600V AC/DC

### Physical

Cable Diameter	5.08-11.43mm (.200-.450")
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No

Gender	Male
Keyway	Single
Material - Connector Body	Nylon
Material - Contact	Copper Alloy
Material - Coupling Nut	Stainless Steel Type 316
Material - Plating Mating	Gold
Net Weight	54.900/g
Orientation	Straight
Poles	4
Temperature Range - Operating	-20° to +80°C
Wire Size (AWG)	15 to 24

---

This document was generated on May 09, 2026