Part Number : 1703401022
Product Description : Impact 85 Ohm Plus 4 Pair, Right-Angle Daughtercard, Unguided, 12 Columns, 144 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free
Series Number : 170340
Status : Active
Product Category : Backplane Connectors



Documents and Resources

Drawings

1703401022_sd.pdf

PK-70873-610-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

SYM-170340-1022-001.zip

EE-170340-001-001.pdf

SP-170340-001-001.zip

Specifications

AS-76060-990-001.pdf

PS-170540-999-001.pdf

Tooling Specifications

ATS-622018839-001.pdf

ATS-622024300-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006

Downloaded from Arrow.com.

EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	170340
Description	Impact 85 Ohm Plus 4 Pair, Right-Angle Daughtercard, Unguided, 12 Columns, 144 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free
Application	Conventional, Coplanar, Daughtercard
Component Type	PCB Receptacle
Product Name	Impact
UPC	884982968660

Agency

Downloaded from Arrow.com.

UL	E29179

Electrical

Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	85Ω
Shielded	No
Shield Type	N/A
Voltage - Maximum	30V AC (RMS)/DC

Physical

Circuits (Loaded)	144
Circuits (maximum)	144
Color - Resin	Gray
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	15.875/g
Number of Columns	12
Number of Pairs	4
Number of Rows	12
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.00mm
PC Tail Length	1.20mm
Pitch - Mating Interface	1.35mm, 1.90mm
Pitch - Termination Interface	1.35mm, 1.90mm

Downloaded from Arrow.com.

Plating min - Mating	0.762µm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Impact 85 Ohm Plus 4 Pair Vertical Headers	170335

Application Tooling

Downloaded from Arrow.com.