





4611110010442



接线图
Wiring Diagram




励磁顺序 vs. 旋转方向
Exciting Sequence vs.
Direction of Rotation

STEP	A	B	C	D	
1	+	+	-	-	CCW ↑
2	-	+	+	-	
3	-	-	+	+	
4	+	-	-	+	

从安装面看为顺时针方向
Clockwise view from
mounting side

规格 Specifications

1. 相数 Number of Phase	2
2. 步距角 Step Angle	1.8°
3. 额定电压 Rated Voltage	4.83 V DC
4. 额定电流 Rated Current	0.84 A
5. 保持力矩 Holding Torque	0.28 N.m MIN(Two phase on/rated current)
6. 相电阻 Phase Resistance	5.75 ohm±10%(20°C)
7. 相电感 Phase Inductance	9.3 mH±20%(1kHz 1V rms)
8. 转子惯量 Rotor Inertia	38g.cm ²
9. 电机重量 Motor Weight	0.23kg
10. 绝缘等级 Insulation Class	B(130°C)



铭牌 Label Detail

MOONS' STEPPING MOTOR
TYPE 17HD4063-04N
XXXXXXXX YY/MM/DD

Work Order Date Format
加工单号 日期格式

Unit: mm

第一角画法


FIRST ANGLE METHOD

未注线性与角尺寸公差
Tolerances for linear and angular dimensions without
individual tolerance indications

GB/T 1804-m eqv ISO 2768-1:m

未注形状与位置尺寸公差
Geometrical tolerance for features without
individual tolerance indications

GB/T 1184-K eqv ISO 2768-2:K



批准 Approve

标准化 Standard

工艺 Technology

审核 Check

设计 Design

2013/9/2

13-9-2

13-9-3

9-9

2013.09.01

MOONS'

Shanghai Moons' Electric Co., Ltd.

Hybrid Stepping Motor

This document is released for information only. Its reproduction
in whole or in part or its dissemination to third parties is prohibited.
All trademarks and registered trademarks appearing on this
document are the property of their respective owners.

Type: 17HD4063-04N

Rev.B

SCALE 1:1

Sheet 1 of 1

B	取消线束标注颜色	13.09.01
A	原始版本 Original revision	2012.07.25

REV.	版本记录 REVISION RECORD	DATE
------	----------------------	------

UNLESS OTHERWISE SPECIFIED

NAMES

SIGNATURE

DATE

Type: 17HD4063-04N

Rev.B

SCALE 1:1

Sheet 1 of 1