


Customer Information Sheet


DRAWING No.: S0911-46R	IF IN DOUBT - ASK	©	NOT TO SCALE	THIRD ANGLE PROJECTION	ALL DIMENSIONS IN mm




REEL DETAILS









SECTION Y-Y





SECTION X-X







CROPPED COMPONENT DIMENSIONS









RECOMMENDED PAD LAYOUT (TOLERANCE ±0.05)

COMPONENT SPECIFICATION:
- MATERIAL = BERYLLIUM COPPER
- FINISH = 2.40µm - 3.60µm TIN OVER
  2.00µm - 2.80µm NICKEL
- ELECTRICAL:
  - CONTACT RESISTANCE = 25mΩ MAX
- MECHANICAL:
  - MAX INSERTION FORCE WITH 0.20mm SHEET = 3.00N
  - MIN INSERTION FORCE WITH 0.20mm SHEET = 0.10N
  - MAX WITHDRAWAL FORCE WITH 0.20mm SHEET = 2.50N
  - MIN WITHDRAWAL FORCE WITH 0.20mm SHEET = 0.10N
  - DURABILITY = 20 CYCLES
- ENVIRONMENTAL:
  - OPERATING TEMPERATURE = -55°C TO +105°C

NOTES:
1. QUANTITY OF COMPONENTS PER REEL: 6,500.
2. THIS PRODUCT IS TAPE AND REELED IN GENERAL ACCORDANCE WITH EIA-481-2 (ELECTRONICS INDUSTRIES ASSOCIATION).
3. RECOMMENDED CAN THICKNESS: 0.15-20mm.

MR	I	11.03.19	21823
NAME	ISS.	DATE	C/NOTE
APPROVED:	M.RUDKIN		
CHECKED:	S.BENNETT		
DRAWN:	S.BENNETT		
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.50mm
X.XX = ±0.20mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL: SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²

TITLE: COMPACT RFI SHIELD CLIP IN TAPE AND REEL

DRAWING NUMBER: S0911-46R

SHT 2 OF 2